

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244988

Luminaire Tested: PRLX-MIN-S-940-05L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-S-940-05L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, OPEN WEAVE SHADE TEXTURE LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.38
Luminous Opening: Rectangular w/ Sides (W: 0.62' x L: 0.62' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76	74	71	69	66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63	65	61	57	58	55	52	49
3	85	74	66	60	80	71	63	58	64	58	53	58	53	49	52	48	45	42
4	78	67	58	52	74	63	56	50	58	51	46	52	47	43	47	43	40	37
5	72	60	52	46	68	58	50	44	53	46	41	48	43	38	44	39	36	33
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	33	30
7	63	51	42	37	60	49	41	36	45	38	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	53	41	34	29	50	39	33	28	37	31	27	34	29	26	32	27	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13400
5°	13328
10°	11786
15°	2805
20°	2345
25°	1969
30°	1565
35°	1293
40°	1128
45°	1028
50°	947
55°	888
60°	834
65°	787
70°	752
75°	705
80°	646
85°	602

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1028 cd/sqm



TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	8.8
10°-20°	53.2	9.2
20°-30°	48.5	8.4
30°-40°	48.0	8.3
40°-50°	48.8	8.5
50°-60°	49.4	8.6
60°-70°	47.9	8.3
70°-80°	43.2	7.5
80°-90°	35.6	6.2
90°-100°	33.4	5.8
100°-110°	31.8	5.5
110°-120°	28.5	4.9
120°-130°	23.6	4.1
130°-140°	16.8	2.9
140°-150°	9.7	1.7
150°-160°	5.0	0.9
160°-170°	1.9	0.3
170°-180°	0.1	0.0
0°-30°	152.1	26.4
0°-40°	200.1	34.7
0°-60°	298.3	51.8
0°-90°	425.1	73.8
90°-120°	93.7	16.3
90°-150°	143.8	25.0
90°-180°	151.0	26.2
0°-180°	576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	540	50
15°	135	53
25°	107	48
35°	76	48
45°	63	49
55°	55	49
65°	48	48
75°	41	43
85°	32	27
90°	31	17
95°	30	25
105°	30	32
115°	29	28
125°	26	24
135°	22	17
145°	15	10
155°	11	5
165°	7	2
175°	0	0
180°	0	

TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	486.3
2.5°	503.9
5°	540.5
7.5°	533.9
10°	524.6
12.5°	232.1
15°	135.0
17.5°	128.0
20°	120.5
22.5°	114.3
25°	106.8
27.5°	97.1
30°	88.7
32.5°	81.2
35°	75.9
37.5°	71.5
40°	68.0
42.5°	65.3
45°	63.1
47.5°	60.9
50°	58.7
52.5°	56.9
55°	55.2
57.5°	53.4
60°	51.6
62.5°	49.9
65°	48.1
67.5°	46.8
70°	45.0
72.5°	43.2
75°	41.0
77.5°	38.8
80°	36.2
82.5°	33.5
85°	32.2
87.5°	31.3
90°	30.9
92.5°	30.9
95°	30.4
97.5°	30.4
100°	30.4
102.5°	30.4
105°	30.0
107.5°	30.0
110°	29.6

TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	29.1
115°	28.7
117.5°	28.2
120°	27.8
122.5°	26.9
125°	26.5
127.5°	25.6
130°	24.3
132.5°	23.4
135°	21.6
137.5°	20.3
140°	18.5
142.5°	16.8
145°	15.0
147.5°	13.7
150°	12.8
152.5°	11.9
155°	10.6
157.5°	9.7
160°	8.8
162.5°	7.9
165°	6.6
167.5°	5.3
170°	3.5
172.5°	1.8
175°	0.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1244988

CATALOG NUMBER: PRLX-MIN-S-940-05L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.3	9.4	9.0	10.2	11.0	8.3	9.4	9.0	10.2	11.0
	3H	10.6	11.6	11.3	12.4	13.3	10.6	11.6	11.3	12.4	13.3
	4H	11.6	12.6	12.4	13.4	14.3	11.6	12.6	12.4	13.4	14.3
	6H	12.6	13.5	13.3	14.3	15.2	12.6	13.5	13.3	14.3	15.2
	8H	13.0	13.9	13.8	14.7	15.6	13.0	13.9	13.8	14.7	15.6
	12H	13.4	14.3	14.2	15.0	16.0	13.4	14.3	14.2	15.0	16.0
4H	2H	8.9	9.9	9.6	10.6	11.5	8.9	9.9	9.6	10.6	11.5
	3H	11.4	12.2	12.2	13.0	14.0	11.4	12.2	12.2	13.0	14.0
	4H	12.6	13.4	13.4	14.2	15.1	12.6	13.4	13.4	14.2	15.1
	6H	13.7	14.4	14.5	15.2	16.2	13.7	14.4	14.5	15.2	16.2
	8H	14.2	14.9	15.0	15.7	16.7	14.2	14.9	15.0	15.7	16.7
	12H	14.7	15.3	15.5	16.1	17.1	14.7	15.3	15.5	16.1	17.1
8H	4H	13.0	13.6	13.8	14.4	15.4	13.0	13.6	13.8	14.4	15.4
	6H	14.3	14.8	15.1	15.7	16.7	14.3	14.8	15.1	15.7	16.7
	8H	14.9	15.4	15.7	16.3	17.3	14.9	15.4	15.7	16.3	17.3
	12H	15.6	16.0	16.4	16.8	17.9	15.6	16.0	16.4	16.8	17.9
12H	4H	13.0	13.6	13.8	14.5	15.5	13.0	13.6	13.8	14.5	15.5
	6H	14.4	14.9	15.2	15.7	16.8	14.4	14.9	15.2	15.7	16.8
	8H	15.1	15.5	15.9	16.4	17.4	15.1	15.5	15.9	16.4	17.4

(END OF REPORT)