

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979782

Luminaire Tested: PRLX-241-935-LL5-F-U-S-BLAK-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P979782  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-241-935-LL5-F-U-S-BLAK-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1953.8 lumens  
Efficiency: N/A  
Efficacy: 66.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P979782  
CATALOG NUMBER: PRLX-241-935-LL5-F-U-S-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P979782

CATALOG NUMBER: PRLX-241-935-LL5-F-U-S-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68
6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64	63
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13007
5°	12791
10°	12445
15°	12130
20°	11974
25°	11808
30°	11600
35°	10198
40°	4528
45°	568
50°	132
55°	148
60°	148
65°	150
70°	124
75°	122
80°	120
85°	124

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 568 cd/sqm

TEST NUMBER: P979782

CATALOG NUMBER: PRLX-241-935-LL5-F-U-S-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.7	8.0
10°-20°	429.4	22.0
20°-30°	639.4	32.7
30°-40°	617.1	31.6
40°-50°	89.8	4.6
50°-60°	9.4	0.5
60°-70°	7.6	0.4
70°-80°	4.3	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1224.5	62.7
0°-40°	1841.6	94.3
0°-60°	1940.7	99.3
0°-90°	1953.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1953.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1687	
5°	1653	156
15°	1520	429
25°	1388	639
35°	1084	617
45°	52	90
55°	11	9
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P979782

CATALOG NUMBER: PRLX-241-935-LL5-F-U-S-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1687.2
2.5°	1679.0
5°	1652.9
7.5°	1618.6
10°	1589.8
12.5°	1551.4
15°	1519.8
17.5°	1489.7
20°	1459.5
22.5°	1427.9
25°	1388.2
27.5°	1347.0
30°	1303.1
32.5°	1233.2
35°	1083.6
37.5°	802.4
40°	449.9
42.5°	186.6
45°	52.1
47.5°	16.5
50°	11.0
52.5°	11.0
55°	11.0
57.5°	9.6
60°	9.6
62.5°	8.2
65°	8.2
67.5°	6.9
70°	5.5
72.5°	5.5
75°	4.1
77.5°	2.7
80°	2.7
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0



TEST NUMBER: P979782  
 CATALOG NUMBER: PRLX-241-935-LL5-F-U-S-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.17	0.00	0.00	0.00	0.00	0.17
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00