

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979792

Luminaire Tested: PRLX-241-935-LL6-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-LL6-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2177.1 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979792
CATALOG NUMBER: PRLX-241-935-LL6-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979792

CATALOG NUMBER: PRLX-241-935-LL6-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95				93	
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88				86	
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81				79	
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75				73	
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69				68	
6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64				63	
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60				58	
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55				54	
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52				50	
10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48				47	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14493
5°	14253
10°	13867
15°	13516
20°	13342
25°	13157
30°	12925
35°	11364
40°	5045
45°	633
50°	146
55°	164
60°	165
65°	168
70°	137
75°	137
80°	138
85°	133

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 633 cd/sqm

TEST NUMBER: P979792

CATALOG NUMBER: PRLX-241-935-LL6-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	8.0
10°-20°	478.5	22.0
20°-30°	712.5	32.7
30°-40°	687.6	31.6
40°-50°	100.0	4.6
50°-60°	10.4	0.5
60°-70°	8.5	0.4
70°-80°	4.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1364.4	62.7
0°-40°	2052.0	94.3
0°-60°	2162.5	99.3
0°-90°	2177.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2177.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1880	
5°	1842	173
15°	1694	478
25°	1547	712
35°	1208	688
45°	58	100
55°	12	10
65°	9	9
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P979792

CATALOG NUMBER: PRLX-241-935-LL6-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1880.0
2.5°	1870.8
5°	1841.8
7.5°	1803.6
10°	1771.5
12.5°	1728.7
15°	1693.5
17.5°	1659.9
20°	1626.3
22.5°	1591.1
25°	1546.8
27.5°	1500.9
30°	1452.0
32.5°	1374.1
35°	1207.5
37.5°	894.1
40°	501.3
42.5°	207.9
45°	58.1
47.5°	18.3
50°	12.2
52.5°	12.2
55°	12.2
57.5°	10.7
60°	10.7
62.5°	9.2
65°	9.2
67.5°	7.6
70°	6.1
72.5°	6.1
75°	4.6
77.5°	3.1
80°	3.1
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0

TEST NUMBER: P979792
 CATALOG NUMBER: PRLX-241-935-LL6-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.04	0.00	0.00	0.00	0.00	0.04
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.12	0.00	0.00	0.00	0.00	0.12
	8H	0.00	0.00	0.00	0.00	0.30	0.00	0.00	0.00	0.00	0.30
	12H	0.00	0.00	0.00	0.00	0.55	0.00	0.00	0.00	0.00	0.55
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.13	0.00	0.00	0.00	0.00	0.13
	8H	0.00	0.00	0.00	0.00	0.39	0.00	0.00	0.00	0.00	0.39