

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979810

Luminaire Tested: PRLX-241-935-LL8-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-LL8-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH CLEAR LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3660.1 lumens
Efficiency: N/A
Efficacy: 59.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.05
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 61.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979810

CATALOG NUMBER: PRLX-241-935-LL8-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979810

CATALOG NUMBER: PRLX-241-935-LL8-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	103	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	83	79	95	88	82	78	85	81	77		83	80	76		82
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	72	66	62	81	72	66	62	70	65	61		69	65	61		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	57	53	62	57	53		61	57	53		61
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26540
5°	25308
10°	24103
15°	23557
20°	23401
25°	23239
30°	22995
35°	21622
40°	3327
45°	541
50°	255
55°	254
60°	291
65°	301
70°	266
75°	280
80°	209
85°	212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 541 cd/sqm

TEST NUMBER: P979810

CATALOG NUMBER: PRLX-241-935-LL8-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.1	8.4
10°-20°	835.1	22.8
20°-30°	1258.5	34.4
30°-40°	1147.9	31.4
40°-50°	67.5	1.8
50°-60°	17.2	0.5
60°-70°	15.5	0.4
70°-80°	9.0	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2399.8	65.6
0°-40°	3547.6	96.9
0°-60°	3632.3	99.2
0°-90°	3660.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3660.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3443	
5°	3270	306
15°	2952	835
25°	2732	1259
35°	2298	1148
45°	50	67
55°	19	17
65°	16	15
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P979810

CATALOG NUMBER: PRLX-241-935-LL8-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3442.7
2.5°	3397.9
5°	3270.4
7.5°	3154.7
10°	3079.1
12.5°	3010.6
15°	2951.6
17.5°	2902.0
20°	2852.4
22.5°	2805.2
25°	2732.0
27.5°	2654.1
30°	2583.2
32.5°	2500.6
35°	2297.5
37.5°	1237.3
40°	330.6
42.5°	111.0
45°	49.6
47.5°	26.0
50°	21.3
52.5°	18.9
55°	18.9
57.5°	18.9
60°	18.9
62.5°	16.5
65°	16.5
67.5°	14.2
70°	11.8
72.5°	9.4
75°	9.4
77.5°	7.1
80°	4.7
82.5°	4.7
85°	2.4
87.5°	2.4
90°	0.0

TEST NUMBER: P979810

CATALOG NUMBER: PRLX-241-935-LL8-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.13	0.00	0.00	0.00	0.00	0.13
	4H	0.00	0.14	0.00	0.50	0.89	0.00	0.14	0.00	0.50	0.89
	6H	0.00	0.57	0.31	0.95	1.34	0.00	0.57	0.31	0.95	1.34
	8H	0.11	0.74	0.54	1.14	1.55	0.11	0.74	0.54	1.14	1.55
	12H	0.24	0.85	0.68	1.24	1.67	0.24	0.85	0.68	1.24	1.67
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.03	0.00	0.44	0.84	0.00	0.03	0.00	0.44	0.84
	4H	0.34	0.89	0.78	1.31	1.76	0.34	0.89	0.78	1.31	1.76
	6H	0.93	1.39	1.40	1.84	2.32	0.93	1.39	1.40	1.84	2.32
	8H	1.20	1.63	1.68	2.08	2.56	1.20	1.63	1.68	2.08	2.56
	12H	1.38	1.75	1.88	2.24	2.72	1.38	1.75	1.88	2.24	2.72
8H	4H	0.60	1.03	1.08	1.48	1.96	0.60	1.03	1.08	1.48	1.96
	6H	1.30	1.64	1.82	2.15	2.63	1.30	1.64	1.82	2.15	2.63
	8H	1.70	2.00	2.23	2.52	3.02	1.70	2.00	2.23	2.52	3.02
	12H	1.98	2.24	2.51	2.74	3.32	1.98	2.24	2.51	2.74	3.32
12H	4H	0.59	0.96	1.08	1.45	1.93	0.59	0.96	1.08	1.45	1.93
	6H	1.35	1.65	1.89	2.17	2.67	1.35	1.65	1.89	2.17	2.67
	8H	1.82	2.08	2.35	2.58	3.16	1.82	2.08	2.35	2.58	3.16

END OF REPORT