

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245008

Luminaire Tested: PRLX-NIM-L-927-09L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-927-09L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL LINES SHADE TEXTUF
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 785.2 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	78	87	82	77	73	70	66	62	58	55	53	48	45	43	38
2	85	76	68	61	78	70	63	57	59	54	49	49	45	42	40	37	34	30
3	77	66	57	50	71	61	53	47	52	45	40	43	38	34	35	31	28	24
4	71	58	49	42	65	54	46	40	46	39	34	38	33	29	31	27	24	20
5	65	52	43	36	60	48	40	34	41	35	30	34	29	25	28	24	21	18
6	60	47	38	32	55	44	36	30	37	31	26	31	26	22	26	22	19	16
7	56	43	34	28	51	40	32	27	34	28	23	29	24	20	24	20	17	15
8	52	39	31	25	48	36	29	24	32	25	21	27	22	18	23	19	16	13
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12
10	46	33	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34363
5°	15559
10°	3706
15°	1468
20°	931
25°	744
30°	638
35°	592
40°	594
45°	564
50°	574
55°	588
60°	606
65°	596
70°	623
75°	622
80°	626
85°	635

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 650 cd/sqm

TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	5.9
10°-20°	26.2	3.3
20°-30°	25.4	3.2
30°-40°	32.6	4.2
40°-50°	42.8	5.5
50°-60°	53.8	6.8
60°-70°	64.1	8.2
70°-80°	71.4	9.1
80°-90°	73.6	9.4
90°-100°	73.6	9.4
100°-110°	71.4	9.1
110°-120°	63.7	8.1
120°-130°	52.2	6.7
130°-140°	39.9	5.1
140°-150°	26.9	3.4
150°-160°	14.8	1.9
160°-170°	5.9	0.8
170°-180°	0.7	0.1
0°-30°	97.7	12.4
0°-40°	130.3	16.6
0°-60°	226.9	28.9
0°-90°	436.0	55.5
90°-120°	208.7	26.6
90°-150°	327.7	41.7
90°-180°	349.0	44.4
0°-180°	785.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1086	
5°	631	46
15°	84	26
25°	54	25
35°	51	33
45°	54	43
55°	61	54
65°	64	64
75°	68	71
85°	68	55
90°	68	37
95°	68	55
105°	68	71
115°	64	64
125°	57	52
135°	51	40
145°	44	27
155°	30	15
165°	20	6
175°	3	1
180°	0	

TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	1086.2
2.5°	1204.2
5°	630.8
7.5°	266.5
10°	182.2
12.5°	114.7
15°	84.3
17.5°	70.8
20°	60.7
22.5°	57.3
25°	54.0
27.5°	54.0
30°	50.6
32.5°	50.6
35°	50.6
37.5°	54.0
40°	54.0
42.5°	54.0
45°	54.0
47.5°	57.3
50°	57.3
52.5°	57.3
55°	60.7
57.5°	60.7
60°	64.1
62.5°	64.1
65°	64.1
67.5°	64.1
70°	67.5
72.5°	67.5
75°	67.5
77.5°	67.5
80°	67.5
82.5°	67.5
85°	67.5
87.5°	67.5
90°	67.5
92.5°	67.5
95°	67.5
97.5°	67.5
100°	67.5
102.5°	67.5
105°	67.5
107.5°	67.5
110°	67.5

TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	64.1
115°	64.1
117.5°	64.1
120°	60.7
122.5°	60.7
125°	57.3
127.5°	57.3
130°	54.0
132.5°	54.0
135°	50.6
137.5°	50.6
140°	47.2
142.5°	43.9
145°	43.9
147.5°	40.5
150°	37.1
152.5°	33.7
155°	30.4
157.5°	30.4
160°	27.0
162.5°	23.6
165°	20.2
167.5°	16.9
170°	13.5
172.5°	10.1
175°	3.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1245008

CATALOG NUMBER: PRLX-NIM-L-927-09L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.6	6.6	6.5	7.6	8.7	5.6	6.6	6.5	7.6	8.7
	3H	8.7	9.6	9.6	10.5	11.8	8.7	9.6	9.6	10.5	11.8
	4H	10.2	11.1	11.1	12.0	13.2	10.2	11.1	11.1	12.0	13.2
	6H	11.6	12.5	12.5	13.4	14.6	11.6	12.5	12.5	13.4	14.6
	8H	12.3	13.1	13.2	14.1	15.3	12.3	13.1	13.2	14.1	15.3
	12H	12.9	13.7	13.9	14.7	15.9	12.9	13.7	13.9	14.7	15.9
4H	2H	6.4	7.3	7.3	8.2	9.5	6.4	7.3	7.3	8.2	9.5
	3H	9.7	10.5	10.6	11.4	12.6	9.7	10.5	10.6	11.4	12.6
	4H	11.3	12.0	12.2	13.0	14.2	11.3	12.0	12.2	13.0	14.2
	6H	12.9	13.5	13.8	14.5	15.8	12.9	13.5	13.8	14.5	15.8
	8H	13.7	14.3	14.6	15.3	16.5	13.7	14.3	14.6	15.3	16.5
	12H	14.4	15.0	15.4	16.0	17.2	14.4	15.0	15.4	16.0	17.2
8H	4H	11.8	12.4	12.8	13.4	14.7	11.8	12.4	12.8	13.4	14.7
	6H	13.6	14.1	14.6	15.2	16.4	13.6	14.1	14.6	15.2	16.4
	8H	14.5	15.0	15.5	16.0	17.3	14.5	15.0	15.5	16.0	17.3
	12H	15.5	15.9	16.4	16.9	18.2	15.5	15.9	16.4	16.9	18.2
12H	4H	11.9	12.5	12.9	13.5	14.8	11.9	12.5	12.9	13.5	14.8
	6H	13.8	14.3	14.8	15.3	16.6	13.8	14.3	14.8	15.3	16.6
	8H	14.8	15.2	15.8	16.2	17.5	14.8	15.2	15.8	16.2	17.5

(END OF REPORT)