

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979822

Luminaire Tested: PRLX-241-940-12L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-940-12L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 570.5 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979822

CATALOG NUMBER: PRLX-241-940-12L-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979822

CATALOG NUMBER: PRLX-241-940-12L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86		
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64	63		
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58		
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54		
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50		
10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3798
5°	3735
10°	3634
15°	3542
20°	3496
25°	3448
30°	3387
35°	2978
40°	1322
45°	166
50°	38
55°	43
60°	43
65°	44
70°	36
75°	36
80°	36
85°	35

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 166 cd/sqm

TEST NUMBER: P979822

CATALOG NUMBER: PRLX-241-940-12L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	8.0
10°-20°	125.4	22.0
20°-30°	186.7	32.7
30°-40°	180.2	31.6
40°-50°	26.2	4.6
50°-60°	2.7	0.5
60°-70°	2.2	0.4
70°-80°	1.3	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.6	62.7
0°-40°	537.8	94.3
0°-60°	566.7	99.3
0°-90°	570.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	570.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	493	
5°	483	45
15°	444	125
25°	405	187
35°	316	180
45°	15	26
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P979822

CATALOG NUMBER: PRLX-241-940-12L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	492.7
2.5°	490.3
5°	482.7
7.5°	472.6
10°	464.2
12.5°	453.0
15°	443.8
17.5°	435.0
20°	426.2
22.5°	417.0
25°	405.4
27.5°	393.3
30°	380.5
32.5°	360.1
35°	316.4
37.5°	234.3
40°	131.4
42.5°	54.5
45°	15.2
47.5°	4.8
50°	3.2
52.5°	3.2
55°	3.2
57.5°	2.8
60°	2.8
62.5°	2.4
65°	2.4
67.5°	2.0
70°	1.6
72.5°	1.6
75°	1.2
77.5°	0.8
80°	0.8
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

TEST NUMBER: P979822

CATALOG NUMBER: PRLX-241-940-12L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT