

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245137

Luminaire Tested: PRLX-NIM-M-927-04L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-927-04L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL RIBS SHADE TEXTL
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 424.2 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245137
CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245137

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	56
1	95	89	83	78	88	82	77	73	70	66	63		58	55	53		48	46	44	38
2	85	76	68	62	78	70	63	58	60	54	50		50	45	42		40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41		43	39	35		35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35		39	34	30		32	28	25	21
5	65	52	43	37	60	49	41	35	42	35	30		35	30	26		29	25	22	18
6	60	47	39	32	56	44	36	30	38	31	27		32	27	23		27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24		30	25	21		25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22		28	23	19		23	19	16	14
9	49	37	29	24	46	34	27	22	30	24	20		26	21	18		22	18	15	13
10	47	34	27	22	43	32	25	21	28	22	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38189
5°	16741
10°	3232
15°	1063
20°	636
25°	500
30°	452
35°	416
40°	436
45°	411
50°	392
55°	419
60°	407
65°	438
70°	432
75°	429
80°	430
85°	434

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 441 cd/sqm



TEST NUMBER: P1245137

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	7.0
10°-20°	13.6	3.2
20°-30°	12.2	2.9
30°-40°	16.7	3.9
40°-50°	22.8	5.4
50°-60°	29.0	6.8
60°-70°	34.5	8.1
70°-80°	38.1	9.0
80°-90°	39.3	9.3
90°-100°	39.3	9.3
100°-110°	38.1	9.0
110°-120°	35.3	8.3
120°-130°	29.0	6.8
130°-140°	21.9	5.2
140°-150°	13.9	3.3
150°-160°	8.0	1.9
160°-170°	2.6	0.6
170°-180°	0.3	0.1
0°-30°	55.5	13.1
0°-40°	72.2	17.0
0°-60°	123.9	29.2
0°-90°	235.8	55.6
90°-120°	112.7	26.6
90°-150°	177.5	41.8
90°-180°	188.0	44.3
0°-180°	424.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	745	
5°	444	30
15°	42	14
25°	26	12
35°	26	17
45°	29	23
55°	33	29
65°	36	35
75°	36	38
85°	36	29
90°	36	20
95°	36	29
105°	36	38
115°	36	35
125°	33	29
135°	29	22
145°	23	14
155°	16	8
165°	10	3
175°	0	0
180°	0	

TEST NUMBER: P1245137

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	745.2
2.5°	748.5
5°	444.5
7.5°	156.9
10°	107.9
12.5°	62.1
15°	42.5
17.5°	32.7
20°	29.4
22.5°	26.1
25°	26.1
27.5°	26.1
30°	26.1
32.5°	26.1
35°	26.1
37.5°	26.1
40°	29.4
42.5°	29.4
45°	29.4
47.5°	29.4
50°	29.4
52.5°	32.7
55°	32.7
57.5°	32.7
60°	32.7
62.5°	32.7
65°	36.0
67.5°	36.0
70°	36.0
72.5°	36.0
75°	36.0
77.5°	36.0
80°	36.0
82.5°	36.0
85°	36.0
87.5°	36.0
90°	36.0
92.5°	36.0
95°	36.0
97.5°	36.0
100°	36.0
102.5°	36.0
105°	36.0
107.5°	36.0
110°	36.0

TEST NUMBER: P1245137

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	36.0
115°	36.0
117.5°	36.0
120°	32.7
122.5°	32.7
125°	32.7
127.5°	32.7
130°	29.4
132.5°	29.4
135°	29.4
137.5°	26.1
140°	26.1
142.5°	22.9
145°	22.9
147.5°	19.6
150°	19.6
152.5°	19.6
155°	16.3
157.5°	16.3
160°	13.1
162.5°	9.8
165°	9.8
167.5°	6.5
170°	6.5
172.5°	3.3
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245137

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.4	5.4	5.2	6.3	7.5	4.4	5.4	5.2	6.3	7.5
	3H	7.5	8.5	8.4	9.4	10.6	7.5	8.5	8.4	9.4	10.6
	4H	8.9	9.8	9.8	10.8	12.0	8.9	9.8	9.8	10.8	12.0
	6H	10.3	11.2	11.3	12.1	13.3	10.3	11.2	11.3	12.1	13.3
	8H	11.0	11.8	11.9	12.8	14.0	11.0	11.8	11.9	12.8	14.0
	12H	11.6	12.4	12.6	13.4	14.6	11.6	12.4	12.6	13.4	14.6
4H	2H	5.2	6.1	6.1	7.1	8.3	5.2	6.1	6.1	7.1	8.3
	3H	8.5	9.3	9.4	10.2	11.5	8.5	9.3	9.4	10.2	11.5
	4H	10.0	10.8	11.0	11.7	13.0	10.0	10.8	11.0	11.7	13.0
	6H	11.6	12.3	12.5	13.2	14.5	11.6	12.3	12.5	13.2	14.5
	8H	12.4	13.0	13.3	13.9	15.2	12.4	13.0	13.3	13.9	15.2
	12H	13.1	13.7	14.1	14.7	15.9	13.1	13.7	14.1	14.7	15.9
8H	4H	10.6	11.2	11.5	12.1	13.4	10.6	11.2	11.5	12.1	13.4
	6H	12.3	12.8	13.3	13.9	15.1	12.3	12.8	13.3	13.9	15.1
	8H	13.2	13.7	14.2	14.7	16.0	13.2	13.7	14.2	14.7	16.0
	12H	14.1	14.6	15.1	15.6	16.9	14.1	14.6	15.1	15.6	16.9
12H	4H	10.7	11.2	11.6	12.2	13.5	10.7	11.2	11.6	12.2	13.5
	6H	12.5	13.0	13.5	14.0	15.3	12.5	13.0	13.5	14.0	15.3
	8H	13.5	13.9	14.4	14.9	16.2	13.5	13.9	14.4	14.9	16.2

(END OF REPORT)