

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979870

Luminaire Tested: PRLX-241-940-LL6-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-940-LL6-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH CLEAR LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2457.2 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.05
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979870
CATALOG NUMBER: PRLX-241-940-LL6-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979870

CATALOG NUMBER: PRLX-241-940-LL6-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	108	103	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64
7	82	72	66	62	81	72	66	62	70	65	61	69	65	61	68	64	61	59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	57	55
9	74	64	58	54	73	63	57	53	62	57	53	61	57	53	61	56	53	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17818
5°	16991
10°	16182
15°	15815
20°	15710
25°	15601
30°	15438
35°	14516
40°	2233
45°	363
50°	172
55°	171
60°	196
65°	202
70°	178
75°	188
80°	142
85°	142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 363 cd/sqm

TEST NUMBER: P979870

CATALOG NUMBER: PRLX-241-940-LL6-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.5	8.4
10°-20°	560.7	22.8
20°-30°	844.9	34.4
30°-40°	770.6	31.4
40°-50°	45.3	1.8
50°-60°	11.6	0.5
60°-70°	10.4	0.4
70°-80°	6.1	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1611.1	65.6
0°-40°	2381.7	96.9
0°-60°	2438.6	99.2
0°-90°	2457.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2457.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2311	
5°	2196	205
15°	1982	561
25°	1834	845
35°	1542	771
45°	33	45
55°	13	12
65°	11	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P979870

CATALOG NUMBER: PRLX-241-940-LL6-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2311.3
2.5°	2281.2
5°	2195.6
7.5°	2117.9
10°	2067.2
12.5°	2021.2
15°	1981.6
17.5°	1948.3
20°	1915.0
22.5°	1883.3
25°	1834.1
27.5°	1781.8
30°	1734.3
32.5°	1678.8
35°	1542.4
37.5°	830.7
40°	221.9
42.5°	74.5
45°	33.3
47.5°	17.4
50°	14.3
52.5°	12.7
55°	12.7
57.5°	12.7
60°	12.7
62.5°	11.1
65°	11.1
67.5°	9.5
70°	7.9
72.5°	6.3
75°	6.3
77.5°	4.8
80°	3.2
82.5°	3.2
85°	1.6
87.5°	1.6
90°	0.0



TEST NUMBER: P979870
 CATALOG NUMBER: PRLX-241-940-LL6-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.18	0.00	0.00	0.00	0.00	0.18
	12H	0.00	0.00	0.00	0.00	0.30	0.00	0.00	0.00	0.00	0.30
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.37	0.00	0.00	0.00	0.00	0.37
	6H	0.00	0.01	0.02	0.46	0.94	0.00	0.01	0.02	0.46	0.94
	8H	0.00	0.26	0.31	0.72	1.19	0.00	0.26	0.31	0.72	1.19
	12H	0.02	0.39	0.51	0.88	1.35	0.02	0.39	0.51	0.88	1.35
8H	4H	0.00	0.00	0.00	0.09	0.57	0.00	0.00	0.00	0.09	0.57
	6H	0.00	0.27	0.44	0.77	1.26	0.00	0.27	0.44	0.77	1.26
	8H	0.34	0.64	0.87	1.16	1.66	0.34	0.64	0.87	1.16	1.66
	12H	0.62	0.88	1.15	1.38	1.96	0.62	0.88	1.15	1.38	1.96
12H	4H	0.00	0.00	0.00	0.06	0.54	0.00	0.00	0.00	0.06	0.54
	6H	0.00	0.28	0.52	0.81	1.30	0.00	0.28	0.52	0.81	1.30
	8H	0.46	0.72	0.99	1.22	1.80	0.46	0.72	0.99	1.22	1.80