

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245038

Luminaire Tested: PRLX-NIM-L-930-05L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-930-05L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, WOVEN OVAL SHADE TEXTURE LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 522.9 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245038
CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

Luminous Intensity Polar Plot





TEST NUMBER: P1245038

CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20								20		
RC	80					70						30								10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61	56
1	95	89	83	78		87	82	77	73		70	66	62		58	55	53		48	45	43	38
2	85	76	68	61		78	70	63	57		59	54	49		49	45	42		40	37	34	30
3	77	66	57	50		71	61	53	47		52	45	40		43	38	34		35	31	28	24
4	71	58	49	42		65	54	46	40		46	39	34		38	33	29		31	27	24	20
5	65	52	43	36		60	48	40	34		41	35	30		34	29	25		28	24	21	18
6	60	47	38	32		55	44	36	30		37	31	26		31	26	22		26	22	19	16
7	56	43	34	28		51	40	32	27		34	28	23		29	24	20		24	20	17	15
8	52	39	31	25		48	36	29	24		32	25	21		27	22	18		23	19	16	13
9	49	36	28	23		45	34	27	22		29	23	19		25	20	17		21	17	15	12
10	46	33	26	21		43	31	25	20		27	22	18		24	19	16		20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22895
5°	10367
10°	2469
15°	979
20°	621
25°	496
30°	425
35°	394
40°	396
45°	376
50°	382
55°	392
60°	404
65°	397
70°	414
75°	414
80°	417
85°	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 432 cd/sqm

TEST NUMBER: P1245038

CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.7	5.9
10°-20°	17.4	3.3
20°-30°	17.0	3.2
30°-40°	21.8	4.2
40°-50°	28.6	5.5
50°-60°	35.8	6.9
60°-70°	42.7	8.2
70°-80°	47.5	9.1
80°-90°	49.0	9.4
90°-100°	49.0	9.4
100°-110°	47.5	9.1
110°-120°	42.4	8.1
120°-130°	34.8	6.7
130°-140°	26.6	5.1
140°-150°	17.9	3.4
150°-160°	9.8	1.9
160°-170°	3.9	0.8
170°-180°	0.5	0.1
0°-30°	65.1	12.4
0°-40°	86.8	16.6
0°-60°	151.2	28.9
0°-90°	290.4	55.5
90°-120°	138.9	26.6
90°-150°	218.2	41.7
90°-180°	232.0	44.4
0°-180°	522.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	724	
5°	420	31
15°	56	17
25°	36	17
35°	34	22
45°	36	29
55°	40	36
65°	43	43
75°	45	48
85°	45	37
90°	45	25
95°	45	37
105°	45	48
115°	43	42
125°	38	35
135°	34	27
145°	29	18
155°	20	10
165°	14	4
175°	2	0
180°	0	

TEST NUMBER: P1245038

CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	723.7
2.5°	802.3
5°	420.3
7.5°	177.5
10°	121.4
12.5°	76.4
15°	56.2
17.5°	47.2
20°	40.5
22.5°	38.2
25°	36.0
27.5°	36.0
30°	33.7
32.5°	33.7
35°	33.7
37.5°	36.0
40°	36.0
42.5°	36.0
45°	36.0
47.5°	38.2
50°	38.2
52.5°	38.2
55°	40.5
57.5°	40.5
60°	42.7
62.5°	42.7
65°	42.7
67.5°	42.7
70°	44.9
72.5°	44.9
75°	44.9
77.5°	44.9
80°	44.9
82.5°	44.9
85°	44.9
87.5°	44.9
90°	44.9
92.5°	44.9
95°	44.9
97.5°	44.9
100°	44.9
102.5°	44.9
105°	44.9
107.5°	44.9
110°	44.9

TEST NUMBER: P1245038

CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	42.7
115°	42.7
117.5°	42.7
120°	40.5
122.5°	40.5
125°	38.2
127.5°	38.2
130°	36.0
132.5°	36.0
135°	33.7
137.5°	33.7
140°	31.5
142.5°	29.2
145°	29.2
147.5°	27.0
150°	24.7
152.5°	22.5
155°	20.2
157.5°	20.2
160°	18.0
162.5°	15.7
165°	13.5
167.5°	11.2
170°	9.0
172.5°	6.7
175°	2.2
177.5°	0.0
180°	0.0



TEST NUMBER: P1245038

CATALOG NUMBER: PRLX-NIM-L-930-05L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.2	5.2	5.1	6.2	7.3	4.2	5.2	5.1	6.2	7.3
	3H	7.3	8.2	8.2	9.1	10.3	7.3	8.2	8.2	9.1	10.3
	4H	8.8	9.7	9.7	10.6	11.8	8.8	9.7	9.7	10.6	11.8
	6H	10.2	11.0	11.1	12.0	13.2	10.2	11.0	11.1	12.0	13.2
	8H	10.9	11.7	11.8	12.6	13.9	10.9	11.7	11.8	12.6	13.9
	12H	11.5	12.3	12.5	13.3	14.5	11.5	12.3	12.5	13.3	14.5
4H	2H	5.0	5.9	5.9	6.8	8.0	5.0	5.9	5.9	6.8	8.0
	3H	8.3	9.0	9.2	10.0	11.2	8.3	9.0	9.2	10.0	11.2
	4H	9.9	10.6	10.8	11.6	12.8	9.9	10.6	10.8	11.6	12.8
	6H	11.5	12.1	12.4	13.1	14.3	11.5	12.1	12.4	13.1	14.3
	8H	12.2	12.9	13.2	13.8	15.1	12.2	12.9	13.2	13.8	15.1
	12H	13.0	13.6	14.0	14.6	15.8	13.0	13.6	14.0	14.6	15.8
8H	4H	10.4	11.0	11.3	12.0	13.3	10.4	11.0	11.3	12.0	13.3
	6H	12.2	12.7	13.2	13.7	15.0	12.2	12.7	13.2	13.7	15.0
	8H	13.1	13.6	14.1	14.6	15.9	13.1	13.6	14.1	14.6	15.9
	12H	14.0	14.5	15.0	15.5	16.8	14.0	14.5	15.0	15.5	16.8
12H	4H	10.5	11.1	11.5	12.1	13.3	10.5	11.1	11.5	12.1	13.3
	6H	12.4	12.9	13.4	13.9	15.2	12.4	12.9	13.4	13.9	15.2
	8H	13.4	13.8	14.3	14.8	16.1	13.4	13.8	14.3	14.8	16.1

(END OF REPORT)