

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245057

Luminaire Tested: PRLX-NIM-L-930-23L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-930-23L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE
LIGHT LEVEL 7
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2341.1 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245057
CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245057

CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	78	87	82	77	73	70	66	62	58	55	53	48	45	43	38
2	85	76	68	61	78	70	63	57	59	54	49	49	45	42	40	37	34	30
3	77	66	57	50	71	61	53	47	52	45	40	43	38	34	35	31	28	24
4	71	58	49	42	65	54	46	40	46	39	34	38	33	29	31	27	24	20
5	65	52	43	36	60	48	40	34	41	35	30	34	29	25	28	24	21	18
6	60	47	38	32	55	44	36	30	37	31	26	31	26	22	26	22	19	16
7	56	43	34	28	51	40	32	27	34	28	23	29	24	20	24	20	17	15
8	52	39	31	25	48	36	29	24	32	25	21	27	22	18	23	19	16	13
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12
10	46	33	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102476
5°	46399
10°	11048
15°	4380
20°	2776
25°	2219
30°	1903
35°	1766
40°	1770
45°	1681
50°	1712
55°	1755
60°	1807
65°	1778
70°	1856
75°	1854
80°	1867
85°	1894

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 1937 cd/sqm

TEST NUMBER: P1245057

CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	5.9
10°-20°	78.0	3.3
20°-30°	75.9	3.2
30°-40°	97.3	4.2
40°-50°	127.7	5.5
50°-60°	160.4	6.9
60°-70°	191.0	8.2
70°-80°	212.9	9.1
80°-90°	219.5	9.4
90°-100°	219.5	9.4
100°-110°	212.9	9.1
110°-120°	189.8	8.1
120°-130°	155.9	6.7
130°-140°	119.0	5.1
140°-150°	80.1	3.4
150°-160°	44.0	1.9
160°-170°	17.7	0.8
170°-180°	2.2	0.1
0°-30°	291.3	12.4
0°-40°	388.6	16.6
0°-60°	676.7	28.9
0°-90°	1300.1	55.5
90°-120°	622.2	26.6
90°-150°	977.2	41.7
90°-180°	1041.0	44.5
0°-180°	2341.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3239	
5°	1881	137
15°	252	78
25°	161	76
35°	151	97
45°	161	128
55°	181	160
65°	191	191
75°	201	213
85°	201	164
90°	201	110
95°	201	164
105°	201	213
115°	191	190
125°	171	156
135°	151	119
145°	131	80
155°	90	44
165°	60	18
175°	10	2
180°	0	

TEST NUMBER: P1245057

CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	3239.2
2.5°	3591.3
5°	1881.1
7.5°	794.7
10°	543.2
12.5°	342.0
15°	251.5
17.5°	211.3
20°	181.1
22.5°	171.0
25°	161.0
27.5°	161.0
30°	150.9
32.5°	150.9
35°	150.9
37.5°	161.0
40°	161.0
42.5°	161.0
45°	161.0
47.5°	171.0
50°	171.0
52.5°	171.0
55°	181.1
57.5°	181.1
60°	191.1
62.5°	191.1
65°	191.1
67.5°	191.1
70°	201.2
72.5°	201.2
75°	201.2
77.5°	201.2
80°	201.2
82.5°	201.2
85°	201.2
87.5°	201.2
90°	201.2
92.5°	201.2
95°	201.2
97.5°	201.2
100°	201.2
102.5°	201.2
105°	201.2
107.5°	201.2
110°	201.2

TEST NUMBER: P1245057

CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	191.1
115°	191.1
117.5°	191.1
120°	181.1
122.5°	181.1
125°	171.0
127.5°	171.0
130°	161.0
132.5°	161.0
135°	150.9
137.5°	150.9
140°	140.8
142.5°	130.8
145°	130.8
147.5°	120.7
150°	110.7
152.5°	100.6
155°	90.5
157.5°	90.5
160°	80.5
162.5°	70.4
165°	60.4
167.5°	50.3
170°	40.2
172.5°	30.2
175°	10.1
177.5°	0.0
180°	0.0



TEST NUMBER: P1245057

CATALOG NUMBER: PRLX-NIM-L-930-23L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.4	10.4	10.3	11.4	12.5	9.4	10.4	10.3	11.4	12.5
	3H	12.5	13.4	13.4	14.3	15.5	12.5	13.4	13.4	14.3	15.5
	4H	14.0	14.9	14.9	15.8	17.0	14.0	14.9	14.9	15.8	17.0
	6H	15.4	16.2	16.3	17.2	18.4	15.4	16.2	16.3	17.2	18.4
	8H	16.1	16.9	17.0	17.9	19.1	16.1	16.9	17.0	17.9	19.1
	12H	16.7	17.5	17.7	18.5	19.7	16.7	17.5	17.7	18.5	19.7
4H	2H	10.2	11.1	11.1	12.0	13.2	10.2	11.1	11.1	12.0	13.2
	3H	13.5	14.2	14.4	15.2	16.4	13.5	14.2	14.4	15.2	16.4
	4H	15.1	15.8	16.0	16.8	18.0	15.1	15.8	16.0	16.8	18.0
	6H	16.7	17.3	17.6	18.3	19.6	16.7	17.3	17.6	18.3	19.6
	8H	17.4	18.1	18.4	19.0	20.3	17.4	18.1	18.4	19.0	20.3
	12H	18.2	18.8	19.2	19.8	21.0	18.2	18.8	19.2	19.8	21.0
8H	4H	15.6	16.2	16.6	17.2	18.5	15.6	16.2	16.6	17.2	18.5
	6H	17.4	17.9	18.4	18.9	20.2	17.4	17.9	18.4	18.9	20.2
	8H	18.3	18.8	19.3	19.8	21.1	18.3	18.8	19.3	19.8	21.1
	12H	19.3	19.7	20.2	20.7	22.0	19.3	19.7	20.2	20.7	22.0
12H	4H	15.7	16.3	16.7	17.3	18.5	15.7	16.3	16.7	17.3	18.5
	6H	17.6	18.1	18.6	19.1	20.4	17.6	18.1	18.6	19.1	20.4
	8H	18.6	19.0	19.6	20.0	21.3	18.6	19.0	19.6	20.0	21.3

(END OF REPORT)