

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245148

Luminaire Tested: PRLX-NIM-M-930-01L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-930-01L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL LINES SHADE TEXT LIGHT LEVEL 1
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 136.9 lumens
Efficiency: N/A
Efficacy: 21.7 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 6.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	78	88	82	77	73	70	66	63	58	55	53	48	46	44	38
2	85	76	68	62	78	70	63	58	60	54	50	50	46	42	40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41	43	39	35	35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35	39	34	30	32	28	25	21
5	65	52	43	37	60	49	41	35	42	35	30	35	30	26	29	25	22	18
6	60	47	39	32	56	44	36	30	38	32	27	32	27	23	27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24	30	25	21	25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	17	14
9	49	37	29	24	46	34	27	22	30	24	20	26	21	18	22	18	15	13
10	47	34	27	22	43	32	25	21	28	22	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12340
5°	5408
10°	1045
15°	343
20°	205
25°	161
30°	146
35°	134
40°	141
45°	133
50°	127
55°	136
60°	132
65°	141
70°	139
75°	138
80°	138
85°	140

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 142 cd/sqm



TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.6	7.0
10°-20°	4.4	3.2
20°-30°	3.9	2.9
30°-40°	5.4	3.9
40°-50°	7.4	5.4
50°-60°	9.4	6.9
60°-70°	11.2	8.1
70°-80°	12.3	9.0
80°-90°	12.7	9.2
90°-100°	12.7	9.2
100°-110°	12.3	9.0
110°-120°	11.4	8.3
120°-130°	9.4	6.9
130°-140°	7.1	5.2
140°-150°	4.5	3.3
150°-160°	2.6	1.9
160°-170°	0.9	0.6
170°-180°	0.1	0.1
0°-30°	17.9	13.1
0°-40°	23.3	17.0
0°-60°	40.0	29.2
0°-90°	76.1	55.6
90°-120°	36.3	26.5
90°-150°	57.3	41.8
90°-180°	61.0	44.6
0°-180°	136.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	241	
5°	144	10
15°	14	4
25°	8	4
35°	8	5
45°	10	7
55°	11	9
65°	12	11
75°	12	12
85°	12	9
90°	12	6
95°	12	9
105°	12	12
115°	12	11
125°	11	9
135°	10	7
145°	7	4
155°	5	3
165°	3	1
175°	0	0
180°	0	

TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.8
2.5°	241.8
5°	143.6
7.5°	50.7
10°	34.9
12.5°	20.1
15°	13.7
17.5°	10.6
20°	9.5
22.5°	8.4
25°	8.4
27.5°	8.4
30°	8.4
32.5°	8.4
35°	8.4
37.5°	8.4
40°	9.5
42.5°	9.5
45°	9.5
47.5°	9.5
50°	9.5
52.5°	10.6
55°	10.6
57.5°	10.6
60°	10.6
62.5°	10.6
65°	11.6
67.5°	11.6
70°	11.6
72.5°	11.6
75°	11.6
77.5°	11.6
80°	11.6
82.5°	11.6
85°	11.6
87.5°	11.6
90°	11.6
92.5°	11.6
95°	11.6
97.5°	11.6
100°	11.6
102.5°	11.6
105°	11.6
107.5°	11.6
110°	11.6

TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	11.6
115°	11.6
117.5°	11.6
120°	10.6
122.5°	10.6
125°	10.6
127.5°	10.6
130°	9.5
132.5°	9.5
135°	9.5
137.5°	8.4
140°	8.4
142.5°	7.4
145°	7.4
147.5°	6.3
150°	6.3
152.5°	6.3
155°	5.3
157.5°	5.3
160°	4.2
162.5°	3.2
165°	3.2
167.5°	2.1
170°	2.1
172.5°	1.1
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245148

CATALOG NUMBER: PRLX-NIM-M-930-01L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.5	1.5	1.3	2.4	3.6	0.5	1.5	1.3	2.4	3.6
	3H	3.6	4.5	4.5	5.5	6.7	3.6	4.5	4.5	5.5	6.7
	4H	5.0	5.9	5.9	6.8	8.1	5.0	5.9	5.9	6.8	8.1
	6H	6.4	7.2	7.3	8.2	9.4	6.4	7.2	7.3	8.2	9.4
	8H	7.1	7.9	8.0	8.8	10.1	7.1	7.9	8.0	8.8	10.1
	12H	7.7	8.5	8.6	9.4	10.7	7.7	8.5	8.6	9.4	10.7
4H	2H	1.3	2.2	2.2	3.1	4.4	1.3	2.2	2.2	3.1	4.4
	3H	4.5	5.3	5.5	6.3	7.5	4.5	5.3	5.5	6.3	7.5
	4H	6.1	6.8	7.0	7.8	9.1	6.1	6.8	7.0	7.8	9.1
	6H	7.7	8.3	8.6	9.3	10.5	7.7	8.3	8.6	9.3	10.5
	8H	8.4	9.0	9.4	10.0	11.3	8.4	9.0	9.4	10.0	11.3
	12H	9.2	9.7	10.1	10.7	12.0	9.2	9.7	10.1	10.7	12.0
8H	4H	6.6	7.2	7.6	8.2	9.5	6.6	7.2	7.6	8.2	9.5
	6H	8.4	8.9	9.3	9.9	11.2	8.4	8.9	9.3	9.9	11.2
	8H	9.3	9.8	10.2	10.8	12.0	9.3	9.8	10.2	10.8	12.0
	12H	10.2	10.6	11.2	11.6	12.9	10.2	10.6	11.2	11.6	12.9
12H	4H	6.7	7.3	7.7	8.3	9.5	6.7	7.3	7.7	8.3	9.5
	6H	8.6	9.0	9.5	10.0	11.3	8.6	9.0	9.5	10.0	11.3
	8H	9.5	10.0	10.5	11.0	12.3	9.5	10.0	10.5	11.0	12.3

(END OF REPORT)