

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979900

Luminaire Tested: PRLX-242-927-LL1-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-26)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-927-LL1-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1178.7 lumens
Efficiency: N/A
Efficacy: 157.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.39
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979900
CATALOG NUMBER: PRLX-242-927-LL1-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979900

CATALOG NUMBER: PRLX-242-927-LL1-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																												
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																												
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65																												
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																												
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49																												
6	73	61	52	46	71	60	52	46	58	51	46	56	50	45	55	49	45	43																												
7	68	55	47	41	66	54	46	41	53	46	40	51	45	40	50	44	40	38																												
8	63	50	42	36	62	49	42	36	48	41	36	47	41	36	46	40	36	34																												
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30																												
10	55	42	35	30	54	42	35	30	41	34	29	40	34	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2105
5°	2107
10°	2104
15°	2078
20°	2065
25°	2056
30°	2046
35°	2046
40°	2049
45°	2046
50°	2043
55°	2008
60°	1881
65°	878
70°	296
75°	92
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2046 cd/sqm

TEST NUMBER: P979900

CATALOG NUMBER: PRLX-242-927-LL1-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	3.8
10°-20°	126.8	10.8
20°-30°	191.9	16.3
30°-40°	234.5	19.9
40°-50°	249.5	21.2
50°-60°	229.0	19.4
60°-70°	94.0	8.0
70°-80°	8.5	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.3	30.8
0°-40°	597.8	50.7
0°-60°	1076.3	91.3
0°-90°	1178.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1178.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	470	
5°	469	45
15°	448	127
25°	416	192
35°	374	235
45°	323	249
55°	257	229
65°	83	94
75°	5	8
85°	0	0
90°	0	

TEST NUMBER: P979900

CATALOG NUMBER: PRLX-242-927-LL1-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	470.4
2.5°	470.0
5°	469.0
7.5°	466.8
10°	463.0
12.5°	457.7
15°	448.5
17.5°	441.1
20°	433.7
22.5°	425.2
25°	416.4
27.5°	406.2
30°	396.0
32.5°	385.7
35°	374.5
37.5°	363.2
40°	350.8
42.5°	337.4
45°	323.3
47.5°	308.9
50°	293.4
52.5°	276.1
55°	257.4
57.5°	238.7
60°	210.2
62.5°	151.6
65°	82.9
67.5°	33.1
70°	22.6
72.5°	15.5
75°	5.3
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

TEST NUMBER: P979900
 CATALOG NUMBER: PRLX-242-927-LL1-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.38	16.91	15.74	17.23	17.54	15.38	16.91	15.74	17.23	17.54
	3H	15.36	16.72	15.74	17.05	17.41	15.36	16.72	15.74	17.05	17.41
	4H	15.31	16.58	15.71	16.93	17.31	15.31	16.58	15.71	16.93	17.31
	6H	15.25	16.42	15.66	16.78	17.18	15.25	16.42	15.66	16.78	17.18
	8H	15.21	16.32	15.64	16.71	17.11	15.21	16.32	15.64	16.71	17.11
	12H	15.18	16.24	15.61	16.62	17.05	15.18	16.24	15.61	16.62	17.05
4H	2H	15.43	16.70	15.83	17.05	17.43	15.43	16.70	15.83	17.05	17.43
	3H	15.44	16.48	15.86	16.88	17.28	15.44	16.48	15.86	16.88	17.28
	4H	15.39	16.31	15.82	16.72	17.16	15.39	16.31	15.82	16.72	17.16
	6H	15.32	16.12	15.78	16.56	17.02	15.32	16.12	15.78	16.56	17.02
	8H	15.28	16.02	15.74	16.46	16.93	15.28	16.02	15.74	16.46	16.93
	12H	15.24	15.90	15.73	16.38	16.85	15.24	15.90	15.73	16.38	16.85
8H	4H	15.29	16.03	15.75	16.47	16.94	15.29	16.03	15.75	16.47	16.94
	6H	15.20	15.81	15.70	16.30	16.78	15.20	15.81	15.70	16.30	16.78
	8H	15.15	15.69	15.66	16.20	16.69	15.15	15.69	15.66	16.20	16.69
	12H	15.11	15.59	15.62	16.09	16.65	15.11	15.59	15.62	16.09	16.65
12H	4H	15.25	15.91	15.73	16.39	16.86	15.25	15.91	15.73	16.39	16.86
	6H	15.15	15.69	15.66	16.20	16.69	15.15	15.69	15.66	16.20	16.69
	8H	15.11	15.59	15.62	16.09	16.65	15.11	15.59	15.62	16.09	16.65