

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245153

Luminaire Tested: PRLX-NIM-M-930-03L-U-NR

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1245153  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-NIM-M-930-03L-U-NR  
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL RIBS SHADE TEXTL  
LIGHT LEVEL 2  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 308.9 lumens  
Efficiency: N/A  
Efficacy: 27.8 lumens/watt  
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18  
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')  
CIE Type: General Diffuse  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1245153  
CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

### Luminous Intensity Polar Plot





TEST NUMBER: P1245153

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	56
1	95	89	83	78	88	82	77	73	70	66	63		58	55	53		48	46	44	38
2	85	76	68	62	78	70	63	58	60	54	50		50	46	42		40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41		43	39	35		35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35		39	34	30		32	28	25	21
5	65	52	43	37	60	49	41	35	42	35	30		35	30	26		29	25	22	18
6	60	47	39	32	56	44	36	30	38	32	27		32	27	23		27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24		30	25	21		25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22		28	23	19		23	19	17	14
9	49	37	29	24	46	34	27	22	30	24	20		26	21	18		22	18	15	13
10	47	34	27	22	43	32	25	21	28	22	19		24	20	17		21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27832
5°	12203
10°	2354
15°	776
20°	463
25°	366
30°	331
35°	304
40°	317
45°	299
50°	285
55°	305
60°	296
65°	319
70°	314
75°	312
80°	313
85°	316

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 90°  
 Luminance: 321 cd/sqm

TEST NUMBER: P1245153

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.6	7.0
10°-20°	9.9	3.2
20°-30°	9.0	2.9
30°-40°	12.2	3.9
40°-50°	16.6	5.4
50°-60°	21.1	6.8
60°-70°	25.1	8.1
70°-80°	27.7	9.0
80°-90°	28.6	9.3
90°-100°	28.6	9.3
100°-110°	27.7	9.0
110°-120°	25.7	8.3
120°-130°	21.1	6.8
130°-140°	15.9	5.2
140°-150°	10.2	3.3
150°-160°	5.9	1.9
160°-170°	1.9	0.6
170°-180°	0.2	0.1
0°-30°	40.5	13.1
0°-40°	52.7	17.0
0°-60°	90.3	29.2
0°-90°	171.8	55.6
90°-120°	82.0	26.5
90°-150°	129.2	41.8
90°-180°	137.0	44.3
0°-180°	308.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	543	
5°	324	22
15°	31	10
25°	19	9
35°	19	12
45°	21	17
55°	24	21
65°	26	25
75°	26	28
85°	26	21
90°	26	14
95°	26	21
105°	26	28
115°	26	26
125°	24	21
135°	21	16
145°	17	10
155°	12	6
165°	7	2
175°	0	0
180°	0	

TEST NUMBER: P1245153

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	543.1
2.5°	545.5
5°	324.0
7.5°	114.3
10°	78.6
12.5°	45.3
15°	31.0
17.5°	23.8
20°	21.4
22.5°	19.1
25°	19.1
27.5°	19.1
30°	19.1
32.5°	19.1
35°	19.1
37.5°	19.1
40°	21.4
42.5°	21.4
45°	21.4
47.5°	21.4
50°	21.4
52.5°	23.8
55°	23.8
57.5°	23.8
60°	23.8
62.5°	23.8
65°	26.2
67.5°	26.2
70°	26.2
72.5°	26.2
75°	26.2
77.5°	26.2
80°	26.2
82.5°	26.2
85°	26.2
87.5°	26.2
90°	26.2
92.5°	26.2
95°	26.2
97.5°	26.2
100°	26.2
102.5°	26.2
105°	26.2
107.5°	26.2
110°	26.2

TEST NUMBER: P1245153

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	26.2
115°	26.2
117.5°	26.2
120°	23.8
122.5°	23.8
125°	23.8
127.5°	23.8
130°	21.4
132.5°	21.4
135°	21.4
137.5°	19.1
140°	19.1
142.5°	16.7
145°	16.7
147.5°	14.3
150°	14.3
152.5°	14.3
155°	11.9
157.5°	11.9
160°	9.5
162.5°	7.1
165°	7.1
167.5°	4.8
170°	4.8
172.5°	2.4
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245153

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-NR

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.3	4.3	4.1	5.2	6.4	3.3	4.3	4.1	5.2	6.4
	3H	6.4	7.3	7.3	8.3	9.5	6.4	7.3	7.3	8.3	9.5
	4H	7.8	8.7	8.7	9.7	10.9	7.8	8.7	8.7	9.7	10.9
	6H	9.2	10.1	10.1	11.0	12.2	9.2	10.1	10.1	11.0	12.2
	8H	9.9	10.7	10.8	11.7	12.9	9.9	10.7	10.8	11.7	12.9
	12H	10.5	11.3	11.5	12.3	13.5	10.5	11.3	11.5	12.3	13.5
4H	2H	4.1	5.0	5.0	5.9	7.2	4.1	5.0	5.0	5.9	7.2
	3H	7.4	8.2	8.3	9.1	10.3	7.4	8.2	8.3	9.1	10.3
	4H	8.9	9.7	9.9	10.6	11.9	8.9	9.7	9.9	10.6	11.9
	6H	10.5	11.1	11.4	12.1	13.4	10.5	11.1	11.4	12.1	13.4
	8H	11.2	11.9	12.2	12.8	14.1	11.2	11.9	12.2	12.8	14.1
	12H	12.0	12.6	13.0	13.6	14.8	12.0	12.6	13.0	13.6	14.8
8H	4H	9.4	10.1	10.4	11.0	12.3	9.4	10.1	10.4	11.0	12.3
	6H	11.2	11.7	12.2	12.7	14.0	11.2	11.7	12.2	12.7	14.0
	8H	12.1	12.6	13.1	13.6	14.9	12.1	12.6	13.1	13.6	14.9
	12H	13.0	13.5	14.0	14.5	15.8	13.0	13.5	14.0	14.5	15.8
12H	4H	9.5	10.1	10.5	11.1	12.4	9.5	10.1	10.5	11.1	12.4
	6H	11.4	11.9	12.4	12.9	14.2	11.4	11.9	12.4	12.9	14.2
	8H	12.4	12.8	13.3	13.8	15.1	12.4	12.8	13.3	13.8	15.1

(END OF REPORT)