

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245154

Luminaire Tested: PRLX-NIM-M-930-03L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-930-03L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, WOVEN OVAL SHADE TEXTU LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 298.3 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245154
CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

Luminous Intensity Polar Plot





TEST NUMBER: P1245154

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	56
1	95	89	83	78	88	82	77	73	70	66	63		58	55	53		48	46	44	38
2	85	76	68	62	78	70	63	58	60	54	50		50	46	42		40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41		43	39	35		35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35		39	34	30		32	28	25	21
5	65	52	43	37	60	49	41	35	42	35	30		35	30	26		29	25	22	18
6	60	47	39	32	56	44	36	30	38	31	27		32	27	23		27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24		30	25	21		25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22		28	23	19		23	19	16	14
9	49	37	29	24	46	34	27	22	30	24	20		26	21	18		22	18	15	13
10	47	34	27	22	43	32	25	21	28	22	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26843
5°	11766
10°	2270
15°	748
20°	448
25°	353
30°	319
35°	293
40°	307
45°	289
50°	276
55°	295
60°	286
65°	308
70°	304
75°	302
80°	302
85°	305

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 310 cd/sqm

TEST NUMBER: P1245154

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.8	7.0
10°-20°	9.5	3.2
20°-30°	8.6	2.9
30°-40°	11.8	3.9
40°-50°	16.0	5.4
50°-60°	20.4	6.8
60°-70°	24.3	8.1
70°-80°	26.8	9.0
80°-90°	27.6	9.3
90°-100°	27.6	9.3
100°-110°	26.8	9.0
110°-120°	24.8	8.3
120°-130°	20.4	6.8
130°-140°	15.4	5.2
140°-150°	9.8	3.3
150°-160°	5.7	1.9
160°-170°	1.9	0.6
170°-180°	0.2	0.1
0°-30°	39.0	13.1
0°-40°	50.8	17.0
0°-60°	87.2	29.2
0°-90°	165.8	55.6
90°-120°	79.2	26.5
90°-150°	124.8	41.8
90°-180°	132.0	44.2
0°-180°	298.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	524	
5°	312	21
15°	30	10
25°	18	9
35°	18	12
45°	21	16
55°	23	20
65°	25	24
75°	25	27
85°	25	21
90°	25	14
95°	25	21
105°	25	27
115°	25	25
125°	23	20
135°	21	15
145°	16	10
155°	12	6
165°	7	2
175°	0	0
180°	0	

TEST NUMBER: P1245154

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	523.8
2.5°	526.1
5°	312.4
7.5°	110.3
10°	75.8
12.5°	43.6
15°	29.9
17.5°	23.0
20°	20.7
22.5°	18.4
25°	18.4
27.5°	18.4
30°	18.4
32.5°	18.4
35°	18.4
37.5°	18.4
40°	20.7
42.5°	20.7
45°	20.7
47.5°	20.7
50°	20.7
52.5°	23.0
55°	23.0
57.5°	23.0
60°	23.0
62.5°	23.0
65°	25.3
67.5°	25.3
70°	25.3
72.5°	25.3
75°	25.3
77.5°	25.3
80°	25.3
82.5°	25.3
85°	25.3
87.5°	25.3
90°	25.3
92.5°	25.3
95°	25.3
97.5°	25.3
100°	25.3
102.5°	25.3
105°	25.3
107.5°	25.3
110°	25.3



TEST NUMBER: P1245154

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	25.3
115°	25.3
117.5°	25.3
120°	23.0
122.5°	23.0
125°	23.0
127.5°	23.0
130°	20.7
132.5°	20.7
135°	20.7
137.5°	18.4
140°	18.4
142.5°	16.1
145°	16.1
147.5°	13.8
150°	13.8
152.5°	13.8
155°	11.5
157.5°	11.5
160°	9.2
162.5°	6.9
165°	6.9
167.5°	4.6
170°	4.6
172.5°	2.3
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245154

CATALOG NUMBER: PRLX-NIM-M-930-03L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.1	4.2	4.0	5.1	6.3	3.1	4.2	4.0	5.1	6.3
	3H	6.3	7.2	7.2	8.2	9.4	6.3	7.2	7.2	8.2	9.4
	4H	7.7	8.6	8.6	9.6	10.8	7.7	8.6	8.6	9.6	10.8
	6H	9.1	10.0	10.0	10.9	12.1	9.1	10.0	10.0	10.9	12.1
	8H	9.8	10.6	10.7	11.5	12.8	9.8	10.6	10.7	11.5	12.8
	12H	10.4	11.2	11.4	12.2	13.4	10.4	11.2	11.4	12.2	13.4
4H	2H	4.0	4.9	4.9	5.8	7.0	4.0	4.9	4.9	5.8	7.0
	3H	7.3	8.0	8.2	9.0	10.2	7.3	8.0	8.2	9.0	10.2
	4H	8.8	9.6	9.7	10.5	11.8	8.8	9.6	9.7	10.5	11.8
	6H	10.4	11.0	11.3	12.0	13.3	10.4	11.0	11.3	12.0	13.3
	8H	11.1	11.7	12.1	12.7	14.0	11.1	11.7	12.1	12.7	14.0
	12H	11.9	12.4	12.8	13.4	14.7	11.9	12.4	12.8	13.4	14.7
8H	4H	9.3	9.9	10.3	10.9	12.2	9.3	9.9	10.3	10.9	12.2
	6H	11.1	11.6	12.0	12.6	13.9	11.1	11.6	12.0	12.6	13.9
	8H	12.0	12.5	13.0	13.5	14.7	12.0	12.5	13.0	13.5	14.7
	12H	12.9	13.3	13.9	14.3	15.7	12.9	13.3	13.9	14.3	15.7
12H	4H	9.4	10.0	10.4	11.0	12.3	9.4	10.0	10.4	11.0	12.3
	6H	11.3	11.7	12.2	12.7	14.0	11.3	11.7	12.2	12.7	14.0
	8H	12.2	12.7	13.2	13.7	15.0	12.2	12.7	13.2	13.7	15.0

(END OF REPORT)