

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979912

Luminaire Tested: PRLX-242-927-LL2-F-U-S-BLAK-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P979912  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-27)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-242-927-LL2-F-U-S-BLAK-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH FROSTED LENS  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1575.5 lumens  
Efficiency: N/A  
Efficacy: 143.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.33  
Luminous Opening: Circular (Dia: 1.75' x H: 0')  
CIE Type: Direct

Input Watts (W): 11  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P979912  
CATALOG NUMBER: PRLX-242-927-LL2-F-U-S-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P979912

CATALOG NUMBER: PRLX-242-927-LL2-F-U-S-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	100	93	86	81	98	91	85	80	87	83	78		84	80	77		81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57		67	61	56		64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49		60	53	48		58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43		54	48	43		53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38		49	43	38		48	42	37	36
8	62	48	40	34	60	48	40	34	46	39	34		45	39	34		44	38	34	32
9	58	44	36	31	56	44	36	31	43	36	31		42	35	31		41	35	30	29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2738
5°	2732
10°	2721
15°	2686
20°	2651
25°	2614
30°	2565
35°	2523
40°	2481
45°	2430
50°	2382
55°	2316
60°	2238
65°	2134
70°	1976
75°	775
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2430 cd/sqm

TEST NUMBER: P979912

CATALOG NUMBER: PRLX-242-927-LL2-F-U-S-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.8	3.7
10°-20°	163.6	10.4
20°-30°	243.7	15.5
30°-40°	288.8	18.3
40°-50°	296.3	18.8
50°-60°	265.2	16.8
60°-70°	198.9	12.6
70°-80°	61.2	3.9
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.0	29.5
0°-40°	753.8	47.8
0°-60°	1315.3	83.5
0°-90°	1575.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1575.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	612	
5°	608	58
15°	580	164
25°	529	244
35°	462	289
45°	384	296
55°	297	265
65°	202	199
75°	45	61
85°	0	0
90°	0	

TEST NUMBER: P979912

CATALOG NUMBER: PRLX-242-927-LL2-F-U-S-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	611.8
2.5°	611.3
5°	608.2
7.5°	604.1
10°	598.9
12.5°	590.7
15°	579.8
17.5°	568.5
20°	556.7
22.5°	543.8
25°	529.3
27.5°	513.4
30°	496.4
32.5°	478.8
35°	461.8
37.5°	443.3
40°	424.7
42.5°	404.1
45°	384.0
47.5°	363.4
50°	342.2
52.5°	319.6
55°	296.9
57.5°	273.2
60°	250.0
62.5°	225.8
65°	201.5
67.5°	176.3
70°	151.0
72.5°	111.8
75°	44.8
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

TEST NUMBER: P979912  
 CATALOG NUMBER: PRLX-242-927-LL2-F-U-S-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.25	16.85	15.62	17.16	17.47	15.25	16.85	15.62	17.16	17.47
	3H	17.00	18.43	17.38	18.76	19.12	17.00	18.43	17.38	18.76	19.12
	4H	17.20	18.54	17.60	18.89	19.27	17.20	18.54	17.60	18.89	19.27
	6H	17.14	18.38	17.55	18.74	19.13	17.14	18.38	17.55	18.74	19.13
	8H	17.11	18.29	17.53	18.67	19.07	17.11	18.29	17.53	18.67	19.07
	12H	17.08	18.21	17.51	18.59	19.02	17.08	18.21	17.51	18.59	19.02
4H	2H	15.89	17.23	16.29	17.58	17.95	15.89	17.23	16.29	17.58	17.95
	3H	17.80	18.91	18.21	19.31	19.71	17.80	18.91	18.21	19.31	19.71
	4H	17.99	18.98	18.42	19.40	19.83	17.99	18.98	18.42	19.40	19.83
	6H	17.94	18.80	18.39	19.24	19.70	17.94	18.80	18.39	19.24	19.70
	8H	17.90	18.70	18.36	19.14	19.61	17.90	18.70	18.36	19.14	19.61
	12H	17.87	18.58	18.35	19.06	19.53	17.87	18.58	18.35	19.06	19.53
8H	4H	18.02	18.82	18.49	19.27	19.73	18.02	18.82	18.49	19.27	19.73
	6H	17.95	18.61	18.45	19.10	19.58	17.95	18.61	18.45	19.10	19.58
	8H	17.91	18.49	18.42	19.00	19.49	17.91	18.49	18.42	19.00	19.49
	12H	17.89	18.40	18.40	18.89	19.45	17.89	18.40	18.40	18.89	19.45
12H	4H	18.00	18.71	18.48	19.19	19.66	18.00	18.71	18.48	19.19	19.66
	6H	17.91	18.49	18.42	19.00	19.49	17.91	18.49	18.42	19.00	19.49
	8H	17.89	18.40	18.40	18.89	19.45	17.89	18.40	18.40	18.89	19.45