

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979952

Luminaire Tested: PRLX-242-927-LL6-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-927-LL6-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4265.5 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.33
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979952
CATALOG NUMBER: PRLX-242-927-LL6-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979952

CATALOG NUMBER: PRLX-242-927-LL6-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86				86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73				73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62				62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53				53
5	77	65	56	50	75	64	56	50	62	55	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40				40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	36				36
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32				32
9	58	44	36	31	56	44	36	31	43	36	31	42	35	31	41	35	30	29				29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26				26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7413
5°	7397
10°	7369
15°	7273
20°	7177
25°	7077
30°	6944
35°	6831
40°	6718
45°	6580
50°	6451
55°	6271
60°	6058
65°	5777
70°	5350
75°	2099
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6580 cd/sqm

TEST NUMBER: P979952

CATALOG NUMBER: PRLX-242-927-LL6-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.4	3.7
10°-20°	442.8	10.4
20°-30°	659.8	15.5
30°-40°	781.9	18.3
40°-50°	802.3	18.8
50°-60°	717.9	16.8
60°-70°	538.5	12.6
70°-80°	165.9	3.9
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1259.0	29.5
0°-40°	2040.9	47.8
0°-60°	3561.1	83.5
0°-90°	4265.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4265.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1656	
5°	1647	156
15°	1570	443
25°	1433	660
35°	1250	782
45°	1040	802
55°	804	718
65°	546	539
75°	121	166
85°	0	0
90°	0	

TEST NUMBER: P979952

CATALOG NUMBER: PRLX-242-927-LL6-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1656.5
2.5°	1655.1
5°	1646.7
7.5°	1635.5
10°	1621.6
12.5°	1599.3
15°	1569.9
17.5°	1539.2
20°	1507.1
22.5°	1472.3
25°	1433.2
27.5°	1389.9
30°	1343.9
32.5°	1296.4
35°	1250.4
37.5°	1200.1
40°	1149.9
42.5°	1094.1
45°	1039.7
47.5°	983.8
50°	926.6
52.5°	865.2
55°	803.8
57.5°	739.6
60°	676.8
62.5°	611.2
65°	545.6
67.5°	477.3
70°	408.9
72.5°	302.8
75°	121.4
77.5°	5.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P979952
 CATALOG NUMBER: PRLX-242-927-LL6-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.71	20.31	19.08	20.62	20.93	18.71	20.31	19.08	20.62	20.93
	3H	20.46	21.89	20.84	22.22	22.58	20.46	21.89	20.84	22.22	22.58
	4H	20.66	22.00	21.06	22.35	22.73	20.66	22.00	21.06	22.35	22.73
	6H	20.60	21.84	21.01	22.20	22.59	20.60	21.84	21.01	22.20	22.59
	8H	20.57	21.75	20.99	22.14	22.54	20.57	21.75	20.99	22.14	22.54
	12H	20.54	21.67	20.97	22.05	22.48	20.54	21.67	20.97	22.05	22.48
4H	2H	19.35	20.69	19.75	21.04	21.41	19.35	20.69	19.75	21.04	21.41
	3H	21.26	22.37	21.67	22.77	23.17	21.26	22.37	21.67	22.77	23.17
	4H	21.45	22.44	21.88	22.86	23.29	21.45	22.44	21.88	22.86	23.29
	6H	21.40	22.26	21.85	22.70	23.16	21.40	22.26	21.85	22.70	23.16
	8H	21.36	22.16	21.82	22.60	23.07	21.36	22.16	21.82	22.60	23.07
	12H	21.33	22.05	21.81	22.52	22.99	21.33	22.05	21.81	22.52	22.99
8H	4H	21.48	22.29	21.95	22.73	23.20	21.48	22.29	21.95	22.73	23.20
	6H	21.41	22.07	21.91	22.56	23.04	21.41	22.07	21.91	22.56	23.04
	8H	21.37	21.96	21.88	22.46	22.95	21.37	21.96	21.88	22.46	22.95
	12H	21.35	21.86	21.86	22.35	22.91	21.35	21.86	21.86	22.35	22.91
12H	4H	21.46	22.17	21.94	22.65	23.12	21.46	22.17	21.94	22.65	23.12
	6H	21.37	21.95	21.88	22.46	22.95	21.37	21.95	21.88	22.46	22.95
	8H	21.35	21.86	21.86	22.35	22.91	21.35	21.86	21.86	22.35	22.91