

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245232

Luminaire Tested: PRLX-NIM-S-930-05L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-S-930-05L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL LINES SHADE TEXTURE, LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245232
CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1245232

CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47		52	47	43		47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41		48	43	39		44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31		39	33	30		36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27		34	29	26		32	28	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12655
5°	12487
10°	10981
15°	2665
20°	2224
25°	1851
30°	1462
35°	1213
40°	1036
45°	937
50°	851
55°	784
60°	742
65°	687
70°	653
75°	622
80°	561
85°	535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 937 cd/sqm



TEST NUMBER: P1245232

CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	8.7
10°-20°	44.0	9.3
20°-30°	40.9	8.6
30°-40°	40.3	8.5
40°-50°	40.2	8.5
50°-60°	40.0	8.4
60°-70°	38.6	8.1
70°-80°	35.1	7.4
80°-90°	29.2	6.1
90°-100°	27.9	5.9
100°-110°	26.1	5.5
110°-120°	23.0	4.8
120°-130°	18.8	4.0
130°-140°	14.0	2.9
140°-150°	9.0	1.9
150°-160°	4.7	1.0
160°-170°	1.6	0.3
170°-180°	0.2	0.0
0°-30°	126.4	26.6
0°-40°	166.7	35.1
0°-60°	246.9	52.0
0°-90°	349.8	73.6
90°-120°	77.0	16.2
90°-150°	118.8	25.0
90°-180°	125.0	26.3
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	400	
5°	444	41
15°	114	44
25°	90	41
35°	64	40
45°	52	40
55°	44	40
65°	38	39
75°	33	35
85°	27	22
90°	26	14
95°	26	21
105°	25	26
115°	23	23
125°	21	19
135°	18	14
145°	15	9
155°	10	5
165°	5	2
175°	1	0
180°	0	

TEST NUMBER: P1245232

CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	400.0
2.5°	412.9
5°	444.5
7.5°	439.4
10°	431.7
12.5°	185.0
15°	113.9
17.5°	107.9
20°	101.9
22.5°	96.8
25°	89.9
27.5°	82.2
30°	74.5
32.5°	68.5
35°	64.2
37.5°	60.0
40°	56.5
42.5°	54.0
45°	52.2
47.5°	49.7
50°	48.0
52.5°	46.3
55°	44.5
57.5°	42.8
60°	42.0
62.5°	40.3
65°	38.5
67.5°	37.7
70°	36.0
72.5°	35.1
75°	33.4
77.5°	31.7
80°	29.1
82.5°	27.4
85°	26.6
87.5°	25.7
90°	25.7
92.5°	25.7
95°	25.7
97.5°	25.7
100°	24.8
102.5°	24.8
105°	24.8
107.5°	24.8
110°	24.0

TEST NUMBER: P1245232

CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	24.0
115°	23.1
117.5°	22.3
120°	22.3
122.5°	21.4
125°	20.6
127.5°	20.6
130°	19.7
132.5°	18.8
135°	18.0
137.5°	17.1
140°	16.3
142.5°	15.4
145°	14.6
147.5°	12.8
150°	12.0
152.5°	11.1
155°	10.3
157.5°	8.6
160°	7.7
162.5°	6.9
165°	5.1
167.5°	4.3
170°	3.4
172.5°	1.7
175°	0.9
177.5°	0.0
180°	0.0



TEST NUMBER: P1245232

CATALOG NUMBER: PRLX-NIM-S-930-05L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.7	8.8	8.4	9.6	10.5	7.7	8.8	8.4	9.6	10.5
	3H	10.0	11.1	10.7	11.8	12.7	10.0	11.1	10.7	11.8	12.7
	4H	11.1	12.1	11.8	12.8	13.8	11.1	12.1	11.8	12.8	13.8
	6H	12.1	13.0	12.8	13.8	14.7	12.1	13.0	12.8	13.8	14.7
	8H	12.5	13.4	13.2	14.2	15.1	12.5	13.4	13.2	14.2	15.1
	12H	12.9	13.7	13.7	14.5	15.5	12.9	13.7	13.7	14.5	15.5
4H	2H	8.3	9.3	9.0	10.0	11.0	8.3	9.3	9.0	10.0	11.0
	3H	10.8	11.7	11.6	12.5	13.4	10.8	11.7	11.6	12.5	13.4
	4H	12.0	12.8	12.8	13.6	14.6	12.0	12.8	12.8	13.6	14.6
	6H	13.2	13.9	14.0	14.7	15.7	13.2	13.9	14.0	14.7	15.7
	8H	13.7	14.3	14.5	15.2	16.1	13.7	14.3	14.5	15.2	16.1
	12H	14.2	14.8	15.0	15.6	16.6	14.2	14.8	15.0	15.6	16.6
8H	4H	12.4	13.1	13.2	13.9	14.9	12.4	13.1	13.2	13.9	14.9
	6H	13.7	14.3	14.6	15.2	16.1	13.7	14.3	14.6	15.2	16.1
	8H	14.4	14.9	15.2	15.7	16.7	14.4	14.9	15.2	15.7	16.7
	12H	15.0	15.5	15.9	16.3	17.4	15.0	15.5	15.9	16.3	17.4
12H	4H	12.5	13.1	13.3	13.9	14.9	12.5	13.1	13.3	13.9	14.9
	6H	13.9	14.4	14.7	15.2	16.2	13.9	14.4	14.7	15.2	16.2
	8H	14.6	15.0	15.4	15.9	16.9	14.6	15.0	15.4	15.9	16.9

(END OF REPORT)