

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245242

Luminaire Tested: PRLX-NIM-S-930-09L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-S-930-09L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, WOVEN OVAL SHADE TEXTURE LIGHT LEVEL 4
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 937.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

Luminous Intensity Polar Plot



TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47		52	47	43		47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41		48	43	39		44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31		39	33	30		36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27		34	29	26		32	28	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24964
5°	24634
10°	21662
15°	5258
20°	4389
25°	3653
30°	2886
35°	2394
40°	2045
45°	1852
50°	1677
55°	1549
60°	1462
65°	1355
70°	1288
75°	1227
80°	1106
85°	1054

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1852 cd/sqm

TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	8.7
10°-20°	86.8	9.3
20°-30°	80.8	8.6
30°-40°	79.6	8.5
40°-50°	79.3	8.5
50°-60°	78.9	8.4
60°-70°	76.0	8.1
70°-80°	69.2	7.4
80°-90°	57.6	6.1
90°-100°	55.1	5.9
100°-110°	51.6	5.5
110°-120°	45.3	4.8
120°-130°	37.0	3.9
130°-140°	27.6	2.9
140°-150°	17.7	1.9
150°-160°	9.2	1.0
160°-170°	3.2	0.3
170°-180°	0.3	0.0
0°-30°	249.4	26.6
0°-40°	328.9	35.1
0°-60°	487.2	52.0
0°-90°	690.0	73.6
90°-120°	152.0	16.2
90°-150°	234.3	25.0
90°-180°	247.0	26.4
0°-180°	937.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	789	
5°	877	82
15°	225	87
25°	177	81
35°	127	80
45°	103	79
55°	88	79
65°	76	76
75°	66	69
85°	52	44
90°	51	28
95°	51	41
105°	49	52
115°	46	45
125°	41	37
135°	36	28
145°	29	18
155°	20	9
165°	10	3
175°	2	0
180°	0	

TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	789.1
2.5°	814.4
5°	876.9
7.5°	866.8
10°	851.6
12.5°	365.0
15°	224.7
17.5°	212.9
20°	201.1
22.5°	190.9
25°	177.4
27.5°	162.2
30°	147.0
32.5°	135.2
35°	126.7
37.5°	118.3
40°	111.5
42.5°	106.4
45°	103.1
47.5°	98.0
50°	94.6
52.5°	91.2
55°	87.9
57.5°	84.5
60°	82.8
62.5°	79.4
65°	76.0
67.5°	74.3
70°	71.0
72.5°	69.3
75°	65.9
77.5°	62.5
80°	57.4
82.5°	54.1
85°	52.4
87.5°	50.7
90°	50.7
92.5°	50.7
95°	50.7
97.5°	50.7
100°	49.0
102.5°	49.0
105°	49.0
107.5°	49.0
110°	47.3

TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	47.3
115°	45.6
117.5°	43.9
120°	43.9
122.5°	42.2
125°	40.6
127.5°	40.6
130°	38.9
132.5°	37.2
135°	35.5
137.5°	33.8
140°	32.1
142.5°	30.4
145°	28.7
147.5°	25.3
150°	23.7
152.5°	22.0
155°	20.3
157.5°	16.9
160°	15.2
162.5°	13.5
165°	10.1
167.5°	8.4
170°	6.8
172.5°	3.4
175°	1.7
177.5°	0.0
180°	0.0



TEST NUMBER: P1245242

CATALOG NUMBER: PRLX-NIM-S-930-09L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.1	11.2	10.8	12.0	12.8	10.1	11.2	10.8	12.0	12.8
	3H	12.4	13.4	13.1	14.2	15.1	12.4	13.4	13.1	14.2	15.1
	4H	13.4	14.4	14.2	15.2	16.1	13.4	14.4	14.2	15.2	16.1
	6H	14.4	15.3	15.2	16.1	17.1	14.4	15.3	15.2	16.1	17.1
	8H	14.8	15.7	15.6	16.5	17.5	14.8	15.7	15.6	16.5	17.5
	12H	15.3	16.1	16.0	16.9	17.9	15.3	16.1	16.0	16.9	17.9
4H	2H	10.7	11.6	11.4	12.4	13.3	10.7	11.6	11.4	12.4	13.3
	3H	13.2	14.0	14.0	14.8	15.8	13.2	14.0	14.0	14.8	15.8
	4H	14.4	15.2	15.2	16.0	17.0	14.4	15.2	15.2	16.0	17.0
	6H	15.5	16.2	16.3	17.1	18.0	15.5	16.2	16.3	17.1	18.0
	8H	16.0	16.7	16.8	17.5	18.5	16.0	16.7	16.8	17.5	18.5
	12H	16.6	17.2	17.4	18.0	19.0	16.6	17.2	17.4	18.0	19.0
8H	4H	14.8	15.5	15.6	16.3	17.3	14.8	15.5	15.6	16.3	17.3
	6H	16.1	16.7	16.9	17.5	18.5	16.1	16.7	16.9	17.5	18.5
	8H	16.7	17.2	17.6	18.1	19.1	16.7	17.2	17.6	18.1	19.1
	12H	17.4	17.9	18.2	18.7	19.8	17.4	17.9	18.2	18.7	19.8
12H	4H	14.9	15.5	15.7	16.3	17.3	14.9	15.5	15.7	16.3	17.3
	6H	16.2	16.7	17.1	17.6	18.6	16.2	16.7	17.1	17.6	18.6
	8H	16.9	17.4	17.8	18.2	19.3	16.9	17.4	17.8	18.2	19.3

(END OF REPORT)