

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245070

Luminaire Tested: PRLX-NIM-L-935-05L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-935-05L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, WOVEN OVAL SHADE TEXTURE
LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.9 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

Luminous Intensity Polar Plot



TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20						20
RC	80					70					50					30						10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	
RCR																						
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61	
1	95	89	83	78		87	82	77	73		70	66	62		58	55	53		48	45	43	
2	85	76	68	61		78	70	63	57		59	54	49		49	45	42		40	37	34	
3	77	66	57	50		71	61	53	47		52	45	40		43	38	34		35	31	28	
4	71	58	49	42		65	54	46	40		46	39	34		38	33	29		31	27	24	
5	65	52	43	36		60	48	40	34		41	35	30		34	29	25		28	24	21	
6	60	47	38	32		55	44	36	30		37	31	26		31	26	22		26	22	19	
7	56	43	34	28		51	40	32	27		34	28	23		29	24	20		24	20	17	
8	52	39	31	25		48	36	29	24		32	25	21		27	22	18		23	19	16	
9	49	36	28	23		45	34	27	22		29	23	19		25	20	17		21	17	15	
10	46	33	26	21		43	31	25	20		27	22	18		24	19	16		20	16	14	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23639
5°	10703
10°	2549
15°	1010
20°	641
25°	511
30°	439
35°	407
40°	408
45°	387
50°	394
55°	405
60°	417
65°	410
70°	428
75°	428
80°	431
85°	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 447 cd/sqm

TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.7	5.9
10°-20°	18.0	3.3
20°-30°	17.5	3.2
30°-40°	22.4	4.2
40°-50°	29.4	5.5
50°-60°	37.0	6.9
60°-70°	44.1	8.2
70°-80°	49.1	9.1
80°-90°	50.6	9.4
90°-100°	50.6	9.4
100°-110°	49.1	9.1
110°-120°	43.8	8.1
120°-130°	35.9	6.7
130°-140°	27.4	5.1
140°-150°	18.5	3.4
150°-160°	10.2	1.9
160°-170°	4.1	0.8
170°-180°	0.5	0.1
0°-30°	67.2	12.4
0°-40°	89.6	16.6
0°-60°	156.0	28.9
0°-90°	299.8	55.5
90°-120°	143.5	26.6
90°-150°	225.4	41.7
90°-180°	240.0	44.5
0°-180°	539.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	747	
5°	434	32
15°	58	18
25°	37	17
35°	35	22
45°	37	29
55°	42	37
65°	44	44
75°	46	49
85°	46	38
90°	46	25
95°	46	38
105°	46	49
115°	44	44
125°	39	36
135°	35	27
145°	30	18
155°	21	10
165°	14	4
175°	2	0
180°	0	

TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	747.2
2.5°	828.4
5°	433.9
7.5°	183.3
10°	125.3
12.5°	78.9
15°	58.0
17.5°	48.7
20°	41.8
22.5°	39.4
25°	37.1
27.5°	37.1
30°	34.8
32.5°	34.8
35°	34.8
37.5°	37.1
40°	37.1
42.5°	37.1
45°	37.1
47.5°	39.4
50°	39.4
52.5°	39.4
55°	41.8
57.5°	41.8
60°	44.1
62.5°	44.1
65°	44.1
67.5°	44.1
70°	46.4
72.5°	46.4
75°	46.4
77.5°	46.4
80°	46.4
82.5°	46.4
85°	46.4
87.5°	46.4
90°	46.4
92.5°	46.4
95°	46.4
97.5°	46.4
100°	46.4
102.5°	46.4
105°	46.4
107.5°	46.4
110°	46.4

TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	44.1
115°	44.1
117.5°	44.1
120°	41.8
122.5°	41.8
125°	39.4
127.5°	39.4
130°	37.1
132.5°	37.1
135°	34.8
137.5°	34.8
140°	32.5
142.5°	30.2
145°	30.2
147.5°	27.8
150°	25.5
152.5°	23.2
155°	20.9
157.5°	20.9
160°	18.6
162.5°	16.2
165°	13.9
167.5°	11.6
170°	9.3
172.5°	7.0
175°	2.3
177.5°	0.0
180°	0.0

TEST NUMBER: P1245070

CATALOG NUMBER: PRLX-NIM-L-935-05L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.3	5.3	5.2	6.3	7.4	4.3	5.3	5.2	6.3	7.4
	3H	7.4	8.3	8.3	9.3	10.5	7.4	8.3	8.3	9.3	10.5
	4H	8.9	9.8	9.8	10.7	11.9	8.9	9.8	9.8	10.7	11.9
	6H	10.3	11.2	11.2	12.1	13.3	10.3	11.2	11.2	12.1	13.3
	8H	11.0	11.8	11.9	12.8	14.0	11.0	11.8	11.9	12.8	14.0
	12H	11.6	12.4	12.6	13.4	14.6	11.6	12.4	12.6	13.4	14.6
4H	2H	5.1	6.0	6.0	6.9	8.2	5.1	6.0	6.0	6.9	8.2
	3H	8.4	9.2	9.3	10.1	11.3	8.4	9.2	9.3	10.1	11.3
	4H	10.0	10.7	10.9	11.7	12.9	10.0	10.7	10.9	11.7	12.9
	6H	11.6	12.2	12.5	13.2	14.5	11.6	12.2	12.5	13.2	14.5
	8H	12.4	13.0	13.3	13.9	15.2	12.4	13.0	13.3	13.9	15.2
	12H	13.1	13.7	14.1	14.7	15.9	13.1	13.7	14.1	14.7	15.9
8H	4H	10.5	11.1	11.5	12.1	13.4	10.5	11.1	11.5	12.1	13.4
	6H	12.3	12.8	13.3	13.9	15.1	12.3	12.8	13.3	13.9	15.1
	8H	13.2	13.7	14.2	14.7	16.0	13.2	13.7	14.2	14.7	16.0
	12H	14.2	14.6	15.1	15.6	16.9	14.2	14.6	15.1	15.6	16.9
12H	4H	10.6	11.2	11.6	12.2	13.5	10.6	11.2	11.6	12.2	13.5
	6H	12.5	13.0	13.5	14.0	15.3	12.5	13.0	13.5	14.0	15.3
	8H	13.5	13.9	14.5	14.9	16.2	13.5	13.9	14.5	14.9	16.2

(END OF REPORT)