

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245074

Luminaire Tested: PRLX-NIM-L-935-09L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-935-09L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, WOVEN OVAL SHADE TEXTURE LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 902.9 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

Luminous Intensity Polar Plot





TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	56
1	95	89	83	78	87	82	77	73	70	66	62		58	55	53		48	45	43	38
2	85	76	68	61	78	70	63	57	59	54	49		49	45	42		40	37	34	30
3	77	66	57	50	71	61	53	47	52	45	40		43	38	34		35	31	28	24
4	71	58	49	42	65	54	46	40	46	39	34		38	33	29		31	27	24	20
5	65	52	43	36	60	48	40	34	41	35	30		34	29	25		28	24	21	18
6	60	47	38	32	55	44	36	30	37	31	26		31	26	22		26	22	19	16
7	56	43	34	28	51	40	32	27	34	28	23		29	24	20		24	20	17	15
8	52	39	31	25	48	36	29	24	32	25	21		27	22	18		23	19	16	13
9	49	36	28	23	45	34	27	22	29	23	19		25	20	17		21	17	15	12
10	46	33	26	21	43	31	25	20	27	22	18		24	19	16		20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39530
5°	17898
10°	4261
15°	1689
20°	1070
25°	856
30°	734
35°	681
40°	683
45°	648
50°	661
55°	676
60°	697
65°	686
70°	716
75°	715
80°	720
85°	731

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 747 cd/sqm

TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.0	5.9
10°-20°	30.1	3.3
20°-30°	29.3	3.2
30°-40°	37.5	4.2
40°-50°	49.3	5.5
50°-60°	61.8	6.8
60°-70°	73.7	8.2
70°-80°	82.1	9.1
80°-90°	84.7	9.4
90°-100°	84.7	9.4
100°-110°	82.1	9.1
110°-120°	73.2	8.1
120°-130°	60.1	6.7
130°-140°	45.9	5.1
140°-150°	30.9	3.4
150°-160°	17.0	1.9
160°-170°	6.8	0.8
170°-180°	0.8	0.1
0°-30°	112.3	12.4
0°-40°	149.9	16.6
0°-60°	261.0	28.9
0°-90°	501.4	55.5
90°-120°	239.9	26.6
90°-150°	376.9	41.7
90°-180°	401.0	44.4
0°-180°	902.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1250	
5°	726	53
15°	97	30
25°	62	29
35°	58	38
45°	62	49
55°	70	62
65°	74	74
75°	78	82
85°	78	63
90°	78	43
95°	78	63
105°	78	82
115°	74	73
125°	66	60
135°	58	46
145°	50	31
155°	35	17
165°	23	7
175°	4	1
180°	0	

TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	1249.5
2.5°	1385.3
5°	725.6
7.5°	306.5
10°	209.5
12.5°	131.9
15°	97.0
17.5°	81.5
20°	69.8
22.5°	66.0
25°	62.1
27.5°	62.1
30°	58.2
32.5°	58.2
35°	58.2
37.5°	62.1
40°	62.1
42.5°	62.1
45°	62.1
47.5°	66.0
50°	66.0
52.5°	66.0
55°	69.8
57.5°	69.8
60°	73.7
62.5°	73.7
65°	73.7
67.5°	73.7
70°	77.6
72.5°	77.6
75°	77.6
77.5°	77.6
80°	77.6
82.5°	77.6
85°	77.6
87.5°	77.6
90°	77.6
92.5°	77.6
95°	77.6
97.5°	77.6
100°	77.6
102.5°	77.6
105°	77.6
107.5°	77.6
110°	77.6

TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	73.7
115°	73.7
117.5°	73.7
120°	69.8
122.5°	69.8
125°	66.0
127.5°	66.0
130°	62.1
132.5°	62.1
135°	58.2
137.5°	58.2
140°	54.3
142.5°	50.4
145°	50.4
147.5°	46.6
150°	42.7
152.5°	38.8
155°	34.9
157.5°	34.9
160°	31.0
162.5°	27.2
165°	23.3
167.5°	19.4
170°	15.5
172.5°	11.6
175°	3.9
177.5°	0.0
180°	0.0



TEST NUMBER: P1245074

CATALOG NUMBER: PRLX-NIM-L-935-09L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.1	7.1	7.0	8.0	9.2	6.1	7.1	7.0	8.0	9.2
	3H	9.2	10.1	10.1	11.0	12.2	9.2	10.1	10.1	11.0	12.2
	4H	10.6	11.6	11.6	12.5	13.7	10.6	11.6	11.6	12.5	13.7
	6H	12.1	12.9	13.0	13.9	15.1	12.1	12.9	13.0	13.9	15.1
	8H	12.8	13.6	13.7	14.5	15.8	12.8	13.6	13.7	14.5	15.8
	12H	13.4	14.2	14.4	15.2	16.4	13.4	14.2	14.4	15.2	16.4
4H	2H	6.9	7.8	7.8	8.7	9.9	6.9	7.8	7.8	8.7	9.9
	3H	10.1	10.9	11.1	11.9	13.1	10.1	10.9	11.1	11.9	13.1
	4H	11.8	12.5	12.7	13.5	14.7	11.8	12.5	12.7	13.5	14.7
	6H	13.4	14.0	14.3	15.0	16.2	13.4	14.0	14.3	15.0	16.2
	8H	14.1	14.8	15.1	15.7	17.0	14.1	14.8	15.1	15.7	17.0
	12H	14.9	15.5	15.9	16.5	17.7	14.9	15.5	15.9	16.5	17.7
8H	4H	12.3	12.9	13.2	13.9	15.2	12.3	12.9	13.2	13.9	15.2
	6H	14.1	14.6	15.1	15.6	16.9	14.1	14.6	15.1	15.6	16.9
	8H	15.0	15.5	16.0	16.5	17.8	15.0	15.5	16.0	16.5	17.8
	12H	15.9	16.4	16.9	17.4	18.7	15.9	16.4	16.9	17.4	18.7
12H	4H	12.4	13.0	13.4	14.0	15.2	12.4	13.0	13.4	14.0	15.2
	6H	14.3	14.8	15.3	15.8	17.1	14.3	14.8	15.3	15.8	17.1
	8H	15.3	15.7	16.3	16.7	18.0	15.3	15.7	16.3	16.7	18.0

(END OF REPORT)