

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245077

Luminaire Tested: PRLX-NIM-L-935-12L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-935-12L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE
LIGHT LEVEL 4
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1291.3 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	78	87	82	77	73	70	66	62	58	55	53	48	45	43	38
2	85	76	68	61	78	70	63	57	59	54	49	49	45	42	40	37	34	30
3	77	66	57	50	71	61	53	47	52	45	40	43	38	34	35	31	28	24
4	71	58	49	42	65	54	46	40	46	39	34	38	33	29	31	27	24	20
5	65	52	43	36	60	48	40	34	41	35	30	34	29	25	28	24	21	18
6	60	47	38	32	55	44	36	30	37	31	26	31	26	22	26	22	19	16
7	56	43	34	28	51	40	32	27	34	28	23	29	24	20	24	20	17	15
8	52	39	31	25	48	36	29	24	32	25	21	27	22	18	23	19	16	13
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12
10	46	33	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56512
5°	25589
10°	6094
15°	2416
20°	1532
25°	1224
30°	1049
35°	973
40°	976
45°	927
50°	944
55°	968
60°	997
65°	981
70°	1024
75°	1023
80°	1030
85°	1045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 1069 cd/sqm



TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	5.9
10°-20°	43.0	3.3
20°-30°	41.9	3.2
30°-40°	53.7	4.2
40°-50°	70.4	5.5
50°-60°	88.5	6.9
60°-70°	105.3	8.2
70°-80°	117.4	9.1
80°-90°	121.1	9.4
90°-100°	121.1	9.4
100°-110°	117.4	9.1
110°-120°	104.7	8.1
120°-130°	86.0	6.7
130°-140°	65.6	5.1
140°-150°	44.2	3.4
150°-160°	24.3	1.9
160°-170°	9.8	0.8
170°-180°	1.2	0.1
0°-30°	160.6	12.4
0°-40°	214.3	16.6
0°-60°	373.2	28.9
0°-90°	717.1	55.5
90°-120°	343.2	26.6
90°-150°	539.0	41.7
90°-180°	574.0	44.5
0°-180°	1291.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1786	
5°	1037	76
15°	139	43
25°	89	42
35°	83	54
45°	89	70
55°	100	88
65°	105	105
75°	111	117
85°	111	91
90°	111	61
95°	111	91
105°	111	117
115°	105	105
125°	94	86
135°	83	66
145°	72	44
155°	50	24
165°	33	10
175°	6	1
180°	0	

TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	1786.3
2.5°	1980.5
5°	1037.4
7.5°	438.3
10°	299.6
12.5°	188.6
15°	138.7
17.5°	116.5
20°	99.9
22.5°	94.3
25°	88.8
27.5°	88.8
30°	83.2
32.5°	83.2
35°	83.2
37.5°	88.8
40°	88.8
42.5°	88.8
45°	88.8
47.5°	94.3
50°	94.3
52.5°	94.3
55°	99.9
57.5°	99.9
60°	105.4
62.5°	105.4
65°	105.4
67.5°	105.4
70°	111.0
72.5°	111.0
75°	111.0
77.5°	111.0
80°	111.0
82.5°	111.0
85°	111.0
87.5°	111.0
90°	111.0
92.5°	111.0
95°	111.0
97.5°	111.0
100°	111.0
102.5°	111.0
105°	111.0
107.5°	111.0
110°	111.0

TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	105.4
115°	105.4
117.5°	105.4
120°	99.9
122.5°	99.9
125°	94.3
127.5°	94.3
130°	88.8
132.5°	88.8
135°	83.2
137.5°	83.2
140°	77.7
142.5°	72.1
145°	72.1
147.5°	66.6
150°	61.0
152.5°	55.5
155°	49.9
157.5°	49.9
160°	44.4
162.5°	38.8
165°	33.3
167.5°	27.7
170°	22.2
172.5°	16.6
175°	5.5
177.5°	0.0
180°	0.0



TEST NUMBER: P1245077

CATALOG NUMBER: PRLX-NIM-L-935-12L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.3	8.4	8.2	9.3	10.5	7.3	8.4	8.2	9.3	10.5
	3H	10.4	11.3	11.3	12.3	13.5	10.4	11.3	11.3	12.3	13.5
	4H	11.9	12.8	12.8	13.7	14.9	11.9	12.8	12.8	13.7	14.9
	6H	13.3	14.2	14.3	15.1	16.3	13.3	14.2	14.3	15.1	16.3
	8H	14.0	14.8	14.9	15.8	17.0	14.0	14.8	14.9	15.8	17.0
	12H	14.7	15.5	15.6	16.4	17.7	14.7	15.5	15.6	16.4	17.7
4H	2H	8.1	9.0	9.0	10.0	11.2	8.1	9.0	9.0	10.0	11.2
	3H	11.4	12.2	12.3	13.1	14.4	11.4	12.2	12.3	13.1	14.4
	4H	13.0	13.8	13.9	14.7	16.0	13.0	13.8	13.9	14.7	16.0
	6H	14.6	15.3	15.6	16.2	17.5	14.6	15.3	15.6	16.2	17.5
	8H	15.4	16.0	16.3	17.0	18.2	15.4	16.0	16.3	17.0	18.2
	12H	16.1	16.7	17.1	17.7	19.0	16.1	16.7	17.1	17.7	19.0
8H	4H	13.5	14.2	14.5	15.1	16.4	13.5	14.2	14.5	15.1	16.4
	6H	15.3	15.9	16.3	16.9	18.1	15.3	15.9	16.3	16.9	18.1
	8H	16.3	16.7	17.2	17.7	19.0	16.3	16.7	17.2	17.7	19.0
	12H	17.2	17.6	18.2	18.6	19.9	17.2	17.6	18.2	18.6	19.9
12H	4H	13.6	14.2	14.6	15.2	16.5	13.6	14.2	14.6	15.2	16.5
	6H	15.5	16.0	16.5	17.0	18.3	15.5	16.0	16.5	17.0	18.3
	8H	16.5	16.9	17.5	17.9	19.3	16.5	16.9	17.5	17.9	19.3

(END OF REPORT)