

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245186

Luminaire Tested: PRLX-NIM-M-935-07L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-935-07L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, WOVEN OVAL SHADE TEXTU
LIGHT LEVEL 5
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.0 lumens
Efficiency: N/A
Efficacy: 24.8 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 28.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

Luminous Intensity Polar Plot



TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20						20
RC	80					70					50					30						10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	
RCR																						
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61	
1	95	89	83	78		88	82	77	73		70	66	63		58	55	53		48	46	44	
2	85	76	68	62		78	70	63	58		60	54	50		50	46	42		40	37	35	
3	77	66	58	51		71	61	54	47		52	46	41		43	39	35		35	32	29	
4	71	59	50	43		65	54	46	40		46	40	35		39	34	30		32	28	25	
5	65	52	43	37		60	49	41	35		42	35	30		35	30	26		29	25	22	
6	60	47	39	32		56	44	36	30		38	32	27		32	27	23		27	23	20	
7	56	43	35	29		52	40	33	27		35	29	24		30	25	21		25	21	18	
8	53	40	32	26		49	37	30	25		32	26	22		28	23	19		23	19	17	
9	49	37	29	24		46	34	27	22		30	24	20		26	21	18		22	18	15	
10	47	34	27	22		43	32	25	21		28	22	19		24	20	17		21	17	15	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64582
5°	28311
10°	5463
15°	1799
20°	1075
25°	847
30°	766
35°	704
40°	737
45°	695
50°	662
55°	709
60°	688
65°	740
70°	729
75°	725
80°	726
85°	733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 745 cd/sqm

TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.1	7.0
10°-20°	23.0	3.2
20°-30°	20.7	2.9
30°-40°	28.2	3.9
40°-50°	38.5	5.4
50°-60°	49.0	6.8
60°-70°	58.4	8.1
70°-80°	64.3	9.0
80°-90°	66.3	9.3
90°-100°	66.3	9.3
100°-110°	64.3	9.0
110°-120°	59.7	8.3
120°-130°	49.0	6.8
130°-140°	37.0	5.2
140°-150°	23.6	3.3
150°-160°	13.6	1.9
160°-170°	4.5	0.6
170°-180°	0.4	0.1
0°-30°	93.8	13.1
0°-40°	122.1	17.0
0°-60°	209.6	29.2
0°-90°	398.6	55.6
90°-120°	190.3	26.5
90°-150°	299.9	41.8
90°-180°	318.0	44.4
0°-180°	717.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1260	
5°	752	50
15°	72	23
25°	44	21
35°	44	28
45°	50	38
55°	55	49
65°	61	58
75°	61	64
85°	61	50
90°	61	33
95°	61	50
105°	61	64
115°	61	60
125°	55	49
135°	50	37
145°	39	24
155°	28	14
165°	17	4
175°	0	0
180°	0	

TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	1260.2
2.5°	1265.7
5°	751.7
7.5°	265.3
10°	182.4
12.5°	105.0
15°	71.9
17.5°	55.3
20°	49.7
22.5°	44.2
25°	44.2
27.5°	44.2
30°	44.2
32.5°	44.2
35°	44.2
37.5°	44.2
40°	49.7
42.5°	49.7
45°	49.7
47.5°	49.7
50°	49.7
52.5°	55.3
55°	55.3
57.5°	55.3
60°	55.3
62.5°	55.3
65°	60.8
67.5°	60.8
70°	60.8
72.5°	60.8
75°	60.8
77.5°	60.8
80°	60.8
82.5°	60.8
85°	60.8
87.5°	60.8
90°	60.8
92.5°	60.8
95°	60.8
97.5°	60.8
100°	60.8
102.5°	60.8
105°	60.8
107.5°	60.8
110°	60.8

TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	60.8
115°	60.8
117.5°	60.8
120°	55.3
122.5°	55.3
125°	55.3
127.5°	55.3
130°	49.7
132.5°	49.7
135°	49.7
137.5°	44.2
140°	44.2
142.5°	38.7
145°	38.7
147.5°	33.2
150°	33.2
152.5°	33.2
155°	27.6
157.5°	27.6
160°	22.1
162.5°	16.6
165°	16.6
167.5°	11.1
170°	11.1
172.5°	5.5
175°	0.0
177.5°	0.0
180°	0.0

TEST NUMBER: P1245186

CATALOG NUMBER: PRLX-NIM-M-935-07L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.2	7.2	7.1	8.1	9.3	6.2	7.2	7.1	8.1	9.3
	3H	9.3	10.3	10.2	11.2	12.4	9.3	10.3	10.2	11.2	12.4
	4H	10.8	11.7	11.7	12.6	13.8	10.8	11.7	11.7	12.6	13.8
	6H	12.2	13.0	13.1	13.9	15.2	12.2	13.0	13.1	13.9	15.2
	8H	12.8	13.6	13.7	14.6	15.8	12.8	13.6	13.7	14.6	15.8
	12H	13.5	14.2	14.4	15.2	16.4	13.5	14.2	14.4	15.2	16.4
4H	2H	7.0	7.9	8.0	8.9	10.1	7.0	7.9	8.0	8.9	10.1
	3H	10.3	11.1	11.2	12.0	13.3	10.3	11.1	11.2	12.0	13.3
	4H	11.9	12.6	12.8	13.6	14.8	11.9	12.6	12.8	13.6	14.8
	6H	13.4	14.1	14.4	15.1	16.3	13.4	14.1	14.4	15.1	16.3
	8H	14.2	14.8	15.1	15.8	17.0	14.2	14.8	15.1	15.8	17.0
	12H	14.9	15.5	15.9	16.5	17.8	14.9	15.5	15.9	16.5	17.8
8H	4H	12.4	13.0	13.3	14.0	15.2	12.4	13.0	13.3	14.0	15.2
	6H	14.1	14.7	15.1	15.7	16.9	14.1	14.7	15.1	15.7	16.9
	8H	15.0	15.5	16.0	16.5	17.8	15.0	15.5	16.0	16.5	17.8
	12H	16.0	16.4	16.9	17.4	18.7	16.0	16.4	16.9	17.4	18.7
12H	4H	12.5	13.0	13.4	14.0	15.3	12.5	13.0	13.4	14.0	15.3
	6H	14.3	14.8	15.3	15.8	17.1	14.3	14.8	15.3	15.8	17.1
	8H	15.3	15.7	16.3	16.7	18.0	15.3	15.7	16.3	16.7	18.0

(END OF REPORT)