

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245251

Luminaire Tested: PRLX-NIM-S-935-05L-U-LF

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245251  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-NIM-S-935-05L-U-LF  
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, LAYERED FINE SHADE TEXTURE LIGHT LEVEL 2  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 554.8 lumens  
Efficiency: N/A  
Efficacy: 50.0 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4  
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')  
CIE Type: Semi-Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

### Luminous Intensity Polar Plot





TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76	74	71	69	66	64	62	58
2	92	84	77	71	87	80	74	68	72	67	63	65	61	57	58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53	58	53	49	52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41	48	43	39	44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31	39	33	30	36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29	36	31	28	34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27	34	29	26	32	28	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	14787
5°	14591
10°	12830
15°	3115
20°	2599
25°	2164
30°	1710
35°	1419
40°	1213
45°	1096
50°	992
55°	916
60°	865
65°	802
70°	762
75°	726
80°	655
85°	624

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1096 cd/sqm



TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.5	8.7
10°-20°	51.4	9.3
20°-30°	47.9	8.6
30°-40°	47.2	8.5
40°-50°	47.0	8.5
50°-60°	46.7	8.4
60°-70°	45.0	8.1
70°-80°	41.0	7.4
80°-90°	34.1	6.1
90°-100°	32.6	5.9
100°-110°	30.5	5.5
110°-120°	26.8	4.8
120°-130°	21.9	3.9
130°-140°	16.3	2.9
140°-150°	10.5	1.9
150°-160°	5.5	1.0
160°-170°	1.9	0.3
170°-180°	0.2	0.0
0°-30°	147.7	26.6
0°-40°	194.9	35.1
0°-60°	288.5	52.0
0°-90°	408.6	73.6
90°-120°	90.0	16.2
90°-150°	138.7	25.0
90°-180°	146.0	26.3
0°-180°	554.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	467	
5°	519	48
15°	133	51
25°	105	48
35°	75	47
45°	61	47
55°	52	47
65°	45	45
75°	39	41
85°	31	26
90°	30	16
95°	30	24
105°	29	31
115°	27	27
125°	24	22
135°	21	16
145°	17	11
155°	12	5
165°	6	2
175°	1	0
180°	0	

TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	467.4
2.5°	482.4
5°	519.4
7.5°	513.4
10°	504.4
12.5°	216.2
15°	133.1
17.5°	126.1
20°	119.1
22.5°	113.1
25°	105.1
27.5°	96.1
30°	87.1
32.5°	80.1
35°	75.1
37.5°	70.1
40°	66.1
42.5°	63.1
45°	61.0
47.5°	58.0
50°	56.0
52.5°	54.0
55°	52.0
57.5°	50.0
60°	49.0
62.5°	47.0
65°	45.0
67.5°	44.0
70°	42.0
72.5°	41.0
75°	39.0
77.5°	37.0
80°	34.0
82.5°	32.0
85°	31.0
87.5°	30.0
90°	30.0
92.5°	30.0
95°	30.0
97.5°	30.0
100°	29.0
102.5°	29.0
105°	29.0
107.5°	29.0
110°	28.0



TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	28.0
115°	27.0
117.5°	26.0
120°	26.0
122.5°	25.0
125°	24.0
127.5°	24.0
130°	23.0
132.5°	22.0
135°	21.0
137.5°	20.0
140°	19.0
142.5°	18.0
145°	17.0
147.5°	15.0
150°	14.0
152.5°	13.0
155°	12.0
157.5°	10.0
160°	9.0
162.5°	8.0
165°	6.0
167.5°	5.0
170°	4.0
172.5°	2.0
175°	1.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245251

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-LF

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.2	9.4	9.0	10.1	11.0	8.2	9.4	9.0	10.1	11.0
	3H	10.6	11.6	11.3	12.3	13.3	10.6	11.6	11.3	12.3	13.3
	4H	11.6	12.6	12.4	13.4	14.3	11.6	12.6	12.4	13.4	14.3
	6H	12.6	13.5	13.4	14.3	15.2	12.6	13.5	13.4	14.3	15.2
	8H	13.0	13.9	13.8	14.7	15.6	13.0	13.9	13.8	14.7	15.6
	12H	13.4	14.3	14.2	15.1	16.0	13.4	14.3	14.2	15.1	16.0
4H	2H	8.8	9.8	9.6	10.6	11.5	8.8	9.8	9.6	10.6	11.5
	3H	11.4	12.2	12.1	13.0	14.0	11.4	12.2	12.1	13.0	14.0
	4H	12.6	13.4	13.4	14.2	15.1	12.6	13.4	13.4	14.2	15.1
	6H	13.7	14.4	14.5	15.2	16.2	13.7	14.4	14.5	15.2	16.2
	8H	14.2	14.9	15.0	15.7	16.7	14.2	14.9	15.0	15.7	16.7
	12H	14.7	15.3	15.6	16.2	17.2	14.7	15.3	15.6	16.2	17.2
8H	4H	13.0	13.6	13.8	14.4	15.4	13.0	13.6	13.8	14.4	15.4
	6H	14.3	14.8	15.1	15.7	16.7	14.3	14.8	15.1	15.7	16.7
	8H	14.9	15.4	15.7	16.3	17.3	14.9	15.4	15.7	16.3	17.3
	12H	15.6	16.0	16.4	16.9	17.9	15.6	16.0	16.4	16.9	17.9
12H	4H	13.0	13.6	13.9	14.5	15.5	13.0	13.6	13.9	14.5	15.5
	6H	14.4	14.9	15.2	15.7	16.8	14.4	14.9	15.2	15.7	16.8
	8H	15.1	15.6	15.9	16.4	17.5	15.1	15.6	15.9	16.4	17.5

(END OF REPORT)