

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245257

Luminaire Tested: PRLX-NIM-S-935-07L-U-NR

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245257  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-NIM-S-935-07L-U-NR  
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE  
LIGHT LEVEL 3  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 784.0 lumens  
Efficiency: N/A  
Efficacy: 48.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4  
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')  
CIE Type: Semi-Direct

Input Watts (W): 16.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

### Luminous Intensity Polar Plot



TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47		52	47	43		47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41		48	43	39		44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31		39	33	30		36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27		34	29	26		32	28	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20886
5°	20611
10°	18123
15°	4400
20°	3671
25°	3056
30°	2415
35°	2003
40°	1712
45°	1548
50°	1404
55°	1295
60°	1224
65°	1134
70°	1078
75°	1026
80°	927
85°	881

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1548 cd/sqm

TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.4	8.7
10°-20°	72.6	9.3
20°-30°	67.6	8.6
30°-40°	66.6	8.5
40°-50°	66.4	8.5
50°-60°	66.0	8.4
60°-70°	63.6	8.1
70°-80°	57.9	7.4
80°-90°	48.2	6.1
90°-100°	46.1	5.9
100°-110°	43.2	5.5
110°-120°	37.9	4.8
120°-130°	30.9	3.9
130°-140°	23.1	2.9
140°-150°	14.8	1.9
150°-160°	7.7	1.0
160°-170°	2.7	0.3
170°-180°	0.3	0.0
0°-30°	208.6	26.6
0°-40°	275.2	35.1
0°-60°	407.6	52.0
0°-90°	577.3	73.6
90°-120°	127.2	16.2
90°-150°	196.0	25.0
90°-180°	207.0	26.4
0°-180°	784.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	660	
5°	734	68
15°	188	73
25°	148	68
35°	106	67
45°	86	66
55°	74	66
65°	64	64
75°	55	58
85°	44	37
90°	42	23
95°	42	34
105°	41	43
115°	38	38
125°	34	31
135°	30	23
145°	24	15
155°	17	8
165°	8	3
175°	1	0
180°	0	

TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	660.2
2.5°	681.4
5°	733.7
7.5°	725.2
10°	712.5
12.5°	305.4
15°	188.0
17.5°	178.1
20°	168.2
22.5°	159.8
25°	148.4
27.5°	135.7
30°	123.0
32.5°	113.1
35°	106.0
37.5°	99.0
40°	93.3
42.5°	89.1
45°	86.2
47.5°	82.0
50°	79.2
52.5°	76.3
55°	73.5
57.5°	70.7
60°	69.3
62.5°	66.4
65°	63.6
67.5°	62.2
70°	59.4
72.5°	58.0
75°	55.1
77.5°	52.3
80°	48.1
82.5°	45.2
85°	43.8
87.5°	42.4
90°	42.4
92.5°	42.4
95°	42.4
97.5°	42.4
100°	41.0
102.5°	41.0
105°	41.0
107.5°	41.0
110°	39.6



TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	39.6
115°	38.2
117.5°	36.8
120°	36.8
122.5°	35.3
125°	33.9
127.5°	33.9
130°	32.5
132.5°	31.1
135°	29.7
137.5°	28.3
140°	26.9
142.5°	25.4
145°	24.0
147.5°	21.2
150°	19.8
152.5°	18.4
155°	17.0
157.5°	14.1
160°	12.7
162.5°	11.3
165°	8.5
167.5°	7.1
170°	5.7
172.5°	2.8
175°	1.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1245257

CATALOG NUMBER: PRLX-NIM-S-935-07L-U-NR

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.4	10.6	10.2	11.3	12.2	9.4	10.6	10.2	11.3	12.2
	3H	11.8	12.8	12.5	13.6	14.5	11.8	12.8	12.5	13.6	14.5
	4H	12.8	13.8	13.6	14.6	15.5	12.8	13.8	13.6	14.6	15.5
	6H	13.8	14.7	14.6	15.5	16.4	13.8	14.7	14.6	15.5	16.4
	8H	14.2	15.1	15.0	15.9	16.8	14.2	15.1	15.0	15.9	16.8
	12H	14.6	15.5	15.4	16.3	17.2	14.6	15.5	15.4	16.3	17.2
4H	2H	10.0	11.0	10.8	11.8	12.7	10.0	11.0	10.8	11.8	12.7
	3H	12.6	13.4	13.3	14.2	15.2	12.6	13.4	13.3	14.2	15.2
	4H	13.8	14.6	14.6	15.4	16.3	13.8	14.6	14.6	15.4	16.3
	6H	14.9	15.6	15.7	16.4	17.4	14.9	15.6	15.7	16.4	17.4
	8H	15.4	16.1	16.2	16.9	17.9	15.4	16.1	16.2	16.9	17.9
	12H	15.9	16.5	16.8	17.4	18.4	15.9	16.5	16.8	17.4	18.4
8H	4H	14.2	14.8	15.0	15.6	16.6	14.2	14.8	15.0	15.6	16.6
	6H	15.5	16.0	16.3	16.9	17.9	15.5	16.0	16.3	16.9	17.9
	8H	16.1	16.6	17.0	17.5	18.5	16.1	16.6	17.0	17.5	18.5
	12H	16.8	17.2	17.6	18.1	19.1	16.8	17.2	17.6	18.1	19.1
12H	4H	14.2	14.8	15.1	15.7	16.7	14.2	14.8	15.1	15.7	16.7
	6H	15.6	16.1	16.4	16.9	18.0	15.6	16.1	16.4	16.9	18.0
	8H	16.3	16.8	17.1	17.6	18.7	16.3	16.8	17.1	17.6	18.7

(END OF REPORT)