

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980062

Luminaire Tested: PRLX-242-935-LL1-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-935-LL1-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH FROSTED LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1180.4 lumens
Efficiency: N/A
Efficacy: 157.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.33
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980062
CATALOG NUMBER: PRLX-242-935-LL1-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980062

CATALOG NUMBER: PRLX-242-935-LL1-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	36
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32
9	58	44	36	31	56	44	36	31	43	36	31	42	35	31	41	35	30	29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2051
5°	2047
10°	2039
15°	2013
20°	1986
25°	1958
30°	1922
35°	1890
40°	1859
45°	1821
50°	1785
55°	1735
60°	1676
65°	1599
70°	1481
75°	581
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1821 cd/sqm



TEST NUMBER: P980062

CATALOG NUMBER: PRLX-242-935-LL1-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	3.7
10°-20°	122.6	10.4
20°-30°	182.6	15.5
30°-40°	216.4	18.3
40°-50°	222.0	18.8
50°-60°	198.7	16.8
60°-70°	149.1	12.6
70°-80°	45.9	3.9
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.4	29.5
0°-40°	564.8	47.8
0°-60°	985.5	83.5
0°-90°	1180.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	456	43
15°	434	123
25°	397	183
35°	346	216
45°	288	222
55°	222	199
65°	151	149
75°	34	46
85°	0	0
90°	0	



TEST NUMBER: P980062

CATALOG NUMBER: PRLX-242-935-LL1-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	458.4
2.5°	458.0
5°	455.7
7.5°	452.6
10°	448.8
12.5°	442.6
15°	434.5
17.5°	426.0
20°	417.1
22.5°	407.4
25°	396.6
27.5°	384.6
30°	371.9
32.5°	358.8
35°	346.0
37.5°	332.1
40°	318.2
42.5°	302.8
45°	287.7
47.5°	272.3
50°	256.4
52.5°	239.4
55°	222.4
57.5°	204.7
60°	187.3
62.5°	169.2
65°	151.0
67.5°	132.1
70°	113.2
72.5°	83.8
75°	33.6
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P980062
 CATALOG NUMBER: PRLX-242-935-LL1-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.25	15.84	14.62	16.16	16.47	14.25	15.84	14.62	16.16	16.47
	3H	16.00	17.43	16.38	17.76	18.12	16.00	17.43	16.38	17.76	18.12
	4H	16.20	17.54	16.60	17.89	18.26	16.20	17.54	16.60	17.89	18.26
	6H	16.14	17.38	16.55	17.74	18.13	16.14	17.38	16.55	17.74	18.13
	8H	16.11	17.28	16.53	17.67	18.07	16.11	17.28	16.53	17.67	18.07
	12H	16.08	17.20	16.51	17.59	18.01	16.08	17.20	16.51	17.59	18.01
4H	2H	14.89	16.23	15.29	16.57	16.95	14.89	16.23	15.29	16.57	16.95
	3H	16.80	17.91	17.21	18.31	18.71	16.80	17.91	17.21	18.31	18.71
	4H	16.98	17.98	17.42	18.39	18.83	16.98	17.98	17.42	18.39	18.83
	6H	16.93	17.79	17.39	18.24	18.69	16.93	17.79	17.39	18.24	18.69
	8H	16.90	17.70	17.36	18.14	18.61	16.90	17.70	17.36	18.14	18.61
	12H	16.87	17.58	17.35	18.06	18.53	16.87	17.58	17.35	18.06	18.53
8H	4H	17.02	17.82	17.48	18.27	18.73	17.02	17.82	17.48	18.27	18.73
	6H	16.95	17.61	17.45	18.10	18.58	16.95	17.61	17.45	18.10	18.58
	8H	16.91	17.49	17.42	18.00	18.49	16.91	17.49	17.42	18.00	18.49
	12H	16.88	17.40	17.39	17.89	18.45	16.88	17.40	17.39	17.89	18.45
12H	4H	17.00	17.71	17.48	18.19	18.66	17.00	17.71	17.48	18.19	18.66
	6H	16.91	17.49	17.42	18.00	18.49	16.91	17.49	17.42	18.00	18.49
	8H	16.88	17.40	17.39	17.89	18.45	16.88	17.40	17.39	17.89	18.45