

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980113

Luminaire Tested: PRLX-242-935-LL6-F-U-S-WHTE-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P980113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-22)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-242-935-LL6-F-U-S-WHTE-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 242 SHADE WITH FROSTED LENS  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5044.1 lumens  
Efficiency: N/A  
Efficacy: 150.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.34  
Luminous Opening: Circular (Dia: 1.75' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 33.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P980113  
CATALOG NUMBER: PRLX-242-935-LL6-F-U-S-WHTE-X

### Luminous Intensity Polar Plot



TEST NUMBER: P980113

CATALOG NUMBER: PRLX-242-935-LL6-F-U-S-WHTE-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	100	92	86	80	98	90	85	79	87	82	78	84	80	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	71	67	63	61
4	84	72	64	57	81	71	63	57	68	61	56	66	60	55	64	59	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	8557
5°	8548
10°	8508
15°	8406
20°	8305
25°	8211
30°	8056
35°	7958
40°	7840
45°	7719
50°	7587
55°	7417
60°	7209
65°	6943
70°	6559
75°	2722
80°	590
85°	940

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7719 cd/sqm

TEST NUMBER: P980113

CATALOG NUMBER: PRLX-242-935-LL6-F-U-S-WHTE-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.6	3.6
10°-20°	512.0	10.1
20°-30°	765.2	15.2
30°-40°	911.4	18.1
40°-50°	940.9	18.7
50°-60°	849.5	16.8
60°-70°	648.7	12.9
70°-80°	219.1	4.3
80°-90°	16.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1457.7	28.9
0°-40°	2369.1	47.0
0°-60°	4159.5	82.5
0°-90°	5044.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5044.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1912	
5°	1903	181
15°	1814	512
25°	1663	765
35°	1457	911
45°	1220	941
55°	951	849
65°	656	649
75°	157	219
85°	18	17
90°	0	

TEST NUMBER: P980113

CATALOG NUMBER: PRLX-242-935-LL6-F-U-S-WHTE-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1912.1
2.5°	1910.5
5°	1902.9
7.5°	1887.6
10°	1872.3
12.5°	1847.9
15°	1814.3
17.5°	1780.6
20°	1743.9
22.5°	1707.3
25°	1662.9
27.5°	1612.5
30°	1559.0
32.5°	1511.6
35°	1456.6
37.5°	1401.6
40°	1342.0
42.5°	1282.4
45°	1219.7
47.5°	1155.5
50°	1089.8
52.5°	1021.0
55°	950.7
57.5°	878.9
60°	805.5
62.5°	732.1
65°	655.7
67.5°	580.8
70°	501.3
72.5°	383.6
75°	157.4
77.5°	33.6
80°	22.9
82.5°	21.4
85°	18.3
87.5°	10.7
90°	0.0



TEST NUMBER: P980113  
 CATALOG NUMBER: PRLX-242-935-LL6-F-U-S-WHTE-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.31	20.92	19.68	21.23	21.55	19.31	20.92	19.68	21.23	21.55
	3H	21.14	22.58	21.52	22.91	23.27	21.14	22.58	21.52	22.91	23.27
	4H	21.37	22.73	21.77	23.08	23.45	21.37	22.73	21.77	23.08	23.45
	6H	21.32	22.57	21.73	22.94	23.33	21.32	22.57	21.73	22.94	23.33
	8H	21.29	22.49	21.72	22.88	23.27	21.29	22.49	21.72	22.88	23.27
	12H	21.27	22.41	21.70	22.79	23.22	21.27	22.41	21.70	22.79	23.22
4H	2H	19.96	21.32	20.36	21.67	22.04	19.96	21.32	20.36	21.67	22.04
	3H	21.97	23.09	22.38	23.49	23.89	21.97	23.09	22.38	23.49	23.89
	4H	22.19	23.20	22.62	23.61	24.05	22.19	23.20	22.62	23.61	24.05
	6H	22.15	23.02	22.60	23.46	23.92	22.15	23.02	22.60	23.46	23.92
	8H	22.12	22.93	22.58	23.38	23.84	22.12	22.93	22.58	23.38	23.84
	12H	22.10	22.83	22.58	23.31	23.78	22.10	22.83	22.58	23.31	23.78
8H	4H	22.24	23.06	22.70	23.50	23.97	22.24	23.06	22.70	23.50	23.97
	6H	22.19	22.86	22.68	23.35	23.82	22.19	22.86	22.68	23.35	23.82
	8H	22.16	22.75	22.67	23.26	23.75	22.16	22.75	22.67	23.26	23.75
	12H	22.15	22.67	22.65	23.16	23.72	22.15	22.67	22.65	23.16	23.72
12H	4H	22.22	22.94	22.70	23.42	23.89	22.22	22.94	22.70	23.42	23.89
	6H	22.15	22.74	22.66	23.25	23.74	22.15	22.74	22.66	23.25	23.74
	8H	22.14	22.66	22.64	23.15	23.71	22.14	22.66	22.64	23.15	23.71