

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245101

Luminaire Tested: PRLX-NIM-L-940-05L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-940-05L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE
LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 580.6 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56		
1	95	89	83	78	87	82	77	73	70	66	62	58	55	53	48	45	43	38		
2	85	76	68	61	78	70	63	57	59	54	49	49	45	42	40	37	34	30		
3	77	66	57	50	71	61	53	47	52	45	40	43	38	34	35	31	28	24		
4	71	58	49	42	65	54	46	40	46	39	34	38	33	29	31	27	24	20		
5	65	52	43	36	60	48	40	34	41	35	30	34	29	25	28	24	21	18		
6	60	47	38	32	55	44	36	30	37	31	26	31	26	22	26	22	19	16		
7	56	43	34	28	51	40	32	27	34	28	23	29	24	20	24	20	17	15		
8	52	39	31	25	48	36	29	24	32	25	21	27	22	18	23	19	16	13		
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12		
10	46	33	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25432
5°	11517
10°	2742
15°	1087
20°	688
25°	550
30°	472
35°	438
40°	439
45°	417
50°	424
55°	435
60°	448
65°	441
70°	460
75°	460
80°	463
85°	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 480 cd/sqm

TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	5.9
10°-20°	19.4	3.3
20°-30°	18.8	3.2
30°-40°	24.1	4.2
40°-50°	31.7	5.5
50°-60°	39.8	6.8
60°-70°	47.4	8.2
70°-80°	52.8	9.1
80°-90°	54.4	9.4
90°-100°	54.4	9.4
100°-110°	52.8	9.1
110°-120°	47.1	8.1
120°-130°	38.6	6.7
130°-140°	29.5	5.1
140°-150°	19.9	3.4
150°-160°	10.9	1.9
160°-170°	4.4	0.8
170°-180°	0.5	0.1
0°-30°	72.3	12.4
0°-40°	96.4	16.6
0°-60°	167.8	28.9
0°-90°	322.4	55.5
90°-120°	154.3	26.6
90°-150°	242.4	41.7
90°-180°	258.0	44.4
0°-180°	580.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	467	34
15°	62	19
25°	40	19
35°	37	24
45°	40	32
55°	45	40
65°	47	47
75°	50	53
85°	50	41
90°	50	27
95°	50	41
105°	50	53
115°	47	47
125°	42	39
135°	37	30
145°	32	20
155°	22	11
165°	15	4
175°	2	1
180°	0	

TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	803.9
2.5°	891.3
5°	466.9
7.5°	197.2
10°	134.8
12.5°	84.9
15°	62.4
17.5°	52.4
20°	44.9
22.5°	42.4
25°	39.9
27.5°	39.9
30°	37.4
32.5°	37.4
35°	37.4
37.5°	39.9
40°	39.9
42.5°	39.9
45°	39.9
47.5°	42.4
50°	42.4
52.5°	42.4
55°	44.9
57.5°	44.9
60°	47.4
62.5°	47.4
65°	47.4
67.5°	47.4
70°	49.9
72.5°	49.9
75°	49.9
77.5°	49.9
80°	49.9
82.5°	49.9
85°	49.9
87.5°	49.9
90°	49.9
92.5°	49.9
95°	49.9
97.5°	49.9
100°	49.9
102.5°	49.9
105°	49.9
107.5°	49.9
110°	49.9

TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	47.4
115°	47.4
117.5°	47.4
120°	44.9
122.5°	44.9
125°	42.4
127.5°	42.4
130°	39.9
132.5°	39.9
135°	37.4
137.5°	37.4
140°	35.0
142.5°	32.5
145°	32.5
147.5°	30.0
150°	27.5
152.5°	25.0
155°	22.5
157.5°	22.5
160°	20.0
162.5°	17.5
165°	15.0
167.5°	12.5
170°	10.0
172.5°	7.5
175°	2.5
177.5°	0.0
180°	0.0

TEST NUMBER: P1245101

CATALOG NUMBER: PRLX-NIM-L-940-05L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.6	5.6	5.4	6.5	7.7	4.6	5.6	5.4	6.5	7.7
	3H	7.6	8.6	8.5	9.5	10.7	7.6	8.6	8.5	9.5	10.7
	4H	9.1	10.0	10.0	11.0	12.2	9.1	10.0	10.0	11.0	12.2
	6H	10.6	11.4	11.5	12.3	13.6	10.6	11.4	11.5	12.3	13.6
	8H	11.2	12.0	12.2	13.0	14.2	11.2	12.0	12.2	13.0	14.2
	12H	11.9	12.7	12.8	13.6	14.9	11.9	12.7	12.8	13.6	14.9
4H	2H	5.3	6.3	6.3	7.2	8.4	5.3	6.3	6.3	7.2	8.4
	3H	8.6	9.4	9.5	10.4	11.6	8.6	9.4	9.5	10.4	11.6
	4H	10.2	11.0	11.2	11.9	13.2	10.2	11.0	11.2	11.9	13.2
	6H	11.8	12.5	12.8	13.5	14.7	11.8	12.5	12.8	13.5	14.7
	8H	12.6	13.2	13.5	14.2	15.5	12.6	13.2	13.5	14.2	15.5
	12H	13.4	13.9	14.3	14.9	16.2	13.4	13.9	14.3	14.9	16.2
8H	4H	10.8	11.4	11.7	12.4	13.6	10.8	11.4	11.7	12.4	13.6
	6H	12.6	13.1	13.5	14.1	15.4	12.6	13.1	13.5	14.1	15.4
	8H	13.5	14.0	14.4	15.0	16.2	13.5	14.0	14.4	15.0	16.2
	12H	14.4	14.8	15.4	15.8	17.2	14.4	14.8	15.4	15.8	17.2
12H	4H	10.9	11.4	11.8	12.4	13.7	10.9	11.4	11.8	12.4	13.7
	6H	12.7	13.2	13.7	14.2	15.5	12.7	13.2	13.7	14.2	15.5
	8H	13.7	14.2	14.7	15.2	16.5	13.7	14.2	14.7	15.2	16.5

(END OF REPORT)