

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245192

Luminaire Tested: PRLX-NIM-M-940-03L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-940-03L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL LINES SHADE TEXT LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 304.0 lumens
Efficiency: N/A
Efficacy: 27.4 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56		
1	95	89	83	78	88	82	77	73	70	66	63	58	55	53	48	46	44	38		
2	85	76	68	62	78	70	63	58	60	54	50	50	46	42	40	37	35	30		
3	77	66	58	51	71	61	54	47	52	46	41	43	39	35	35	32	29	25		
4	71	59	50	43	65	54	46	40	46	40	35	39	34	30	32	28	25	21		
5	65	52	43	37	60	49	41	35	42	35	30	35	30	26	29	25	22	18		
6	60	47	39	32	56	44	36	30	38	31	27	32	27	23	27	23	20	17		
7	56	43	35	29	52	40	33	27	35	29	24	30	25	21	25	21	18	15		
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	16	14		
9	49	37	29	24	46	34	27	22	30	24	20	26	21	18	22	18	15	13		
10	47	34	27	22	43	32	25	21	28	22	19	24	20	17	21	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27381
5°	12003
10°	2315
15°	763
20°	456
25°	358
30°	324
35°	298
40°	313
45°	295
50°	281
55°	300
60°	291
65°	314
70°	309
75°	308
80°	308
85°	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 316 cd/sqm

TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	7.0
10°-20°	9.7	3.2
20°-30°	8.8	2.9
30°-40°	12.0	3.9
40°-50°	16.3	5.4
50°-60°	20.7	6.8
60°-70°	24.7	8.1
70°-80°	27.3	9.0
80°-90°	28.1	9.3
90°-100°	28.1	9.3
100°-110°	27.3	9.0
110°-120°	25.3	8.3
120°-130°	20.7	6.8
130°-140°	15.7	5.2
140°-150°	10.0	3.3
150°-160°	5.8	1.9
160°-170°	1.9	0.6
170°-180°	0.2	0.1
0°-30°	39.8	13.1
0°-40°	51.7	17.0
0°-60°	88.8	29.2
0°-90°	169.0	55.6
90°-120°	80.8	26.6
90°-150°	127.2	41.8
90°-180°	135.0	44.4
0°-180°	304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	319	21
15°	30	10
25°	19	9
35°	19	12
45°	21	16
55°	23	21
65°	26	25
75°	26	27
85°	26	21
90°	26	14
95°	26	21
105°	26	27
115°	26	25
125°	23	21
135°	21	16
145°	16	10
155°	12	6
165°	7	2
175°	0	0
180°	0	

TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	534.3
2.5°	536.7
5°	318.7
7.5°	112.5
10°	77.3
12.5°	44.5
15°	30.5
17.5°	23.4
20°	21.1
22.5°	18.7
25°	18.7
27.5°	18.7
30°	18.7
32.5°	18.7
35°	18.7
37.5°	18.7
40°	21.1
42.5°	21.1
45°	21.1
47.5°	21.1
50°	21.1
52.5°	23.4
55°	23.4
57.5°	23.4
60°	23.4
62.5°	23.4
65°	25.8
67.5°	25.8
70°	25.8
72.5°	25.8
75°	25.8
77.5°	25.8
80°	25.8
82.5°	25.8
85°	25.8
87.5°	25.8
90°	25.8
92.5°	25.8
95°	25.8
97.5°	25.8
100°	25.8
102.5°	25.8
105°	25.8
107.5°	25.8
110°	25.8

TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	25.8
115°	25.8
117.5°	25.8
120°	23.4
122.5°	23.4
125°	23.4
127.5°	23.4
130°	21.1
132.5°	21.1
135°	21.1
137.5°	18.7
140°	18.7
142.5°	16.4
145°	16.4
147.5°	14.1
150°	14.1
152.5°	14.1
155°	11.7
157.5°	11.7
160°	9.4
162.5°	7.0
165°	7.0
167.5°	4.7
170°	4.7
172.5°	2.3
175°	0.0
177.5°	0.0
180°	0.0

TEST NUMBER: P1245192

CATALOG NUMBER: PRLX-NIM-M-940-03L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.2	4.2	4.1	5.1	6.3	3.2	4.2	4.1	5.1	6.3
	3H	6.3	7.3	7.2	8.2	9.4	6.3	7.3	7.2	8.2	9.4
	4H	7.8	8.7	8.7	9.6	10.8	7.8	8.7	8.7	9.6	10.8
	6H	9.2	10.0	10.1	11.0	12.2	9.2	10.0	10.1	11.0	12.2
	8H	9.8	10.6	10.8	11.6	12.8	9.8	10.6	10.8	11.6	12.8
	12H	10.5	11.3	11.4	12.2	13.5	10.5	11.3	11.4	12.2	13.5
4H	2H	4.0	5.0	5.0	5.9	7.1	4.0	5.0	5.0	5.9	7.1
	3H	7.3	8.1	8.2	9.1	10.3	7.3	8.1	8.2	9.1	10.3
	4H	8.9	9.6	9.8	10.6	11.8	8.9	9.6	9.8	10.6	11.8
	6H	10.4	11.1	11.4	12.1	13.3	10.4	11.1	11.4	12.1	13.3
	8H	11.2	11.8	12.1	12.8	14.1	11.2	11.8	12.1	12.8	14.1
	12H	11.9	12.5	12.9	13.5	14.8	11.9	12.5	12.9	13.5	14.8
8H	4H	9.4	10.0	10.3	11.0	12.2	9.4	10.0	10.3	11.0	12.2
	6H	11.1	11.7	12.1	12.7	14.0	11.1	11.7	12.1	12.7	14.0
	8H	12.1	12.5	13.0	13.5	14.8	12.1	12.5	13.0	13.5	14.8
	12H	13.0	13.4	14.0	14.4	15.7	13.0	13.4	14.0	14.4	15.7
12H	4H	9.5	10.1	10.5	11.1	12.3	9.5	10.1	10.5	11.1	12.3
	6H	11.3	11.8	12.3	12.8	14.1	11.3	11.8	12.3	12.8	14.1
	8H	12.3	12.7	13.3	13.7	15.1	12.3	12.7	13.3	13.7	15.1

(END OF REPORT)