

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980182

Luminaire Tested: PRLX-242-940-LL5-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-940-LL5-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH FROSTED LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4348.6 lumens
Efficiency: N/A
Efficacy: 147.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.33
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980182
CATALOG NUMBER: PRLX-242-940-LL5-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980182

CATALOG NUMBER: PRLX-242-940-LL5-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	36
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32
9	58	44	36	31	56	44	36	31	43	36	31	42	35	31	41	35	30	29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7557
5°	7542
10°	7512
15°	7415
20°	7317
25°	7215
30°	7079
35°	6964
40°	6848
45°	6708
50°	6577
55°	6394
60°	6176
65°	5891
70°	5454
75°	2141
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6708 cd/sqm



TEST NUMBER: P980182

CATALOG NUMBER: PRLX-242-940-LL5-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.4	3.7
10°-20°	451.5	10.4
20°-30°	672.6	15.5
30°-40°	797.1	18.3
40°-50°	817.9	18.8
50°-60°	731.9	16.8
60°-70°	549.0	12.6
70°-80°	169.1	3.9
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.5	29.5
0°-40°	2080.7	47.8
0°-60°	3630.5	83.5
0°-90°	4348.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4348.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1689	
5°	1679	159
15°	1600	451
25°	1461	673
35°	1275	797
45°	1060	818
55°	820	732
65°	556	549
75°	124	169
85°	0	0
90°	0	



TEST NUMBER: P980182

CATALOG NUMBER: PRLX-242-940-LL5-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1688.7
2.5°	1687.3
5°	1678.8
7.5°	1667.4
10°	1653.2
12.5°	1630.4
15°	1600.5
17.5°	1569.2
20°	1536.5
22.5°	1500.9
25°	1461.1
27.5°	1417.0
30°	1370.0
32.5°	1321.7
35°	1274.7
37.5°	1223.5
40°	1172.3
42.5°	1115.4
45°	1059.9
47.5°	1003.0
50°	944.7
52.5°	882.1
55°	819.5
57.5°	754.0
60°	690.0
62.5°	623.1
65°	556.3
67.5°	486.6
70°	416.8
72.5°	308.7
75°	123.8
77.5°	5.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P980182
 CATALOG NUMBER: PRLX-242-940-LL5-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.78	20.37	19.15	20.69	21.00	18.78	20.37	19.15	20.69	21.00
	3H	20.53	21.96	20.91	22.29	22.65	20.53	21.96	20.91	22.29	22.65
	4H	20.73	22.07	21.13	22.42	22.79	20.73	22.07	21.13	22.42	22.79
	6H	20.67	21.91	21.08	22.27	22.66	20.67	21.91	21.08	22.27	22.66
	8H	20.64	21.81	21.06	22.20	22.60	20.64	21.81	21.06	22.20	22.60
	12H	20.61	21.73	21.04	22.11	22.54	20.61	21.73	21.04	22.11	22.54
4H	2H	19.42	20.76	19.82	21.10	21.48	19.42	20.76	19.82	21.10	21.48
	3H	21.33	22.44	21.74	22.84	23.24	21.33	22.44	21.74	22.84	23.24
	4H	21.51	22.51	21.95	22.92	23.36	21.51	22.51	21.95	22.92	23.36
	6H	21.46	22.32	21.92	22.77	23.22	21.46	22.32	21.92	22.77	23.22
	8H	21.42	22.23	21.89	22.67	23.14	21.42	22.23	21.89	22.67	23.14
	12H	21.40	22.11	21.88	22.59	23.06	21.40	22.11	21.88	22.59	23.06
8H	4H	21.55	22.35	22.01	22.80	23.26	21.55	22.35	22.01	22.80	23.26
	6H	21.48	22.14	21.98	22.63	23.10	21.48	22.14	21.98	22.63	23.10
	8H	21.44	22.02	21.95	22.53	23.02	21.44	22.02	21.95	22.53	23.02
	12H	21.41	21.93	21.92	22.42	22.98	21.41	21.93	21.92	22.42	22.98
12H	4H	21.52	22.24	22.01	22.72	23.19	21.52	22.24	22.01	22.72	23.19
	6H	21.44	22.02	21.95	22.53	23.02	21.44	22.02	21.95	22.53	23.02
	8H	21.41	21.93	21.92	22.42	22.98	21.41	21.93	21.92	22.42	22.98