

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980192

Luminaire Tested: PRLX-242-940-LL6-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-940-LL6-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH FROSTED LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4845.4 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.33
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980192
CATALOG NUMBER: PRLX-242-940-LL6-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980192

CATALOG NUMBER: PRLX-242-940-LL6-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	36
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32
9	58	44	36	31	56	44	36	31	43	36	31	42	35	31	41	35	30	29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8421
5°	8403
10°	8371
15°	8262
20°	8154
25°	8039
30°	7889
35°	7760
40°	7631
45°	7474
50°	7328
55°	7124
60°	6881
65°	6563
70°	6078
75°	2384
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7474 cd/sqm

TEST NUMBER: P980192

CATALOG NUMBER: PRLX-242-940-LL6-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.7	3.7
10°-20°	503.1	10.4
20°-30°	749.5	15.5
30°-40°	888.2	18.3
40°-50°	911.3	18.8
50°-60°	815.5	16.8
60°-70°	611.8	12.6
70°-80°	188.4	3.9
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1430.2	29.5
0°-40°	2318.4	47.8
0°-60°	4045.3	83.5
0°-90°	4845.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4845.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1882	
5°	1871	178
15°	1783	503
25°	1628	749
35°	1420	888
45°	1181	911
55°	913	816
65°	620	612
75°	138	188
85°	0	0
90°	0	



TEST NUMBER: P980192

CATALOG NUMBER: PRLX-242-940-LL6-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1881.7
2.5°	1880.1
5°	1870.6
7.5°	1857.9
10°	1842.1
12.5°	1816.7
15°	1783.4
17.5°	1748.5
20°	1712.1
22.5°	1672.4
25°	1628.0
27.5°	1578.9
30°	1526.6
32.5°	1472.7
35°	1420.4
37.5°	1363.3
40°	1306.2
42.5°	1242.8
45°	1181.0
47.5°	1117.6
50°	1052.6
52.5°	982.9
55°	913.1
57.5°	840.2
60°	768.8
62.5°	694.3
65°	619.8
67.5°	542.2
70°	464.5
72.5°	344.0
75°	137.9
77.5°	6.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P980192
 CATALOG NUMBER: PRLX-242-940-LL6-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.16	20.75	19.52	21.06	21.38	19.16	20.75	19.52	21.06	21.38
	3H	20.91	22.34	21.28	22.66	23.02	20.91	22.34	21.28	22.66	23.02
	4H	21.10	22.44	21.50	22.79	23.17	21.10	22.44	21.50	22.79	23.17
	6H	21.04	22.28	21.46	22.65	23.04	21.04	22.28	21.46	22.65	23.04
	8H	21.01	22.19	21.44	22.58	22.98	21.01	22.19	21.44	22.58	22.98
	12H	20.98	22.11	21.41	22.49	22.92	20.98	22.11	21.41	22.49	22.92
4H	2H	19.79	21.13	20.19	21.48	21.86	19.79	21.13	20.19	21.48	21.86
	3H	21.71	22.82	22.12	23.22	23.62	21.71	22.82	22.12	23.22	23.62
	4H	21.89	22.88	22.32	23.30	23.74	21.89	22.88	22.32	23.30	23.74
	6H	21.84	22.70	22.29	23.14	23.60	21.84	22.70	22.29	23.14	23.60
	8H	21.80	22.60	22.26	23.05	23.51	21.80	22.60	22.26	23.05	23.51
	12H	21.77	22.49	22.26	22.97	23.44	21.77	22.49	22.26	22.97	23.44
8H	4H	21.93	22.73	22.39	23.17	23.64	21.93	22.73	22.39	23.17	23.64
	6H	21.86	22.51	22.35	23.00	23.48	21.86	22.51	22.35	23.00	23.48
	8H	21.81	22.40	22.33	22.91	23.40	21.81	22.40	22.33	22.91	23.40
	12H	21.79	22.30	22.30	22.79	23.36	21.79	22.30	22.30	22.79	23.36
12H	4H	21.90	22.61	22.38	23.09	23.56	21.90	22.61	22.38	23.09	23.56
	6H	21.81	22.40	22.33	22.91	23.39	21.81	22.40	22.33	22.91	23.39
	8H	21.79	22.30	22.30	22.79	23.36	21.79	22.30	22.30	22.79	23.36