

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245393

Luminaire Tested: PRLX-UNA-M-927-06L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-M-927-06L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, OPEN WEAVE SHADE TEXTU
LIGHT LEVEL 4
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 526.7 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245393
CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

Luminous Intensity Polar Plot



TEST NUMBER: P1245393

CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	55
1	95	90	84	79	88	83	78	74	70	67	64		59	56	54		48	46	45	39
2	86	77	70	63	79	71	65	59	61	56	51		51	47	43		42	39	36	31
3	78	68	59	53	72	63	55	49	53	48	43		45	40	36		37	33	30	26
4	72	60	51	45	66	56	48	42	48	42	37		40	35	32		33	30	27	23
5	67	54	45	39	61	50	43	37	43	37	32		37	32	28		31	27	24	21
6	62	49	41	34	57	46	38	33	40	33	29		34	29	25		28	25	22	19
7	58	45	37	31	53	42	35	29	37	31	26		31	27	23		27	23	20	17
8	54	41	34	28	50	39	32	27	34	28	24		29	25	21		25	21	19	16
9	51	38	31	26	47	36	29	25	32	26	22		28	23	20		24	20	17	15
10	48	36	29	24	45	34	27	23	30	24	21		26	22	19		23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50376
5°	25498
10°	4897
15°	1644
20°	982
25°	749
30°	617
35°	556
40°	507
45°	488
50°	474
55°	465
60°	469
65°	467
70°	477
75°	491
80°	500
85°	513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 531 cd/sqm



TEST NUMBER: P1245393

CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	8.3
10°-20°	21.0	4.0
20°-30°	18.1	3.4
30°-40°	21.8	4.1
40°-50°	26.9	5.1
50°-60°	32.7	6.2
60°-70°	38.2	7.3
70°-80°	43.3	8.2
80°-90°	46.5	8.8
90°-100°	47.7	9.1
100°-110°	46.5	8.8
110°-120°	42.2	8.0
120°-130°	35.5	6.7
130°-140°	27.4	5.2
140°-150°	18.9	3.6
150°-160°	11.0	2.1
160°-170°	4.7	0.9
170°-180°	0.7	0.1
0°-30°	82.7	15.7
0°-40°	104.5	19.8
0°-60°	164.1	31.2
0°-90°	292.1	55.5
90°-120°	136.4	25.9
90°-150°	218.2	41.4
90°-180°	235.0	44.6
0°-180°	526.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	983	
5°	677	44
15°	66	21
25°	39	18
35°	35	22
45°	35	27
55°	36	33
65°	38	38
75°	41	43
85°	43	35
90°	43	24
95°	44	36
105°	44	46
115°	43	42
125°	40	36
135°	36	27
145°	30	19
155°	24	11
165°	16	5
175°	5	1
180°	1	

TEST NUMBER: P1245393

CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	983.0
2.5°	1059.2
5°	677.0
7.5°	236.2
10°	163.5
12.5°	93.6
15°	65.7
17.5°	53.1
20°	45.4
22.5°	41.2
25°	39.1
27.5°	37.0
30°	35.6
32.5°	34.9
35°	34.9
37.5°	34.2
40°	34.2
42.5°	34.2
45°	34.9
47.5°	34.9
50°	35.6
52.5°	35.6
55°	36.3
57.5°	37.0
60°	37.7
62.5°	37.7
65°	38.4
67.5°	39.1
70°	39.8
72.5°	40.5
75°	41.2
77.5°	41.2
80°	41.9
82.5°	42.6
85°	42.6
87.5°	42.6
90°	43.3
92.5°	43.3
95°	44.0
97.5°	44.0
100°	44.0
102.5°	44.0
105°	44.0
107.5°	44.0
110°	43.3



TEST NUMBER: P1245393

CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	43.3
115°	42.6
117.5°	41.9
120°	41.2
122.5°	40.5
125°	39.8
127.5°	38.4
130°	37.7
132.5°	36.3
135°	35.6
137.5°	34.2
140°	32.8
142.5°	31.4
145°	30.0
147.5°	28.6
150°	27.2
152.5°	25.2
155°	23.8
157.5°	21.7
160°	20.3
162.5°	18.2
165°	16.1
167.5°	14.0
170°	11.9
172.5°	8.4
175°	4.9
177.5°	2.1
180°	0.7



TEST NUMBER: P1245393

CATALOG NUMBER: PRLX-UNA-M-927-06L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.5	5.5	5.4	6.4	7.6	4.5	5.5	5.4	6.4	7.6
	3H	7.5	8.4	8.4	9.4	10.6	7.5	8.4	8.4	9.4	10.6
	4H	9.0	9.9	9.9	10.8	12.0	9.0	9.9	9.9	10.8	12.0
	6H	10.5	11.3	11.4	12.2	13.5	10.5	11.3	11.4	12.2	13.5
	8H	11.2	12.0	12.1	12.9	14.2	11.2	12.0	12.1	12.9	14.2
	12H	11.9	12.6	12.8	13.6	14.8	11.9	12.6	12.8	13.6	14.8
4H	2H	5.3	6.1	6.2	7.1	8.3	5.3	6.1	6.2	7.1	8.3
	3H	8.5	9.2	9.4	10.2	11.4	8.5	9.2	9.4	10.2	11.4
	4H	10.1	10.8	11.0	11.8	13.0	10.1	10.8	11.0	11.8	13.0
	6H	11.7	12.4	12.7	13.4	14.6	11.7	12.4	12.7	13.4	14.6
	8H	12.5	13.1	13.5	14.1	15.4	12.5	13.1	13.5	14.1	15.4
	12H	13.3	13.9	14.3	14.9	16.2	13.3	13.9	14.3	14.9	16.2
8H	4H	10.6	11.2	11.6	12.2	13.5	10.6	11.2	11.6	12.2	13.5
	6H	12.5	13.0	13.4	14.0	15.3	12.5	13.0	13.4	14.0	15.3
	8H	13.4	13.9	14.4	14.9	16.2	13.4	13.9	14.4	14.9	16.2
	12H	14.4	14.8	15.4	15.8	17.1	14.4	14.8	15.4	15.8	17.1
12H	4H	10.7	11.3	11.7	12.3	13.6	10.7	11.3	11.7	12.3	13.6
	6H	12.7	13.1	13.6	14.1	15.4	12.7	13.1	13.6	14.1	15.4
	8H	13.7	14.1	14.7	15.1	16.4	13.7	14.1	14.7	15.1	16.4

(END OF REPORT)