

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980232

Luminaire Tested: PRLX-243-927-18L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P980232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-927-18L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1136.2 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.31
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980232

CATALOG NUMBER: PRLX-243-927-18L-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P980232

CATALOG NUMBER: PRLX-243-927-18L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	67	62	71	66	61		70	64	60		68
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63
7	74	62	55	50	72	62	55	50	60	54	49		59	53	49		58
8	69	57	50	45	68	57	50	45	56	49	45		54	49	44		53
9	65	53	46	41	64	52	46	41	51	45	41		50	45	40		49
10	61	49	42	37	60	49	42	37	48	41	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3126
5°	3099
10°	3042
15°	2970
20°	2920
25°	2873
30°	2819
35°	2781
40°	2739
45°	2693
50°	2215
55°	523
60°	31
65°	30
70°	38
75°	40
80°	28
85°	28

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2693 cd/sqm

TEST NUMBER: P980232

CATALOG NUMBER: PRLX-243-927-18L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	5.2
10°-20°	164.2	14.5
20°-30°	243.1	21.4
30°-40°	288.9	25.4
40°-50°	290.1	25.5
50°-60°	85.5	7.5
60°-70°	2.6	0.2
70°-80°	2.0	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.4	41.0
0°-40°	755.3	66.5
0°-60°	1130.9	99.5
0°-90°	1136.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1136.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	626	59
15°	581	164
25°	528	243
35°	462	289
45°	386	290
55°	61	85
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P980232

CATALOG NUMBER: PRLX-243-927-18L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	633.5
2.5°	631.9
5°	625.7
7.5°	617.0
10°	607.2
12.5°	595.3
15°	581.4
17.5°	569.0
20°	556.1
22.5°	543.3
25°	527.8
27.5°	511.3
30°	494.8
32.5°	478.3
35°	461.8
37.5°	444.8
40°	425.2
42.5°	406.7
45°	386.0
47.5°	355.6
50°	288.6
52.5°	174.2
55°	60.8
57.5°	11.9
60°	3.1
62.5°	2.6
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.1
75°	2.1
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

TEST NUMBER: P980232

CATALOG NUMBER: PRLX-243-927-18L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT