

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245406

Luminaire Tested: PRLX-UNA-M-930-04L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-M-930-04L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 423.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	55
1	95	90	84	79	88	83	78	74	70	67	64		59	56	54		48	46	45	39
2	86	77	70	63	79	71	65	59	61	56	51		51	47	43		42	39	36	31
3	78	68	59	53	72	63	55	49	53	48	43		45	40	36		37	33	30	26
4	72	60	51	45	66	56	48	42	48	42	37		40	35	32		33	30	27	23
5	67	54	45	39	61	50	43	37	43	37	32		37	32	28		31	27	24	21
6	62	49	41	34	57	46	38	33	40	33	29		34	29	25		28	25	22	19
7	58	45	37	31	53	42	35	29	37	31	26		31	27	23		27	23	20	17
8	54	41	34	28	50	39	32	27	34	28	24		29	25	21		25	21	19	16
9	51	38	31	26	47	36	29	25	32	26	22		28	23	20		24	20	17	15
10	48	36	29	24	45	34	27	23	30	24	21		26	22	19		23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40434
5°	20466
10°	3930
15°	1318
20°	789
25°	602
30°	496
35°	446
40°	408
45°	392
50°	381
55°	374
60°	377
65°	375
70°	384
75°	395
80°	401
85°	412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 426 cd/sqm



TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	8.3
10°-20°	16.8	4.0
20°-30°	14.6	3.4
30°-40°	17.5	4.1
40°-50°	21.6	5.1
50°-60°	26.2	6.2
60°-70°	30.7	7.3
70°-80°	34.8	8.2
80°-90°	37.3	8.8
90°-100°	38.3	9.1
100°-110°	37.3	8.8
110°-120°	33.9	8.0
120°-130°	28.5	6.7
130°-140°	22.0	5.2
140°-150°	15.2	3.6
150°-160°	8.8	2.1
160°-170°	3.8	0.9
170°-180°	0.6	0.1
0°-30°	66.4	15.7
0°-40°	83.9	19.8
0°-60°	131.8	31.2
0°-90°	234.6	55.5
90°-120°	109.5	25.9
90°-150°	175.2	41.4
90°-180°	188.0	44.4
0°-180°	423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	789	
5°	543	35
15°	53	17
25°	31	15
35°	28	18
45°	28	22
55°	29	26
65°	31	31
75°	33	35
85°	34	28
90°	35	19
95°	35	29
105°	35	37
115°	34	34
125°	32	29
135°	29	22
145°	24	15
155°	19	9
165°	13	4
175°	4	1
180°	1	

TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	789.0
2.5°	850.2
5°	543.4
7.5°	189.5
10°	131.2
12.5°	75.1
15°	52.7
17.5°	42.6
20°	36.5
22.5°	33.1
25°	31.4
27.5°	29.7
30°	28.6
32.5°	28.0
35°	28.0
37.5°	27.5
40°	27.5
42.5°	27.5
45°	28.0
47.5°	28.0
50°	28.6
52.5°	28.6
55°	29.2
57.5°	29.7
60°	30.3
62.5°	30.3
65°	30.8
67.5°	31.4
70°	32.0
72.5°	32.5
75°	33.1
77.5°	33.1
80°	33.6
82.5°	34.2
85°	34.2
87.5°	34.2
90°	34.8
92.5°	34.8
95°	35.3
97.5°	35.3
100°	35.3
102.5°	35.3
105°	35.3
107.5°	35.3
110°	34.8

TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	34.8
115°	34.2
117.5°	33.6
120°	33.1
122.5°	32.5
125°	32.0
127.5°	30.8
130°	30.3
132.5°	29.2
135°	28.6
137.5°	27.5
140°	26.4
142.5°	25.2
145°	24.1
147.5°	23.0
150°	21.9
152.5°	20.2
155°	19.1
157.5°	17.4
160°	16.3
162.5°	14.6
165°	12.9
167.5°	11.2
170°	9.5
172.5°	6.7
175°	3.9
177.5°	1.7
180°	0.6



TEST NUMBER: P1245406

CATALOG NUMBER: PRLX-UNA-M-930-04L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.7	4.7	4.6	5.7	6.8	3.7	4.7	4.6	5.7	6.8
	3H	6.7	7.7	7.6	8.6	9.8	6.7	7.7	7.6	8.6	9.8
	4H	8.2	9.1	9.2	10.1	11.3	8.2	9.1	9.2	10.1	11.3
	6H	9.7	10.5	10.6	11.5	12.7	9.7	10.5	10.6	11.5	12.7
	8H	10.4	11.2	11.3	12.2	13.4	10.4	11.2	11.3	12.2	13.4
	12H	11.1	11.9	12.1	12.8	14.1	11.1	11.9	12.1	12.8	14.1
4H	2H	4.5	5.4	5.4	6.3	7.5	4.5	5.4	5.4	6.3	7.5
	3H	7.7	8.5	8.6	9.4	10.7	7.7	8.5	8.6	9.4	10.7
	4H	9.3	10.1	10.3	11.0	12.3	9.3	10.1	10.3	11.0	12.3
	6H	11.0	11.6	11.9	12.6	13.8	11.0	11.6	11.9	12.6	13.8
	8H	11.8	12.4	12.7	13.4	14.6	11.8	12.4	12.7	13.4	14.6
	12H	12.6	13.1	13.6	14.1	15.4	12.6	13.1	13.6	14.1	15.4
8H	4H	9.9	10.5	10.8	11.4	12.7	9.9	10.5	10.8	11.4	12.7
	6H	11.7	12.2	12.7	13.2	14.5	11.7	12.2	12.7	13.2	14.5
	8H	12.7	13.1	13.6	14.1	15.4	12.7	13.1	13.6	14.1	15.4
	12H	13.6	14.1	14.6	15.1	16.4	13.6	14.1	14.6	15.1	16.4
12H	4H	10.0	10.5	10.9	11.5	12.8	10.0	10.5	10.9	11.5	12.8
	6H	11.9	12.4	12.9	13.4	14.7	11.9	12.4	12.9	13.4	14.7
	8H	12.9	13.4	13.9	14.4	15.7	12.9	13.4	13.9	14.4	15.7

(END OF REPORT)