

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980220

Luminaire Tested: PRLX-243-927-LL1-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-927-LL1-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 865.0 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.34
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct


Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980220

CATALOG NUMBER: PRLX-243-927-LL1-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P980220

CATALOG NUMBER: PRLX-243-927-LL1-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	99	95	91	103	98	93	89	94	91	87		91	88	86		88
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82
4	92	83	76	71	90	81	75	70	79	74	69		77	72	69		75
5	86	75	68	63	84	74	68	63	73	67	62		71	66	62		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59
8	70	58	51	46	69	58	51	46	57	50	46		55	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	62	50	43	38	61	50	43	38	49	43	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2481
5°	2424
10°	2348
15°	2294
20°	2270
25°	2259
30°	2246
35°	2245
40°	2241
45°	2241
50°	1299
55°	115
60°	18
65°	21
70°	26
75°	27
80°	20
85°	23

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2241 cd/sqm

TEST NUMBER: P980220

CATALOG NUMBER: PRLX-243-927-LL1-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	5.3
10°-20°	127.0	14.7
20°-30°	191.3	22.1
30°-40°	233.2	27.0
40°-50°	234.4	27.1
50°-60°	29.3	3.4
60°-70°	1.8	0.2
70°-80°	1.5	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.4	42.1
0°-40°	597.6	69.1
0°-60°	861.2	99.6
0°-90°	865.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	865.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	503	
5°	489	46
15°	449	127
25°	415	191
35°	373	233
45°	321	234
55°	13	29
65°	2	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P980220

CATALOG NUMBER: PRLX-243-927-LL1-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	502.8
2.5°	500.7
5°	489.4
7.5°	477.8
10°	468.6
12.5°	459.8
15°	449.2
17.5°	440.4
20°	432.3
22.5°	424.9
25°	415.0
27.5°	404.8
30°	394.2
32.5°	383.6
35°	372.7
37.5°	361.1
40°	348.0
42.5°	334.6
45°	321.2
47.5°	303.2
50°	169.2
52.5°	32.1
55°	13.4
57.5°	4.2
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.4
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

TEST NUMBER: P980220

CATALOG NUMBER: PRLX-243-927-LL1-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT