

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980231

Luminaire Tested: PRLX-243-927-LL2-C-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-31)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-927-LL2-C-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 243 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1669.6 lumens
Efficiency: N/A
Efficacy: 151.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.38
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980231
CATALOG NUMBER: PRLX-243-927-LL2-C-U-S-WHTE-X

Luminous Intensity Polar Plot





TEST NUMBER: P980231

CATALOG NUMBER: PRLX-243-927-LL2-C-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68				68
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	60				60
5	82	71	63	57	80	70	63	57	68	61	56	66	60	56	64	59	55	53				53
6	76	65	57	51	75	64	56	51	62	55	50	60	55	50	59	54	50	48				48
7	71	59	51	46	70	58	51	46	57	50	45	56	49	45	54	49	45	43				43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39				39
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4081
5°	4000
10°	3904
15°	3830
20°	3813
25°	3816
30°	3808
35°	3828
40°	3851
45°	3884
50°	2698
55°	878
60°	732
65°	794
70°	870
75°	904
80°	864
85°	877

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3884 cd/sqm

TEST NUMBER: P980231

CATALOG NUMBER: PRLX-243-927-LL2-C-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	4.6
10°-20°	212.3	12.7
20°-30°	323.0	19.3
30°-40°	398.0	23.8
40°-50°	408.3	24.5
50°-60°	118.6	7.1
60°-70°	67.1	4.0
70°-80°	49.1	2.9
80°-90°	16.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.5	36.6
0°-40°	1009.5	60.5
0°-60°	1536.5	92.0
0°-90°	1669.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1669.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	827	
5°	808	76
15°	750	212
25°	701	323
35°	636	398
45°	557	408
55°	102	119
65°	68	67
75°	47	49
85°	16	17
90°	0	

TEST NUMBER: P980231

CATALOG NUMBER: PRLX-243-927-LL2-C-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	827.2
2.5°	824.7
5°	807.7
7.5°	791.7
10°	779.3
12.5°	765.4
15°	749.9
17.5°	739.1
20°	726.2
22.5°	715.4
25°	701.0
27.5°	684.5
30°	668.5
32.5°	653.0
35°	635.5
37.5°	618.0
40°	597.9
42.5°	578.8
45°	556.7
47.5°	509.8
50°	351.5
52.5°	138.1
55°	102.1
57.5°	84.0
60°	74.2
62.5°	71.1
65°	68.0
67.5°	64.4
70°	60.3
72.5°	54.6
75°	47.4
77.5°	38.7
80°	30.4
82.5°	22.7
85°	15.5
87.5°	8.8
90°	0.0



TEST NUMBER: P980231
 CATALOG NUMBER: PRLX-243-927-LL2-C-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.41	8.82	7.77	9.13	9.45	7.41	8.82	7.77	9.13	9.45
	3H	9.83	11.08	10.21	11.41	11.78	9.83	11.08	10.21	11.41	11.78
	4H	10.89	12.06	11.29	12.41	12.79	10.89	12.06	11.29	12.41	12.79
	6H	11.67	12.75	12.09	13.12	13.51	11.67	12.75	12.09	13.12	13.51
	8H	11.95	12.98	12.38	13.37	13.77	11.95	12.98	12.38	13.37	13.77
	12H	12.17	13.15	12.60	13.53	13.96	12.17	13.15	12.60	13.53	13.96
4H	2H	8.16	9.33	8.56	9.68	10.06	8.16	9.33	8.56	9.68	10.06
	3H	10.85	11.81	11.26	12.21	12.61	10.85	11.81	11.26	12.21	12.61
	4H	12.04	12.90	12.48	13.32	13.76	12.04	12.90	12.48	13.32	13.76
	6H	12.96	13.70	13.42	14.15	14.61	12.96	13.70	13.42	14.15	14.61
	8H	13.29	13.98	13.75	14.43	14.90	13.29	13.98	13.75	14.43	14.90
	12H	13.55	14.17	14.04	14.66	15.13	13.55	14.17	14.04	14.66	15.13
8H	4H	12.47	13.16	12.93	13.61	14.08	12.47	13.16	12.93	13.61	14.08
	6H	13.52	14.10	14.02	14.59	15.07	13.52	14.10	14.02	14.59	15.07
	8H	13.94	14.47	14.46	14.98	15.47	13.94	14.47	14.46	14.98	15.47
	12H	14.32	14.78	14.83	15.28	15.84	14.32	14.78	14.83	15.28	15.84
12H	4H	12.51	13.13	13.00	13.62	14.09	12.51	13.13	13.00	13.62	14.09
	6H	13.61	14.13	14.12	14.64	15.13	13.61	14.13	14.12	14.64	15.13
	8H	14.10	14.57	14.61	15.06	15.63	14.10	14.57	14.61	15.06	15.63