

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245478

Luminaire Tested: PRLX-UNA-S-935-05L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-UNA-S-935-05L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 503.0 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Rectangular w/ Sides (W: 0.47' x L: 0.47' x H: 1.12')
CIE Type: Semi-Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92		81	81	81		71	71	71	66
1	99	94	89	84	93	88	84	80	78	74	71		68	65	63		59	57	55	51
2	90	81	74	68	84	77	70	65	68	63	58		59	55	52		52	49	46	42
3	82	72	64	57	77	68	60	55	60	54	49		53	48	44		46	43	40	36
4	76	64	56	49	71	61	53	47	54	48	43		48	43	39		42	38	35	32
5	70	58	49	43	66	55	47	41	49	43	38		44	38	34		38	34	31	28
6	65	53	44	38	61	50	42	37	45	39	34		40	35	31		36	32	28	26
7	61	48	40	35	57	46	39	33	42	35	31		37	32	28		33	29	26	24
8	57	45	37	31	54	43	35	30	39	33	28		35	30	26		31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26		33	28	24		30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24		31	26	23		28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23553
5°	21857
10°	5854
15°	3818
20°	2685
25°	1875
30°	1461
35°	1223
40°	1074
45°	970
50°	890
55°	828
60°	783
65°	745
70°	713
75°	686
80°	649
85°	631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 970 cd/sqm

TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.3	8.4
10°-20°	34.8	6.9
20°-30°	34.6	6.9
30°-40°	34.7	6.9
40°-50°	36.9	7.3
50°-60°	38.6	7.7
60°-70°	39.2	7.8
70°-80°	38.2	7.6
80°-90°	35.0	7.0
90°-100°	34.6	6.9
100°-110°	33.1	6.6
110°-120°	30.0	6.0
120°-130°	25.1	5.0
130°-140°	19.5	3.9
140°-150°	13.7	2.7
150°-160°	8.4	1.7
160°-170°	3.9	0.8
170°-180°	0.6	0.1
0°-30°	111.7	22.2
0°-40°	146.4	29.1
0°-60°	221.8	44.1
0°-90°	334.2	66.4
90°-120°	97.7	19.4
90°-150°	155.9	31.0
90°-180°	169.0	33.6
0°-180°	503.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	481	
5°	538	42
15°	124	35
25°	74	35
35°	55	35
45°	48	37
55°	43	39
65°	40	39
75°	36	38
85°	32	26
90°	32	17
95°	32	26
105°	32	33
115°	30	30
125°	28	25
135°	25	19
145°	22	14
155°	18	8
165°	14	4
175°	5	1
180°	1	

TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	480.8
2.5°	522.1
5°	537.8
7.5°	510.6
10°	167.5
12.5°	136.9
15°	123.7
17.5°	111.4
20°	96.5
22.5°	82.9
25°	73.5
27.5°	67.2
30°	61.6
32.5°	58.2
35°	54.8
37.5°	52.7
40°	50.6
42.5°	48.9
45°	47.6
47.5°	46.3
50°	45.1
52.5°	44.2
55°	42.9
57.5°	42.1
60°	41.2
62.5°	40.4
65°	39.5
67.5°	38.7
70°	37.8
72.5°	37.4
75°	36.1
77.5°	35.3
80°	33.6
82.5°	32.3
85°	31.9
87.5°	31.5
90°	31.5
92.5°	31.5
95°	31.9
97.5°	31.9
100°	31.5
102.5°	31.5
105°	31.5
107.5°	31.0
110°	31.0

TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	30.6
115°	30.2
117.5°	29.8
120°	29.3
122.5°	28.5
125°	28.1
127.5°	27.2
130°	26.8
132.5°	25.9
135°	25.1
137.5°	24.2
140°	23.4
142.5°	22.5
145°	21.7
147.5°	20.8
150°	20.0
152.5°	19.1
155°	17.9
157.5°	17.0
160°	15.7
162.5°	14.9
165°	13.6
167.5°	11.9
170°	9.8
172.5°	7.7
175°	5.1
177.5°	2.6
180°	1.3



TEST NUMBER: P1245478

CATALOG NUMBER: PRLX-UNA-S-935-05L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.4	8.5	8.2	9.3	10.3	7.4	8.5	8.2	9.3	10.3
	3H	9.8	10.8	10.6	11.6	12.7	9.8	10.8	10.6	11.6	12.7
	4H	11.0	11.9	11.8	12.8	13.8	11.0	11.9	11.8	12.8	13.8
	6H	12.1	13.0	12.9	13.8	14.9	12.1	13.0	12.9	13.8	14.9
	8H	12.6	13.4	13.4	14.3	15.4	12.6	13.4	13.4	14.3	15.4
	12H	13.1	13.9	13.9	14.8	15.9	13.1	13.9	13.9	14.8	15.9
4H	2H	8.0	8.9	8.8	9.8	10.8	8.0	8.9	8.8	9.8	10.8
	3H	10.7	11.5	11.5	12.3	13.4	10.7	11.5	11.5	12.3	13.4
	4H	12.0	12.7	12.8	13.6	14.7	12.0	12.7	12.8	13.6	14.7
	6H	13.3	13.9	14.1	14.8	15.9	13.3	13.9	14.1	14.8	15.9
	8H	13.9	14.5	14.7	15.4	16.5	13.9	14.5	14.7	15.4	16.5
	12H	14.5	15.0	15.3	15.9	17.0	14.5	15.0	15.3	15.9	17.0
8H	4H	12.4	13.0	13.3	13.9	15.0	12.4	13.0	13.3	13.9	15.0
	6H	13.9	14.4	14.8	15.3	16.4	13.9	14.4	14.8	15.3	16.4
	8H	14.6	15.1	15.5	16.0	17.1	14.6	15.1	15.5	16.0	17.1
	12H	15.4	15.8	16.3	16.7	17.9	15.4	15.8	16.3	16.7	17.9
12H	4H	12.5	13.0	13.4	14.0	15.1	12.5	13.0	13.4	14.0	15.1
	6H	14.0	14.5	14.9	15.4	16.6	14.0	14.5	14.9	15.4	16.6
	8H	14.8	15.2	15.7	16.2	17.3	14.8	15.2	15.7	16.2	17.3

(END OF REPORT)