

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980340

Luminaire Tested: PRLX-243-930-43L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P980340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-930-43L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3256.7 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.34
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980340

CATALOG NUMBER: PRLX-243-930-43L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P980340

CATALOG NUMBER: PRLX-243-930-43L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	99	95	91	103	98	93	89	94	91	88		91	88	86		88
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82
4	92	83	76	71	90	81	75	70	79	74	69		77	72	69		75
5	86	75	68	63	84	74	68	63	73	67	62		71	66	62		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59
8	70	58	51	46	69	58	51	46	57	50	46		55	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	62	50	43	38	61	50	43	38	49	43	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9341
5°	9127
10°	8840
15°	8640
20°	8547
25°	8507
30°	8457
35°	8453
40°	8440
45°	8439
50°	4892
55°	434
60°	65
65°	77
70°	95
75°	101
80°	77
85°	74

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8439 cd/sqm

TEST NUMBER: P980340

CATALOG NUMBER: PRLX-243-930-43L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	5.3
10°-20°	478.3	14.7
20°-30°	720.4	22.1
30°-40°	878.1	27.0
40°-50°	882.5	27.1
50°-60°	110.2	3.4
60°-70°	6.6	0.2
70°-80°	5.4	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1372.0	42.1
0°-40°	2250.2	69.1
0°-60°	3242.9	99.6
0°-90°	3256.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3256.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1893	
5°	1843	173
15°	1692	478
25°	1563	720
35°	1403	878
45°	1210	883
55°	50	110
65°	7	7
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P980340

CATALOG NUMBER: PRLX-243-930-43L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1893.3
2.5°	1885.3
5°	1842.9
7.5°	1799.0
10°	1764.5
12.5°	1731.3
15°	1691.5
17.5°	1658.3
20°	1627.8
22.5°	1599.9
25°	1562.7
27.5°	1524.2
30°	1484.4
32.5°	1444.5
35°	1403.4
37.5°	1359.6
40°	1310.5
42.5°	1260.0
45°	1209.5
47.5°	1141.8
50°	637.3
52.5°	120.8
55°	50.5
57.5°	15.9
60°	6.6
62.5°	6.6
65°	6.6
67.5°	6.6
70°	6.6
72.5°	6.6
75°	5.3
77.5°	4.0
80°	2.7
82.5°	2.7
85°	1.3
87.5°	1.3
90°	0.0

TEST NUMBER: P980340

CATALOG NUMBER: PRLX-243-930-43L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT