

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245364

Luminaire Tested: PRLX-UNA-L-940-05L-U-PS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-UNA-L-940-05L-U-PS  
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 2  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 547.0 lumens  
Efficiency: N/A  
Efficacy: 37.0 lumens/watt  
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.2  
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')  
CIE Type: General Diffuse  
  
Input Watts (W): 14.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

### Luminous Intensity Polar Plot





TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	57
1	96	90	85	80	88	83	79	75	71	68	64		60	57	55		49	47	46	40
2	86	77	70	63	80	72	65	59	61	56	51		51	47	44		42	39	37	32
3	79	68	59	52	72	63	55	49	54	48	43		45	40	37		37	34	31	27
4	72	60	51	44	66	56	48	42	48	41	37		40	35	31		33	30	27	23
5	66	54	45	38	61	50	42	36	43	37	32		36	31	28		30	27	23	20
6	61	48	40	34	57	45	37	32	39	33	28		33	28	25		28	24	21	18
7	57	44	36	30	53	41	34	28	36	30	25		31	26	22		26	22	19	17
8	53	41	33	27	49	38	31	26	33	27	23		29	24	20		24	21	18	15
9	50	37	30	25	46	35	28	23	31	25	21		27	22	19		23	19	16	14
10	47	35	27	22	44	33	26	21	29	23	19		25	21	17		22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	23275
5°	10907
10°	3067
15°	1440
20°	949
25°	706
30°	580
35°	507
40°	457
45°	429
50°	409
55°	398
60°	391
65°	390
70°	388
75°	390
80°	386
85°	392

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 429 cd/sqm

TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.8	6.0
10°-20°	24.6	4.5
20°-30°	24.0	4.4
30°-40°	27.3	5.0
40°-50°	31.9	5.8
50°-60°	37.0	6.8
60°-70°	41.5	7.6
70°-80°	44.6	8.1
80°-90°	45.5	8.3
90°-100°	46.7	8.5
100°-110°	45.7	8.4
110°-120°	41.8	7.6
120°-130°	35.6	6.5
130°-140°	28.1	5.1
140°-150°	20.1	3.7
150°-160°	12.6	2.3
160°-170°	6.1	1.1
170°-180°	1.3	0.2
0°-30°	81.4	14.9
0°-40°	108.6	19.9
0°-60°	177.4	32.4
0°-90°	309.1	56.5
90°-120°	134.1	24.5
90°-150°	217.9	39.8
90°-180°	238.0	43.5
0°-180°	547.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	736	
5°	442	33
15°	83	25
25°	51	24
35°	43	27
45°	41	32
55°	41	37
65°	42	42
75°	42	45
85°	42	34
90°	42	23
95°	43	35
105°	43	46
115°	42	42
125°	40	36
135°	36	28
145°	32	20
155°	27	13
165°	22	6
175°	11	1
180°	7	

TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	735.7
2.5°	798.3
5°	442.2
7.5°	205.1
10°	150.8
12.5°	103.8
15°	82.7
17.5°	70.5
20°	61.9
22.5°	55.6
25°	51.2
27.5°	48.2
30°	46.0
32.5°	44.5
35°	43.3
37.5°	42.3
40°	41.6
42.5°	41.4
45°	41.1
47.5°	40.9
50°	40.9
52.5°	41.1
55°	41.1
57.5°	41.4
60°	41.4
62.5°	41.6
65°	41.9
67.5°	42.1
70°	42.1
72.5°	42.3
75°	42.3
77.5°	42.1
80°	41.6
82.5°	41.6
85°	41.6
87.5°	41.9
90°	42.1
92.5°	42.6
95°	42.8
97.5°	43.1
100°	43.3
102.5°	43.3
105°	43.3
107.5°	43.1
110°	42.8

TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	42.6
115°	42.1
117.5°	41.6
120°	41.1
122.5°	40.4
125°	39.6
127.5°	38.9
130°	38.2
132.5°	37.2
135°	36.2
137.5°	35.2
140°	34.0
142.5°	33.0
145°	31.8
147.5°	30.8
150°	29.6
152.5°	28.4
155°	27.2
157.5°	25.9
160°	24.5
162.5°	23.3
165°	21.5
167.5°	19.6
170°	17.1
172.5°	14.4
175°	11.3
177.5°	8.3
180°	7.3



TEST NUMBER: P1245364

CATALOG NUMBER: PRLX-UNA-L-940-05L-U-PS

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.2	5.2	5.1	6.2	7.3	4.2	5.2	5.1	6.2	7.3
	3H	7.1	8.0	8.0	8.9	10.1	7.1	8.0	8.0	8.9	10.1
	4H	8.4	9.3	9.3	10.3	11.5	8.4	9.3	9.3	10.3	11.5
	6H	9.8	10.6	10.7	11.5	12.8	9.8	10.6	10.7	11.5	12.8
	8H	10.4	11.2	11.3	12.2	13.4	10.4	11.2	11.3	12.2	13.4
	12H	11.0	11.8	12.0	12.8	14.0	11.0	11.8	12.0	12.8	14.0
4H	2H	5.0	5.8	5.9	6.8	8.0	5.0	5.8	5.9	6.8	8.0
	3H	8.0	8.8	8.9	9.7	10.9	8.0	8.8	8.9	9.7	10.9
	4H	9.5	10.2	10.4	11.2	12.4	9.5	10.2	10.4	11.2	12.4
	6H	11.0	11.7	12.0	12.6	13.9	11.0	11.7	12.0	12.6	13.9
	8H	11.8	12.4	12.7	13.3	14.6	11.8	12.4	12.7	13.3	14.6
	12H	12.5	13.0	13.4	14.0	15.3	12.5	13.0	13.4	14.0	15.3
8H	4H	10.0	10.6	10.9	11.6	12.8	10.0	10.6	10.9	11.6	12.8
	6H	11.7	12.2	12.7	13.2	14.5	11.7	12.2	12.7	13.2	14.5
	8H	12.6	13.1	13.6	14.0	15.3	12.6	13.1	13.6	14.0	15.3
	12H	13.5	13.9	14.5	14.9	16.2	13.5	13.9	14.5	14.9	16.2
12H	4H	10.1	10.6	11.1	11.6	12.9	10.1	10.6	11.1	11.6	12.9
	6H	11.9	12.3	12.9	13.3	14.6	11.9	12.3	12.9	13.3	14.6
	8H	12.8	13.3	13.8	14.2	15.6	12.8	13.3	13.8	14.2	15.6

(END OF REPORT)