

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245433

Luminaire Tested: PRLX-UNA-M-940-03L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-M-940-03L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 312.0 lumens
Efficiency: N/A
Efficacy: 28.1 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	55
1	95	90	84	79	88	83	78	74	70	67	64		59	56	54		48	46	45	39
2	86	77	70	63	79	71	65	59	61	56	51		51	47	43		42	39	36	31
3	78	68	59	53	72	63	55	49	53	48	43		45	40	36		37	33	30	26
4	72	60	51	45	66	56	48	42	48	42	37		40	35	32		33	30	27	23
5	67	54	45	39	61	50	43	37	43	37	32		37	32	28		31	27	24	21
6	62	49	41	34	57	46	38	33	40	33	29		34	29	25		28	25	22	19
7	58	45	37	31	53	42	35	29	37	31	26		31	27	23		27	23	20	17
8	54	41	34	28	50	39	32	27	34	28	24		29	25	21		25	21	19	16
9	51	38	31	26	47	36	29	25	32	26	22		28	23	20		24	20	17	15
10	48	36	29	24	45	34	27	23	30	24	21		26	22	19		23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29826
5°	15095
10°	2899
15°	973
20°	582
25°	445
30°	366
35°	330
40°	301
45°	289
50°	281
55°	275
60°	277
65°	277
70°	283
75°	291
80°	296
85°	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 314 cd/sqm

TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	8.3
10°-20°	12.4	4.0
20°-30°	10.7	3.4
30°-40°	12.9	4.1
40°-50°	16.0	5.1
50°-60°	19.3	6.2
60°-70°	22.7	7.3
70°-80°	25.7	8.2
80°-90°	27.5	8.8
90°-100°	28.3	9.1
100°-110°	27.5	8.8
110°-120°	25.0	8.0
120°-130°	21.0	6.7
130°-140°	16.2	5.2
140°-150°	11.2	3.6
150°-160°	6.5	2.1
160°-170°	2.8	0.9
170°-180°	0.4	0.1
0°-30°	49.0	15.7
0°-40°	61.9	19.8
0°-60°	97.2	31.2
0°-90°	173.0	55.5
90°-120°	80.8	25.9
90°-150°	129.3	41.4
90°-180°	139.0	44.5
0°-180°	312.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	582	
5°	401	26
15°	39	12
25°	23	11
35°	21	13
45°	21	16
55°	22	19
65°	23	23
75°	24	26
85°	25	21
90°	26	14
95°	26	21
105°	26	28
115°	25	25
125°	24	21
135°	21	16
145°	18	11
155°	14	7
165°	10	3
175°	3	0
180°	0	

TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	582.0
2.5°	627.1
5°	400.8
7.5°	139.8
10°	96.8
12.5°	55.4
15°	38.9
17.5°	31.4
20°	26.9
22.5°	24.4
25°	23.2
27.5°	21.9
30°	21.1
32.5°	20.7
35°	20.7
37.5°	20.3
40°	20.3
42.5°	20.3
45°	20.7
47.5°	20.7
50°	21.1
52.5°	21.1
55°	21.5
57.5°	21.9
60°	22.3
62.5°	22.3
65°	22.8
67.5°	23.2
70°	23.6
72.5°	24.0
75°	24.4
77.5°	24.4
80°	24.8
82.5°	25.2
85°	25.2
87.5°	25.2
90°	25.6
92.5°	25.6
95°	26.1
97.5°	26.1
100°	26.1
102.5°	26.1
105°	26.1
107.5°	26.1
110°	25.6



TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	25.6
115°	25.2
117.5°	24.8
120°	24.4
122.5°	24.0
125°	23.6
127.5°	22.8
130°	22.3
132.5°	21.5
135°	21.1
137.5°	20.3
140°	19.4
142.5°	18.6
145°	17.8
147.5°	17.0
150°	16.1
152.5°	14.9
155°	14.1
157.5°	12.8
160°	12.0
162.5°	10.8
165°	9.5
167.5°	8.3
170°	7.0
172.5°	5.0
175°	2.9
177.5°	1.2
180°	0.4



TEST NUMBER: P1245433

CATALOG NUMBER: PRLX-UNA-M-940-03L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.7	3.7	3.6	4.6	5.8	2.7	3.7	3.6	4.6	5.8
	3H	5.7	6.6	6.6	7.5	8.7	5.7	6.6	6.6	7.5	8.7
	4H	7.2	8.1	8.1	9.0	10.2	7.2	8.1	8.1	9.0	10.2
	6H	8.6	9.5	9.6	10.4	11.6	8.6	9.5	9.6	10.4	11.6
	8H	9.4	10.1	10.3	11.1	12.3	9.4	10.1	10.3	11.1	12.3
	12H	10.1	10.8	11.0	11.8	13.0	10.1	10.8	11.0	11.8	13.0
4H	2H	3.4	4.3	4.4	5.3	6.5	3.4	4.3	4.4	5.3	6.5
	3H	6.6	7.4	7.6	8.4	9.6	6.6	7.4	7.6	8.4	9.6
	4H	8.3	9.0	9.2	10.0	11.2	8.3	9.0	9.2	10.0	11.2
	6H	9.9	10.5	10.9	11.5	12.8	9.9	10.5	10.9	11.5	12.8
	8H	10.7	11.3	11.7	12.3	13.6	10.7	11.3	11.7	12.3	13.6
	12H	11.5	12.1	12.5	13.1	14.3	11.5	12.1	12.5	13.1	14.3
8H	4H	8.8	9.4	9.8	10.4	11.7	8.8	9.4	9.8	10.4	11.7
	6H	10.6	11.2	11.6	12.2	13.4	10.6	11.2	11.6	12.2	13.4
	8H	11.6	12.1	12.6	13.1	14.4	11.6	12.1	12.6	13.1	14.4
	12H	12.6	13.0	13.6	14.0	15.3	12.6	13.0	13.6	14.0	15.3
12H	4H	8.9	9.5	9.9	10.5	11.7	8.9	9.5	9.9	10.5	11.7
	6H	10.8	11.3	11.8	12.3	13.6	10.8	11.3	11.8	12.3	13.6
	8H	11.9	12.3	12.9	13.3	14.6	11.9	12.3	12.9	13.3	14.6

(END OF REPORT)