

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979231

Luminaire Tested: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

Issue Date: 4/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P979231  
TEST IS SCALED FROM ( LM79-2019 )  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE  
Description: PrentaLux 2-INCH CYLINDER, SPOT OPTIC  
1000 LUMENS  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 926.5 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.33  
Luminous Opening: Circular (Dia: 0.21' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

### Luminous Intensity Polar Plot



TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 112 | 110 | 109 | 112 | 110 | 108 | 107 | 106 | 105 | 104 |  | 103 | 101 | 100 |  | 99  |
| 2   | 111 | 107 | 103 | 101 | 108 | 105 | 102 | 100 | 102 | 100 | 97  |  | 99  | 97  | 95  |  | 96  |
| 3   | 107 | 102 | 98  | 95  | 105 | 100 | 97  | 94  | 98  | 95  | 92  |  | 95  | 93  | 91  |  | 93  |
| 4   | 103 | 97  | 93  | 90  | 101 | 96  | 92  | 89  | 94  | 91  | 88  |  | 92  | 89  | 87  |  | 90  |
| 5   | 100 | 93  | 89  | 86  | 98  | 92  | 88  | 85  | 91  | 87  | 84  |  | 89  | 86  | 84  |  | 88  |
| 6   | 96  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  |  | 86  | 83  | 81  |  | 85  |
| 7   | 93  | 86  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  |
| 8   | 90  | 83  | 79  | 76  | 89  | 83  | 79  | 76  | 82  | 78  | 75  |  | 81  | 78  | 75  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 76  | 73  |  | 79  | 75  | 73  |  | 78  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 71  |  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°      | 90°     | 180°    | 270°    |
|-----|---------|---------|---------|---------|
| 0°  | 1543791 | 1543791 | 1543791 | 1543791 |
| 5°  | 1381011 | 1298467 | 1182761 | 1261718 |
| 10° | 821608  | 730409  | 613808  | 693677  |
| 15° | 383669  | 335988  | 288950  | 322475  |
| 20° | 206499  | 188806  | 171642  | 186160  |
| 25° | 143503  | 133456  | 125775  | 133765  |
| 30° | 105645  | 95238   | 88528   | 94987   |
| 35° | 60701   | 52089   | 44767   | 51634   |
| 40° | 23935   | 19757   | 14807   | 19311   |
| 45° | 7384    | 6592    | 4834    | 6461    |
| 50° | 3626    | 3239    | 2804    | 3239    |
| 55° | 2655    | 2384    | 2167    | 2384    |
| 60° | 2175    | 1989    | 1865    | 1989    |
| 65° | 1838    | 1691    | 1618    | 1618    |
| 70° | 1454    | 1363    | 1272    | 1363    |
| 75° | 1081    | 1081    | 1081    | 1081    |
| 80° | 716     | 716     | 716     | 716     |
| 85° | 713     | 713     | 713     | 713     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 7559 cd/sqm

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 328.9  | 35.5      |
| 10°-20°   | 304.8  | 32.9      |
| 20°-30°   | 181.1  | 19.5      |
| 30°-40°   | 88.0   | 9.5       |
| 40°-50°   | 14.0   | 1.5       |
| 50°-60°   | 4.1    | 0.4       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 1.0    | 0.1       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.1    | 0.0       |
| 140°-150° | 0.3    | 0.0       |
| 150°-160° | 0.7    | 0.1       |
| 160°-170° | 0.8    | 0.1       |
| 170°-180° | 0.3    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 814.9  | 87.9      |
| 0°-40°    | 902.8  | 97.4      |
| 0°-60°    | 920.9  | 99.4      |
| 0°-90°    | 924.3  | 99.8      |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.4    | 0.0       |
| 90°-180°  | 2.0    | 0.2       |
| 0°-180°   | 926.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 90°  | 180° | 270° | 360° | Flux |
|------|------|------|------|------|------|------|
| 0°   | 4968 | 4968 | 4968 | 4968 | 4968 |      |
| 5°   | 4427 | 4162 | 3791 | 4044 | 4425 | 360  |
| 15°  | 1192 | 1044 | 898  | 1002 | 1192 | 349  |
| 25°  | 418  | 389  | 367  | 390  | 419  | 195  |
| 35°  | 160  | 137  | 118  | 136  | 160  | 101  |
| 45°  | 17   | 15   | 11   | 15   | 17   | 17   |
| 55°  | 5    | 4    | 4    | 4    | 5    | 5    |
| 65°  | 2    | 2    | 2    | 2    | 2    | 2    |
| 75°  | 1    | 1    | 1    | 1    | 1    | 1    |
| 85°  | 0    | 0    | 0    | 0    | 0    | 0    |
| 90°  | 0    | 0    | 0    | 0    | 0    | 0    |
| 95°  | 0    | 0    | 0    | 0    | 0    | 0    |
| 105° | 0    | 0    | 0    | 0    | 0    | 0    |
| 115° | 0    | 0    | 0    | 0    | 0    | 0    |
| 125° | 0    | 0    | 0    | 0    | 0    | 0    |
| 135° | 0    | 0    | 0    | 0    | 0    | 0    |
| 145° | 0    | 0    | 0    | 0    | 0    | 0    |
| 155° | 2    | 2    | 2    | 2    | 2    | 1    |
| 165° | 3    | 3    | 3    | 3    | 3    | 1    |
| 175° | 3    | 3    | 3    | 3    | 3    | 0    |
| 180° | 3    | 3    | 3    | 3    | 3    |      |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   | 202.5° | 225°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 |
| 0.5°  | 4999.4 | 4996.1 | 4983.2 | 4966.3 | 4952.1 | 4936.5 | 4938.5 | 4914.2 | 4917.5 | 4917.5 | 4941.2 |
| 1°    | 5020.4 | 5002.1 | 4987.9 | 4956.8 | 4931.1 | 4908.1 | 4887.8 | 4864.1 | 4862.0 | 4874.2 | 4886.4 |
| 1.5°  | 5013.0 | 5004.2 | 4978.5 | 4942.6 | 4898.6 | 4853.3 | 4813.3 | 4783.5 | 4772.7 | 4796.4 | 4809.9 |
| 2°    | 4978.5 | 4968.3 | 4943.9 | 4897.9 | 4830.2 | 4793.7 | 4731.4 | 4697.6 | 4680.7 | 4681.3 | 4703.7 |
| 2.5°  | 4931.8 | 4928.4 | 4881.7 | 4824.8 | 4763.2 | 4713.2 | 4627.9 | 4583.9 | 4564.9 | 4579.2 | 4603.5 |
| 3°    | 4851.9 | 4851.9 | 4822.8 | 4757.1 | 4678.6 | 4580.5 | 4511.5 | 4465.5 | 4424.2 | 4431.6 | 4466.1 |
| 3.5°  | 4791.7 | 4776.1 | 4726.0 | 4650.2 | 4563.6 | 4472.9 | 4384.9 | 4320.6 | 4299.6 | 4301.7 | 4332.1 |
| 4°    | 4680.0 | 4662.4 | 4627.2 | 4546.0 | 4445.1 | 4328.7 | 4234.0 | 4169.0 | 4133.8 | 4133.8 | 4182.6 |
| 4.5°  | 4559.5 | 4559.5 | 4504.7 | 4406.6 | 4293.5 | 4189.3 | 4079.0 | 4001.2 | 3959.9 | 3964.0 | 4016.1 |
| 5°    | 4426.9 | 4416.7 | 4362.6 | 4267.8 | 4162.3 | 4027.6 | 3922.0 | 3838.1 | 3791.4 | 3795.4 | 3845.5 |
| 5.5°  | 4275.3 | 4267.2 | 4203.5 | 4114.9 | 3995.1 | 3850.3 | 3733.8 | 3647.2 | 3601.2 | 3597.8 | 3654.0 |
| 6°    | 4108.1 | 4108.8 | 4055.3 | 3939.6 | 3800.2 | 3666.8 | 3556.5 | 3465.8 | 3401.5 | 3412.4 | 3459.1 |
| 6.5°  | 3934.8 | 3924.7 | 3868.5 | 3760.2 | 3635.0 | 3490.2 | 3355.5 | 3270.2 | 3223.5 | 3214.7 | 3269.6 |
| 7°    | 3749.4 | 3744.7 | 3683.1 | 3578.2 | 3435.4 | 3286.5 | 3166.0 | 3069.2 | 3009.0 | 3009.0 | 3063.8 |
| 7.5°  | 3560.6 | 3555.2 | 3485.5 | 3384.6 | 3247.2 | 3100.4 | 2973.1 | 2876.4 | 2830.3 | 2826.9 | 2887.2 |
| 8°    | 3372.4 | 3373.8 | 3316.9 | 3197.8 | 3059.1 | 2926.4 | 2793.8 | 2699.7 | 2632.0 | 2639.5 | 2694.3 |
| 8.5°  | 3176.8 | 3168.7 | 3104.4 | 3009.7 | 2856.0 | 2722.0 | 2599.5 | 2500.7 | 2447.9 | 2457.4 | 2501.4 |
| 9°    | 2974.5 | 2971.8 | 2909.5 | 2797.8 | 2671.3 | 2536.6 | 2420.2 | 2318.7 | 2270.6 | 2273.3 | 2322.7 |
| 9.5°  | 2787.0 | 2779.6 | 2728.8 | 2619.2 | 2481.8 | 2353.9 | 2244.9 | 2156.9 | 2100.8 | 2104.1 | 2152.9 |
| 10°   | 2603.6 | 2596.8 | 2548.1 | 2445.2 | 2314.6 | 2189.4 | 2071.7 | 1997.9 | 1945.1 | 1948.5 | 1997.9 |
| 10.5° | 2414.8 | 2422.9 | 2357.3 | 2254.4 | 2136.6 | 2030.4 | 1916.7 | 1836.8 | 1798.9 | 1796.9 | 1836.8 |
| 11°   | 2244.2 | 2233.4 | 2184.0 | 2092.6 | 1974.2 | 1862.5 | 1767.1 | 1695.4 | 1650.0 | 1648.0 | 1689.9 |
| 11.5° | 2075.0 | 2065.6 | 2020.2 | 1933.6 | 1817.2 | 1720.4 | 1626.3 | 1558.6 | 1521.4 | 1525.5 | 1562.0 |
| 12°   | 1916.7 | 1918.7 | 1864.6 | 1774.5 | 1679.8 | 1587.7 | 1501.1 | 1443.6 | 1406.4 | 1409.8 | 1441.6 |
| 12.5° | 1767.8 | 1765.7 | 1715.0 | 1643.2 | 1545.8 | 1457.1 | 1386.7 | 1326.5 | 1299.4 | 1298.1 | 1327.9 |
| 13°   | 1633.8 | 1627.7 | 1587.7 | 1512.6 | 1432.8 | 1350.2 | 1281.2 | 1226.3 | 1199.3 | 1199.3 | 1225.7 |
| 13.5° | 1502.5 | 1501.8 | 1463.2 | 1394.9 | 1313.6 | 1246.0 | 1184.4 | 1134.3 | 1110.6 | 1110.6 | 1135.0 |
| 14°   | 1388.8 | 1386.1 | 1350.2 | 1290.6 | 1218.2 | 1154.6 | 1098.4 | 1053.8 | 1030.1 | 1030.7 | 1053.1 |
| 14.5° | 1287.3 | 1287.9 | 1248.7 | 1191.8 | 1128.2 | 1071.4 | 1020.6 | 979.3  | 961.0  | 962.4  | 982.7  |
| 15°   | 1192.5 | 1194.5 | 1154.6 | 1104.5 | 1044.3 | 994.2  | 951.6  | 915.7  | 898.1  | 896.7  | 915.0  |
| 15.5° | 1107.2 | 1105.9 | 1072.0 | 1023.3 | 973.9  | 927.9  | 886.6  | 857.5  | 838.5  | 837.9  | 855.5  |
| 16°   | 1025.3 | 1024.0 | 993.5  | 953.6  | 906.2  | 863.6  | 832.5  | 799.3  | 784.4  | 786.4  | 802.7  |
| 16.5° | 953.6  | 952.2  | 926.5  | 887.3  | 846.7  | 808.8  | 779.0  | 752.6  | 737.0  | 739.7  | 753.3  |
| 17°   | 891.3  | 887.9  | 863.6  | 830.4  | 793.2  | 764.8  | 733.6  | 710.6  | 697.8  | 697.8  | 712.0  |
| 17.5° | 835.2  | 832.5  | 809.4  | 778.3  | 744.5  | 718.1  | 694.4  | 671.9  | 660.2  | 658.1  | 672.6  |
| 18°   | 783.0  | 781.0  | 758.0  | 731.6  | 702.5  | 678.8  | 657.0  | 635.6  | 625.3  | 625.7  | 637.7  |
| 18.5° | 736.3  | 733.6  | 713.3  | 689.6  | 664.6  | 641.8  | 624.2  | 605.0  | 593.1  | 595.4  | 608.1  |
| 19°   | 694.4  | 691.0  | 676.5  | 651.5  | 630.6  | 609.2  | 592.8  | 576.9  | 566.2  | 566.6  | 577.8  |
| 19.5° | 656.5  | 655.5  | 638.1  | 621.0  | 599.7  | 582.6  | 565.1  | 549.8  | 541.3  | 542.4  | 554.0  |
| 20°   | 624.4  | 621.5  | 603.8  | 589.5  | 570.9  | 555.4  | 542.6  | 525.7  | 519.0  | 519.4  | 530.1  |
| 20.5° | 592.9  | 591.1  | 579.0  | 560.2  | 545.8  | 532.6  | 518.7  | 505.0  | 498.5  | 499.6  | 509.4  |
| 21°   | 566.7  | 563.8  | 552.2  | 537.0  | 522.5  | 510.2  | 498.7  | 485.3  | 479.9  | 481.4  | 490.2  |
| 21.5° | 542.2  | 539.0  | 526.5  | 514.9  | 501.2  | 490.3  | 479.0  | 468.3  | 462.3  | 463.5  | 472.3  |
| 22°   | 518.9  | 517.3  | 505.4  | 493.5  | 481.9  | 471.2  | 461.0  | 449.5  | 445.5  | 446.5  | 455.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   | 112.5° | 135°  | 157.5° | 180°  | 202.5° | 225°  |
|-------|-------|-------|-------|-------|-------|--------|-------|--------|-------|--------|-------|
| 22.5° | 498.4 | 495.3 | 486.5 | 474.3 | 463.8 | 453.2  | 446.3 | 433.4  | 430.8 | 431.0  | 439.4 |
| 23°   | 479.9 | 475.6 | 467.8 | 456.9 | 446.6 | 437.9  | 431.2 | 418.3  | 416.6 | 417.4  | 425.4 |
| 23.5° | 462.4 | 459.7 | 451.2 | 440.8 | 430.6 | 424.0  | 416.8 | 404.5  | 403.2 | 404.9  | 411.9 |
| 24°   | 447.3 | 443.4 | 435.9 | 425.6 | 416.8 | 408.4  | 403.6 | 392.1  | 390.7 | 391.9  | 398.4 |
| 24.5° | 433.0 | 428.7 | 422.0 | 412.0 | 403.0 | 395.4  | 392.0 | 379.5  | 379.7 | 378.9  | 385.2 |
| 25°   | 418.5 | 415.8 | 408.1 | 399.3 | 389.2 | 383.3  | 379.7 | 367.3  | 366.8 | 365.9  | 373.2 |
| 25.5° | 404.7 | 401.7 | 394.8 | 386.2 | 376.3 | 370.1  | 368.2 | 355.7  | 354.6 | 354.4  | 361.1 |
| 26°   | 392.0 | 388.7 | 382.0 | 373.0 | 364.4 | 357.0  | 356.9 | 343.2  | 343.7 | 343.9  | 349.5 |
| 26.5° | 380.2 | 375.7 | 370.2 | 360.4 | 351.6 | 345.0  | 346.0 | 330.9  | 333.1 | 331.8  | 338.1 |
| 27°   | 367.3 | 364.5 | 358.1 | 349.0 | 339.5 | 333.5  | 333.8 | 319.7  | 320.9 | 319.6  | 326.0 |
| 27.5° | 355.2 | 352.4 | 347.3 | 337.7 | 327.6 | 321.7  | 322.1 | 308.5  | 308.4 | 307.5  | 314.2 |
| 28°   | 343.9 | 340.0 | 335.3 | 326.1 | 315.0 | 308.8  | 311.2 | 296.8  | 296.9 | 296.5  | 302.1 |
| 28.5° | 331.9 | 327.4 | 323.2 | 313.2 | 302.9 | 295.8  | 299.3 | 284.4  | 284.6 | 283.5  | 289.2 |
| 29°   | 319.9 | 315.8 | 310.5 | 300.8 | 290.9 | 283.6  | 287.4 | 271.2  | 271.9 | 271.8  | 277.1 |
| 29.5° | 307.1 | 303.3 | 297.0 | 287.8 | 278.2 | 271.4  | 274.5 | 258.1  | 259.1 | 258.8  | 264.4 |
| 30°   | 294.4 | 291.3 | 285.5 | 275.5 | 265.4 | 258.4  | 261.0 | 245.8  | 246.7 | 246.1  | 251.8 |
| 30.5° | 281.7 | 278.5 | 274.2 | 263.5 | 252.8 | 244.9  | 247.8 | 233.2  | 234.4 | 233.2  | 239.0 |
| 31°   | 267.9 | 265.0 | 261.0 | 249.8 | 239.9 | 231.3  | 234.6 | 220.2  | 220.4 | 219.4  | 225.3 |
| 31.5° | 255.1 | 251.5 | 247.4 | 237.9 | 226.9 | 218.8  | 221.0 | 207.2  | 207.0 | 207.2  | 212.6 |
| 32°   | 241.6 | 237.6 | 233.4 | 224.2 | 213.9 | 205.8  | 206.8 | 193.2  | 193.3 | 193.7  | 198.6 |
| 32.5° | 227.9 | 224.4 | 219.6 | 210.9 | 200.4 | 191.7  | 192.4 | 180.1  | 180.4 | 180.3  | 185.0 |
| 33°   | 213.7 | 210.9 | 206.8 | 197.4 | 187.2 | 178.8  | 178.2 | 167.2  | 167.5 | 167.7  | 172.4 |
| 33.5° | 199.8 | 197.1 | 192.7 | 183.7 | 174.0 | 165.6  | 163.9 | 154.4  | 153.5 | 153.8  | 158.5 |
| 34°   | 186.3 | 183.8 | 180.2 | 171.1 | 161.8 | 153.0  | 150.7 | 141.5  | 141.4 | 141.8  | 146.8 |
| 34.5° | 173.0 | 170.8 | 167.4 | 159.0 | 149.6 | 140.8  | 138.3 | 129.1  | 129.5 | 129.8  | 134.9 |
| 35°   | 160.0 | 157.6 | 154.0 | 145.7 | 137.3 | 128.3  | 125.1 | 117.7  | 118.0 | 118.3  | 122.2 |
| 35.5° | 148.1 | 145.8 | 142.4 | 134.6 | 126.3 | 117.5  | 112.9 | 107.3  | 107.0 | 107.8  | 111.9 |
| 36°   | 135.3 | 133.3 | 129.2 | 123.2 | 115.1 | 106.4  | 101.7 | 96.3   | 96.4  | 96.8   | 101.4 |
| 36.5° | 123.2 | 121.6 | 117.6 | 111.4 | 104.6 | 96.2   | 91.0  | 86.1   | 86.2  | 86.8   | 90.8  |
| 37°   | 111.9 | 111.3 | 108.0 | 102.1 | 95.2  | 86.8   | 80.7  | 77.1   | 76.9  | 78.4   | 82.2  |
| 37.5° | 100.8 | 100.2 | 96.5  | 91.2  | 84.8  | 77.4   | 71.1  | 68.1   | 67.9  | 68.9   | 72.1  |
| 38°   | 91.6  | 91.4  | 87.4  | 81.8  | 76.4  | 69.4   | 62.9  | 60.7   | 60.4  | 61.3   | 64.6  |
| 38.5° | 82.2  | 81.9  | 78.8  | 74.2  | 68.7  | 61.7   | 55.5  | 53.3   | 53.4  | 54.3   | 57.8  |
| 39°   | 73.7  | 73.0  | 69.7  | 65.5  | 60.9  | 55.0   | 48.8  | 47.2   | 46.8  | 47.4   | 50.3  |
| 39.5° | 66.3  | 66.1  | 63.3  | 59.4  | 54.8  | 49.0   | 43.0  | 41.8   | 41.6  | 42.4   | 45.2  |
| 40°   | 59.0  | 58.8  | 56.7  | 53.1  | 48.7  | 43.4   | 37.7  | 36.7   | 36.5  | 37.3   | 39.9  |
| 40.5° | 52.6  | 52.2  | 50.3  | 46.6  | 43.0  | 38.5   | 33.2  | 32.4   | 32.1  | 32.6   | 34.5  |
| 41°   | 47.3  | 47.0  | 45.5  | 42.2  | 38.8  | 34.2   | 29.2  | 28.6   | 28.3  | 29.3   | 31.3  |
| 41.5° | 41.1  | 40.9  | 39.5  | 37.1  | 34.1  | 30.1   | 25.7  | 25.1   | 24.8  | 25.6   | 27.4  |
| 42°   | 36.6  | 36.3  | 34.8  | 32.7  | 30.1  | 26.8   | 22.7  | 22.2   | 22.0  | 22.4   | 24.1  |
| 42.5° | 32.3  | 32.1  | 31.3  | 29.5  | 27.0  | 23.8   | 20.1  | 19.7   | 19.5  | 20.2   | 21.6  |
| 43°   | 28.1  | 28.1  | 27.2  | 25.7  | 23.8  | 21.1   | 17.8  | 17.4   | 17.2  | 17.8   | 18.8  |
| 43.5° | 24.8  | 25.2  | 24.3  | 22.8  | 21.3  | 19.0   | 15.9  | 15.3   | 15.2  | 15.9   | 17.1  |
| 44°   | 21.4  | 21.9  | 21.4  | 20.4  | 19.0  | 16.9   | 14.1  | 13.5   | 13.5  | 14.2   | 15.5  |
| 44.5° | 18.9  | 19.3  | 18.6  | 17.7  | 16.6  | 15.0   | 12.6  | 12.1   | 12.1  | 12.4   | 13.7  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 0°   | 22.5° | 45°  | 67.5° | 90°  | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|-------|------|-------|------|-------|------|--------|------|--------|------|--------|------|
| 45°   | 16.8 | 17.2  | 16.8 | 15.9  | 15.0 | 13.4   | 11.4 | 11.0   | 11.0 | 11.5   | 12.4 |
| 45.5° | 14.8 | 15.3  | 14.9 | 14.3  | 13.3 | 12.0   | 10.3 | 10.0   | 10.0 | 10.5   | 11.2 |
| 46°   | 13.4 | 13.8  | 13.3 | 12.7  | 12.0 | 10.9   | 9.5  | 9.2    | 9.3  | 9.6    | 10.2 |
| 46.5° | 12.1 | 12.4  | 12.1 | 11.6  | 10.9 | 10.0   | 8.8  | 8.5    | 8.6  | 8.9    | 9.5  |
| 47°   | 11.0 | 11.2  | 11.0 | 10.5  | 9.9  | 9.2    | 8.2  | 7.9    | 8.0  | 8.3    | 8.8  |
| 47.5° | 10.2 | 10.4  | 10.2 | 9.7   | 9.2  | 8.5    | 7.6  | 7.4    | 7.5  | 7.7    | 8.2  |
| 48°   | 9.5  | 9.7   | 9.5  | 9.1   | 8.6  | 7.9    | 7.2  | 7.0    | 7.1  | 7.3    | 7.7  |
| 48.5° | 8.8  | 9.0   | 8.8  | 8.4   | 8.0  | 7.4    | 6.8  | 6.6    | 6.7  | 6.9    | 7.3  |
| 49°   | 8.3  | 8.5   | 8.3  | 7.9   | 7.5  | 7.0    | 6.4  | 6.2    | 6.3  | 6.6    | 6.9  |
| 49.5° | 7.8  | 8.0   | 7.8  | 7.5   | 7.1  | 6.6    | 6.1  | 6.0    | 6.0  | 6.2    | 6.5  |
| 50°   | 7.5  | 7.6   | 7.5  | 7.1   | 6.7  | 6.3    | 5.8  | 5.7    | 5.8  | 6.0    | 6.2  |
| 50.5° | 7.1  | 7.2   | 7.1  | 6.8   | 6.4  | 5.9    | 5.6  | 5.4    | 5.5  | 5.7    | 6.0  |
| 51°   | 6.7  | 6.8   | 6.7  | 6.4   | 6.0  | 5.7    | 5.3  | 5.2    | 5.3  | 5.5    | 5.7  |
| 51.5° | 6.4  | 6.5   | 6.4  | 6.1   | 5.8  | 5.4    | 5.1  | 5.0    | 5.1  | 5.2    | 5.5  |
| 52°   | 6.1  | 6.2   | 6.1  | 5.9   | 5.5  | 5.2    | 4.9  | 4.8    | 4.9  | 5.0    | 5.2  |
| 52.5° | 5.9  | 6.0   | 5.9  | 5.6   | 5.3  | 5.0    | 4.7  | 4.6    | 4.7  | 4.9    | 5.0  |
| 53°   | 5.7  | 5.7   | 5.6  | 5.4   | 5.1  | 4.8    | 4.6  | 4.5    | 4.5  | 4.7    | 4.8  |
| 53.5° | 5.4  | 5.5   | 5.4  | 5.2   | 4.9  | 4.6    | 4.4  | 4.3    | 4.4  | 4.5    | 4.7  |
| 54°   | 5.3  | 5.3   | 5.3  | 5.0   | 4.7  | 4.5    | 4.3  | 4.2    | 4.2  | 4.4    | 4.5  |
| 54.5° | 5.1  | 5.1   | 5.0  | 4.8   | 4.5  | 4.3    | 4.1  | 4.1    | 4.1  | 4.2    | 4.4  |
| 55°   | 4.9  | 5.0   | 4.9  | 4.7   | 4.4  | 4.2    | 4.0  | 3.9    | 4.0  | 4.1    | 4.3  |
| 55.5° | 4.7  | 4.8   | 4.7  | 4.5   | 4.2  | 4.0    | 3.9  | 3.8    | 3.9  | 4.0    | 4.1  |
| 56°   | 4.6  | 4.6   | 4.6  | 4.3   | 4.1  | 3.9    | 3.8  | 3.7    | 3.8  | 3.9    | 4.0  |
| 56.5° | 4.4  | 4.5   | 4.4  | 4.2   | 4.0  | 3.8    | 3.7  | 3.6    | 3.7  | 3.8    | 3.9  |
| 57°   | 4.3  | 4.3   | 4.2  | 4.1   | 3.8  | 3.7    | 3.6  | 3.5    | 3.5  | 3.6    | 3.7  |
| 57.5° | 4.1  | 4.2   | 4.1  | 3.9   | 3.7  | 3.6    | 3.5  | 3.4    | 3.4  | 3.5    | 3.6  |
| 58°   | 4.0  | 4.1   | 4.0  | 3.8   | 3.6  | 3.5    | 3.4  | 3.3    | 3.3  | 3.4    | 3.5  |
| 58.5° | 3.9  | 3.9   | 3.9  | 3.7   | 3.5  | 3.4    | 3.3  | 3.2    | 3.3  | 3.3    | 3.4  |
| 59°   | 3.7  | 3.8   | 3.7  | 3.6   | 3.4  | 3.3    | 3.2  | 3.1    | 3.2  | 3.2    | 3.3  |
| 59.5° | 3.6  | 3.7   | 3.6  | 3.5   | 3.3  | 3.1    | 3.1  | 3.0    | 3.1  | 3.1    | 3.2  |
| 60°   | 3.5  | 3.6   | 3.5  | 3.4   | 3.2  | 3.1    | 3.0  | 3.0    | 3.0  | 3.0    | 3.1  |
| 60.5° | 3.4  | 3.5   | 3.4  | 3.3   | 3.1  | 3.0    | 2.9  | 2.9    | 2.9  | 3.0    | 3.0  |
| 61°   | 3.3  | 3.3   | 3.3  | 3.1   | 3.0  | 2.9    | 2.8  | 2.8    | 2.8  | 2.9    | 2.9  |
| 61.5° | 3.2  | 3.2   | 3.2  | 3.0   | 2.9  | 2.8    | 2.7  | 2.7    | 2.7  | 2.8    | 2.8  |
| 62°   | 3.1  | 3.1   | 3.1  | 3.0   | 2.8  | 2.7    | 2.6  | 2.6    | 2.6  | 2.7    | 2.7  |
| 62.5° | 2.9  | 3.0   | 2.9  | 2.8   | 2.7  | 2.6    | 2.6  | 2.5    | 2.6  | 2.6    | 2.6  |
| 63°   | 2.9  | 2.9   | 2.9  | 2.8   | 2.6  | 2.5    | 2.5  | 2.5    | 2.5  | 2.5    | 2.5  |
| 63.5° | 2.7  | 2.8   | 2.8  | 2.7   | 2.5  | 2.4    | 2.4  | 2.4    | 2.4  | 2.4    | 2.4  |
| 64°   | 2.6  | 2.7   | 2.7  | 2.6   | 2.4  | 2.4    | 2.3  | 2.3    | 2.3  | 2.3    | 2.4  |
| 64.5° | 2.6  | 2.6   | 2.6  | 2.5   | 2.4  | 2.3    | 2.2  | 2.2    | 2.2  | 2.3    | 2.3  |
| 65°   | 2.5  | 2.5   | 2.5  | 2.4   | 2.3  | 2.2    | 2.2  | 2.2    | 2.2  | 2.2    | 2.2  |
| 65.5° | 2.4  | 2.4   | 2.4  | 2.3   | 2.2  | 2.1    | 2.1  | 2.1    | 2.1  | 2.1    | 2.1  |
| 66°   | 2.3  | 2.3   | 2.3  | 2.2   | 2.1  | 2.0    | 2.0  | 2.0    | 2.0  | 2.0    | 2.0  |
| 66.5° | 2.2  | 2.2   | 2.2  | 2.1   | 2.0  | 2.0    | 1.9  | 1.9    | 1.9  | 1.9    | 2.0  |
| 67°   | 2.1  | 2.1   | 2.1  | 2.0   | 2.0  | 1.9    | 1.9  | 1.9    | 1.9  | 1.9    | 1.9  |



TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|-------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 67.5° | 2.0 | 2.0   | 2.0 | 2.0   | 1.9 | 1.8    | 1.8  | 1.8    | 1.8  | 1.8    | 1.8  |
| 68°   | 1.9 | 1.9   | 1.9 | 1.9   | 1.8 | 1.7    | 1.7  | 1.7    | 1.7  | 1.7    | 1.7  |
| 68.5° | 1.8 | 1.9   | 1.9 | 1.8   | 1.7 | 1.7    | 1.7  | 1.6    | 1.6  | 1.6    | 1.6  |
| 69°   | 1.8 | 1.8   | 1.8 | 1.7   | 1.7 | 1.6    | 1.6  | 1.6    | 1.6  | 1.6    | 1.6  |
| 69.5° | 1.7 | 1.7   | 1.7 | 1.7   | 1.6 | 1.5    | 1.5  | 1.5    | 1.5  | 1.5    | 1.5  |
| 70°   | 1.6 | 1.6   | 1.6 | 1.6   | 1.5 | 1.5    | 1.5  | 1.4    | 1.4  | 1.4    | 1.4  |
| 70.5° | 1.5 | 1.6   | 1.6 | 1.5   | 1.5 | 1.4    | 1.4  | 1.4    | 1.4  | 1.4    | 1.4  |
| 71°   | 1.4 | 1.5   | 1.5 | 1.4   | 1.4 | 1.3    | 1.3  | 1.3    | 1.3  | 1.3    | 1.3  |
| 71.5° | 1.4 | 1.4   | 1.4 | 1.4   | 1.3 | 1.3    | 1.3  | 1.3    | 1.3  | 1.3    | 1.3  |
| 72°   | 1.3 | 1.3   | 1.3 | 1.3   | 1.2 | 1.2    | 1.2  | 1.2    | 1.2  | 1.2    | 1.2  |
| 72.5° | 1.2 | 1.2   | 1.3 | 1.2   | 1.2 | 1.2    | 1.1  | 1.1    | 1.1  | 1.1    | 1.1  |
| 73°   | 1.2 | 1.2   | 1.2 | 1.2   | 1.1 | 1.1    | 1.1  | 1.1    | 1.1  | 1.1    | 1.1  |
| 73.5° | 1.1 | 1.1   | 1.1 | 1.1   | 1.1 | 1.0    | 1.0  | 1.0    | 1.0  | 1.0    | 1.0  |
| 74°   | 1.0 | 1.1   | 1.1 | 1.0   | 1.0 | 1.0    | 1.0  | 1.0    | 1.0  | 1.0    | 1.0  |
| 74.5° | 1.0 | 1.0   | 1.0 | 1.0   | 1.0 | 0.9    | 0.9  | 0.9    | 0.9  | 0.9    | 0.9  |
| 75°   | 0.9 | 0.9   | 0.9 | 0.9   | 0.9 | 0.9    | 0.9  | 0.9    | 0.9  | 0.9    | 0.9  |
| 75.5° | 0.9 | 0.9   | 0.9 | 0.9   | 0.8 | 0.8    | 0.8  | 0.8    | 0.8  | 0.8    | 0.8  |
| 76°   | 0.8 | 0.8   | 0.8 | 0.8   | 0.8 | 0.8    | 0.8  | 0.8    | 0.8  | 0.8    | 0.8  |
| 76.5° | 0.7 | 0.8   | 0.8 | 0.8   | 0.7 | 0.7    | 0.7  | 0.7    | 0.7  | 0.7    | 0.7  |
| 77°   | 0.7 | 0.7   | 0.7 | 0.7   | 0.7 | 0.7    | 0.7  | 0.7    | 0.7  | 0.7    | 0.7  |
| 77.5° | 0.7 | 0.7   | 0.7 | 0.7   | 0.6 | 0.6    | 0.6  | 0.6    | 0.6  | 0.6    | 0.6  |
| 78°   | 0.6 | 0.6   | 0.6 | 0.6   | 0.6 | 0.6    | 0.6  | 0.6    | 0.6  | 0.6    | 0.6  |
| 78.5° | 0.6 | 0.6   | 0.6 | 0.6   | 0.6 | 0.6    | 0.6  | 0.5    | 0.6  | 0.6    | 0.6  |
| 79°   | 0.5 | 0.5   | 0.5 | 0.5   | 0.5 | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 79.5° | 0.5 | 0.5   | 0.5 | 0.5   | 0.5 | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 80°   | 0.4 | 0.4   | 0.4 | 0.4   | 0.4 | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 80.5° | 0.4 | 0.4   | 0.4 | 0.4   | 0.4 | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 81°   | 0.4 | 0.4   | 0.4 | 0.4   | 0.4 | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 81.5° | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 82°   | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 82.5° | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 83°   | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.2    | 0.3  |
| 83.5° | 0.2 | 0.3   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 84°   | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 84.5° | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 85°   | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 85.5° | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 86°   | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 86.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 87°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 87.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 88°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 88.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 89°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 89.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 90°    | 0.1 | 0.1   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 91°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 91.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 93°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 93.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 96°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 96.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 98°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 98.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 99°    | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 99.5°  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 103°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 103.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 112°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 113°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 113.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 114°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 114.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 119°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 119.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 123°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 123.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 126°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 126.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 128°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 128.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 129°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 129.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.1    | 0.1  | 0.0    | 0.0  |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.1  | 0.0    | 0.0  | 0.1    | 0.1  |
| 131°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.1    | 0.0  | 0.1    | 0.1  | 0.1    | 0.0  |
| 131.5° | 0.0 | 0.0   | 0.0 | 0.1   | 0.0 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 132°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 132.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 133°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 133.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 134°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 134.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 135°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 135.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 136°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 136.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 137°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 137.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 138°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 138.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 139°   | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.1    | 0.1  | 0.2    | 0.2  | 0.1    | 0.2  |
| 139.5° | 0.1 | 0.1   | 0.1 | 0.1   | 0.1 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 140°   | 0.1 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 140.5° | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 141°   | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 141.5° | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 142°   | 0.2 | 0.2   | 0.2 | 0.2   | 0.2 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 142.5° | 0.2 | 0.2   | 0.2 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 143°   | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 143.5° | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.3    | 0.3  | 0.4    | 0.3  | 0.4    | 0.3  |
| 144°   | 0.3 | 0.3   | 0.3 | 0.3   | 0.3 | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 144.5° | 0.3 | 0.3   | 0.3 | 0.4   | 0.4 | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 145°   | 0.4 | 0.4   | 0.4 | 0.4   | 0.4 | 0.4    | 0.4  | 0.4    | 0.5  | 0.4    | 0.4  |
| 145.5° | 0.4 | 0.4   | 0.4 | 0.4   | 0.4 | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 146°   | 0.4 | 0.4   | 0.4 | 0.4   | 0.5 | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 146.5° | 0.5 | 0.5   | 0.5 | 0.5   | 0.5 | 0.5    | 0.6  | 0.6    | 0.6  | 0.6    | 0.6  |
| 147°   | 0.5 | 0.5   | 0.5 | 0.5   | 0.5 | 0.6    | 0.6  | 0.6    | 0.6  | 0.6    | 0.6  |
| 147.5° | 0.5 | 0.5   | 0.5 | 0.6   | 0.6 | 0.6    | 0.6  | 0.7    | 0.7  | 0.7    | 0.7  |
| 148°   | 0.6 | 0.6   | 0.6 | 0.6   | 0.6 | 0.7    | 0.7  | 0.7    | 0.7  | 0.7    | 0.7  |
| 148.5° | 0.6 | 0.6   | 0.6 | 0.6   | 0.7 | 0.7    | 0.8  | 0.8    | 0.8  | 0.8    | 0.8  |
| 149°   | 0.7 | 0.7   | 0.7 | 0.7   | 0.7 | 0.8    | 0.8  | 0.8    | 0.8  | 0.8    | 0.8  |
| 149.5° | 0.7 | 0.7   | 0.7 | 0.7   | 0.8 | 0.8    | 0.9  | 0.9    | 0.9  | 0.9    | 0.9  |
| 150°   | 0.8 | 0.8   | 0.8 | 0.8   | 0.9 | 0.9    | 0.9  | 1.0    | 1.0  | 1.0    | 1.0  |
| 150.5° | 0.8 | 0.8   | 0.8 | 0.9   | 0.9 | 1.0    | 1.0  | 1.0    | 1.0  | 1.0    | 1.0  |
| 151°   | 0.9 | 0.9   | 0.9 | 0.9   | 1.0 | 1.0    | 1.1  | 1.1    | 1.1  | 1.1    | 1.1  |
| 151.5° | 1.0 | 0.9   | 1.0 | 1.0   | 1.0 | 1.1    | 1.2  | 1.2    | 1.2  | 1.2    | 1.2  |
| 152°   | 1.0 | 1.0   | 1.0 | 1.1   | 1.1 | 1.2    | 1.2  | 1.3    | 1.3  | 1.3    | 1.2  |
| 152.5° | 1.1 | 1.1   | 1.1 | 1.1   | 1.2 | 1.2    | 1.3  | 1.3    | 1.3  | 1.4    | 1.3  |
| 153°   | 1.1 | 1.1   | 1.2 | 1.2   | 1.3 | 1.3    | 1.4  | 1.4    | 1.4  | 1.4    | 1.4  |
| 153.5° | 1.2 | 1.2   | 1.2 | 1.3   | 1.3 | 1.4    | 1.5  | 1.5    | 1.5  | 1.5    | 1.5  |
| 154°   | 1.3 | 1.3   | 1.3 | 1.4   | 1.4 | 1.5    | 1.5  | 1.6    | 1.6  | 1.6    | 1.6  |
| 154.5° | 1.4 | 1.4   | 1.4 | 1.4   | 1.5 | 1.6    | 1.6  | 1.7    | 1.7  | 1.7    | 1.6  |
| 155°   | 1.5 | 1.5   | 1.5 | 1.5   | 1.6 | 1.7    | 1.7  | 1.8    | 1.8  | 1.8    | 1.8  |
| 155.5° | 1.5 | 1.5   | 1.5 | 1.6   | 1.7 | 1.7    | 1.8  | 1.8    | 1.9  | 1.8    | 1.8  |
| 156°   | 1.6 | 1.6   | 1.6 | 1.7   | 1.7 | 1.8    | 1.9  | 1.9    | 1.9  | 1.9    | 1.9  |
| 156.5° | 1.7 | 1.7   | 1.7 | 1.8   | 1.8 | 1.9    | 2.0  | 2.0    | 2.0  | 2.0    | 2.0  |
| 157°   | 1.8 | 1.8   | 1.8 | 1.8   | 1.9 | 2.0    | 2.0  | 2.1    | 2.1  | 2.1    | 2.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 157.5° | 1.9 | 1.8   | 1.9 | 1.9   | 2.0 | 2.0    | 2.1  | 2.1    | 2.2  | 2.2    | 2.1  |
| 158°   | 1.9 | 1.9   | 1.9 | 2.0   | 2.1 | 2.1    | 2.2  | 2.2    | 2.2  | 2.2    | 2.2  |
| 158.5° | 2.0 | 2.0   | 2.0 | 2.1   | 2.2 | 2.2    | 2.3  | 2.3    | 2.3  | 2.3    | 2.3  |
| 159°   | 2.1 | 2.1   | 2.1 | 2.2   | 2.2 | 2.3    | 2.4  | 2.4    | 2.4  | 2.4    | 2.4  |
| 159.5° | 2.2 | 2.2   | 2.2 | 2.3   | 2.3 | 2.4    | 2.4  | 2.5    | 2.5  | 2.5    | 2.5  |
| 160°   | 2.3 | 2.3   | 2.3 | 2.3   | 2.4 | 2.5    | 2.5  | 2.6    | 2.6  | 2.6    | 2.6  |
| 160.5° | 2.4 | 2.4   | 2.4 | 2.4   | 2.5 | 2.5    | 2.6  | 2.6    | 2.6  | 2.6    | 2.6  |
| 161°   | 2.4 | 2.4   | 2.5 | 2.5   | 2.6 | 2.6    | 2.7  | 2.7    | 2.7  | 2.7    | 2.7  |
| 161.5° | 2.5 | 2.5   | 2.5 | 2.6   | 2.6 | 2.7    | 2.7  | 2.8    | 2.8  | 2.8    | 2.8  |
| 162°   | 2.6 | 2.6   | 2.6 | 2.6   | 2.7 | 2.7    | 2.8  | 2.8    | 2.8  | 2.8    | 2.8  |
| 162.5° | 2.6 | 2.6   | 2.7 | 2.7   | 2.8 | 2.8    | 2.8  | 2.9    | 2.9  | 2.9    | 2.9  |
| 163°   | 2.7 | 2.7   | 2.7 | 2.8   | 2.8 | 2.9    | 2.9  | 2.9    | 2.9  | 2.9    | 2.9  |
| 163.5° | 2.8 | 2.8   | 2.8 | 2.8   | 2.9 | 2.9    | 2.9  | 3.0    | 3.0  | 3.0    | 3.0  |
| 164°   | 2.8 | 2.8   | 2.8 | 2.9   | 2.9 | 3.0    | 3.0  | 3.0    | 3.0  | 3.0    | 3.0  |
| 164.5° | 2.9 | 2.9   | 2.9 | 2.9   | 3.0 | 3.0    | 3.0  | 3.0    | 3.0  | 3.1    | 3.0  |
| 165°   | 2.9 | 2.9   | 3.0 | 3.0   | 3.0 | 3.0    | 3.1  | 3.1    | 3.1  | 3.1    | 3.1  |
| 165.5° | 3.0 | 3.0   | 3.0 | 3.0   | 3.1 | 3.1    | 3.1  | 3.1    | 3.1  | 3.1    | 3.1  |
| 166°   | 3.0 | 3.0   | 3.1 | 3.1   | 3.1 | 3.1    | 3.2  | 3.2    | 3.2  | 3.2    | 3.1  |
| 166.5° | 3.1 | 3.1   | 3.1 | 3.1   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 167°   | 3.1 | 3.1   | 3.1 | 3.1   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 167.5° | 3.1 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 168°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 168.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 169°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 169.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 170°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 170.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.2  | 3.1    | 3.1  |
| 171°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.1  | 3.1    | 3.1  |
| 171.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.2    | 3.1  | 3.1    | 3.1  |
| 172°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.1    | 3.1  | 3.1    | 3.1  |
| 172.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.1    | 3.1  | 3.1    | 3.1  |
| 173°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.2  | 3.1    | 3.1  | 3.1    | 3.1  |
| 173.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.1  | 3.1    | 3.1  | 3.0    | 3.0  |
| 174°   | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.2    | 3.1  | 3.1    | 3.0  | 3.0    | 3.0  |
| 174.5° | 3.2 | 3.2   | 3.2 | 3.2   | 3.2 | 3.1    | 3.1  | 3.0    | 3.0  | 3.0    | 3.0  |
| 175°   | 3.1 | 3.2   | 3.2 | 3.2   | 3.1 | 3.1    | 3.1  | 3.0    | 3.0  | 3.0    | 3.0  |
| 175.5° | 3.1 | 3.1   | 3.1 | 3.1   | 3.1 | 3.1    | 3.0  | 3.0    | 3.0  | 2.9    | 2.9  |
| 176°   | 3.1 | 3.1   | 3.1 | 3.1   | 3.1 | 3.1    | 3.0  | 3.0    | 2.9  | 2.9    | 2.9  |
| 176.5° | 3.0 | 3.1   | 3.1 | 3.1   | 3.1 | 3.0    | 3.0  | 2.9    | 2.9  | 2.9    | 2.9  |
| 177°   | 3.0 | 3.0   | 3.1 | 3.0   | 3.0 | 3.0    | 3.0  | 2.9    | 2.9  | 2.9    | 2.8  |
| 177.5° | 3.0 | 3.0   | 3.0 | 3.0   | 3.0 | 3.0    | 2.9  | 2.9    | 2.9  | 2.8    | 2.8  |
| 178°   | 2.9 | 3.0   | 3.0 | 3.0   | 3.0 | 3.0    | 2.9  | 2.9    | 2.9  | 2.8    | 2.8  |
| 178.5° | 2.9 | 3.0   | 3.0 | 3.0   | 3.0 | 2.9    | 2.9  | 2.9    | 2.8  | 2.8    | 2.8  |
| 179°   | 2.9 | 2.9   | 3.0 | 3.0   | 2.9 | 2.9    | 2.9  | 2.9    | 2.8  | 2.8    | 2.8  |
| 179.5° | 2.9 | 2.9   | 2.9 | 2.9   | 2.9 | 2.9    | 2.9  | 2.9    | 2.8  | 2.8    | 2.8  |



TEST NUMBER: P979231  
CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

|      | 0°  | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|------|-----|-------|-----|-------|-----|--------|------|--------|------|--------|------|
| 180° | 2.8 | 2.8   | 2.8 | 2.8   | 2.8 | 2.8    | 2.8  | 2.8    | 2.8  | 2.8    | 2.8  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270°   | 292.5° | 315°   | 337.5° | 360°   |
|-------|--------|--------|--------|--------|--------|--------|
| 0°    | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 | 4967.6 |
| 0.5°  | 4951.4 | 4972.4 | 4979.8 | 4987.9 | 5006.2 | 5000.8 |
| 1°    | 4920.9 | 4937.2 | 4975.8 | 4985.9 | 5002.1 | 5007.6 |
| 1.5°  | 4834.3 | 4879.6 | 4923.6 | 4967.6 | 4987.9 | 5009.6 |
| 2°    | 4753.8 | 4818.1 | 4866.1 | 4919.6 | 4961.5 | 4962.9 |
| 2.5°  | 4659.0 | 4717.2 | 4804.5 | 4858.7 | 4916.2 | 4932.4 |
| 3°    | 4544.0 | 4631.3 | 4704.4 | 4782.9 | 4831.6 | 4863.4 |
| 3.5°  | 4399.8 | 4484.4 | 4583.2 | 4680.7 | 4751.1 | 4778.8 |
| 4°    | 4259.0 | 4352.4 | 4470.9 | 4567.0 | 4637.4 | 4667.8 |
| 4.5°  | 4097.3 | 4213.0 | 4320.6 | 4442.4 | 4523.0 | 4562.9 |
| 5°    | 3933.5 | 4044.5 | 4175.8 | 4284.1 | 4377.5 | 4424.8 |
| 5.5°  | 3750.1 | 3873.3 | 4001.2 | 4129.1 | 4224.5 | 4278.0 |
| 6°    | 3557.2 | 3687.8 | 3822.5 | 3957.9 | 4055.3 | 4106.8 |
| 6.5°  | 3370.4 | 3491.6 | 3645.2 | 3783.9 | 3888.2 | 3939.6 |
| 7°    | 3171.4 | 3304.1 | 3448.2 | 3580.2 | 3694.6 | 3748.7 |
| 7.5°  | 2979.2 | 3110.5 | 3258.7 | 3402.2 | 3505.1 | 3564.6 |
| 8°    | 2793.8 | 2922.4 | 3071.3 | 3212.0 | 3316.9 | 3379.9 |
| 8.5°  | 2604.3 | 2734.2 | 2870.9 | 3015.8 | 3121.3 | 3172.8 |
| 9°    | 2411.4 | 2538.0 | 2685.5 | 2814.8 | 2922.4 | 2979.2 |
| 9.5°  | 2245.6 | 2368.1 | 2492.6 | 2634.1 | 2730.8 | 2784.3 |
| 10°   | 2079.8 | 2198.2 | 2332.9 | 2454.7 | 2548.8 | 2602.9 |
| 10.5° | 1916.7 | 2029.7 | 2154.9 | 2274.0 | 2364.7 | 2422.9 |
| 11°   | 1767.1 | 1867.9 | 1987.1 | 2097.4 | 2190.1 | 2238.1 |
| 11.5° | 1626.3 | 1729.9 | 1840.2 | 1937.6 | 2024.3 | 2077.1 |
| 12°   | 1499.1 | 1591.8 | 1690.6 | 1792.8 | 1868.6 | 1916.7 |
| 12.5° | 1382.7 | 1470.0 | 1558.0 | 1649.3 | 1729.9 | 1768.4 |
| 13°   | 1277.1 | 1354.9 | 1443.6 | 1524.8 | 1590.5 | 1632.4 |
| 13.5° | 1183.0 | 1248.7 | 1329.9 | 1407.0 | 1470.0 | 1507.9 |
| 14°   | 1095.7 | 1157.3 | 1227.7 | 1302.1 | 1362.4 | 1392.2 |
| 14.5° | 1018.6 | 1078.1 | 1141.7 | 1204.7 | 1257.5 | 1285.9 |
| 15°   | 950.9  | 1002.3 | 1059.9 | 1114.7 | 1165.4 | 1191.8 |
| 15.5° | 887.9  | 931.9  | 984.1  | 1038.2 | 1079.5 | 1106.5 |
| 16°   | 831.1  | 871.0  | 922.5  | 966.5  | 1003.0 | 1025.3 |
| 16.5° | 781.0  | 816.9  | 858.2  | 902.2  | 938.0  | 954.9  |
| 17°   | 735.7  | 768.8  | 804.0  | 844.0  | 875.8  | 891.3  |
| 17.5° | 694.4  | 724.8  | 762.7  | 792.5  | 819.6  | 833.1  |
| 18°   | 658.6  | 684.2  | 719.4  | 746.5  | 770.2  | 783.7  |
| 18.5° | 625.4  | 649.4  | 677.5  | 705.2  | 726.9  | 737.7  |
| 19°   | 595.0  | 616.8  | 644.0  | 668.8  | 685.6  | 695.7  |
| 19.5° | 570.0  | 588.3  | 612.3  | 634.1  | 651.4  | 656.3  |
| 20°   | 545.8  | 562.9  | 584.3  | 603.5  | 620.1  | 624.3  |
| 20.5° | 522.5  | 540.9  | 559.6  | 576.6  | 589.3  | 596.8  |
| 21°   | 502.1  | 517.1  | 535.6  | 552.5  | 562.9  | 568.0  |
| 21.5° | 483.2  | 497.3  | 514.8  | 529.1  | 539.5  | 540.2  |
| 22°   | 466.0  | 477.9  | 495.5  | 507.9  | 517.1  | 519.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270°  | 292.5° | 315°  | 337.5° | 360°  |
|-------|--------|-------|--------|-------|--------|-------|
| 22.5° | 449.7  | 462.2 | 476.5  | 489.0 | 496.6  | 499.1 |
| 23°   | 436.1  | 445.0 | 460.3  | 470.5 | 478.6  | 480.7 |
| 23.5° | 420.8  | 429.8 | 444.7  | 454.3 | 461.4  | 461.8 |
| 24°   | 406.5  | 417.0 | 430.4  | 439.3 | 447.1  | 446.5 |
| 24.5° | 393.1  | 403.9 | 415.9  | 425.2 | 431.6  | 433.0 |
| 25°   | 380.5  | 390.1 | 401.5  | 410.7 | 417.8  | 419.1 |
| 25.5° | 368.6  | 376.3 | 389.2  | 397.0 | 404.2  | 405.1 |
| 26°   | 356.3  | 364.4 | 377.1  | 383.9 | 390.9  | 392.1 |
| 26.5° | 343.5  | 352.5 | 364.4  | 371.8 | 377.8  | 380.4 |
| 27°   | 331.9  | 340.9 | 352.0  | 360.1 | 365.7  | 367.9 |
| 27.5° | 320.1  | 327.6 | 339.5  | 347.5 | 353.8  | 355.4 |
| 28°   | 307.7  | 315.9 | 326.9  | 334.9 | 341.4  | 343.7 |
| 28.5° | 294.8  | 303.1 | 314.0  | 321.9 | 328.8  | 332.4 |
| 29°   | 282.8  | 291.5 | 301.6  | 309.5 | 315.7  | 320.2 |
| 29.5° | 269.4  | 277.9 | 288.9  | 296.5 | 303.1  | 306.3 |
| 30°   | 257.2  | 264.7 | 275.7  | 283.3 | 290.2  | 294.1 |
| 30.5° | 244.7  | 251.9 | 262.9  | 270.7 | 278.0  | 281.6 |
| 31°   | 230.9  | 239.4 | 250.3  | 258.0 | 264.3  | 269.0 |
| 31.5° | 218.0  | 227.1 | 236.5  | 244.5 | 250.5  | 255.6 |
| 32°   | 204.1  | 213.3 | 222.5  | 230.8 | 236.9  | 241.7 |
| 32.5° | 190.8  | 199.7 | 208.0  | 217.2 | 223.1  | 227.5 |
| 33°   | 177.9  | 186.3 | 195.1  | 203.1 | 209.5  | 213.4 |
| 33.5° | 164.8  | 172.9 | 181.9  | 189.2 | 195.8  | 199.3 |
| 34°   | 152.0  | 160.9 | 168.9  | 176.3 | 182.7  | 186.9 |
| 34.5° | 139.8  | 148.4 | 156.3  | 164.1 | 168.9  | 173.5 |
| 35°   | 127.3  | 136.1 | 143.7  | 150.9 | 156.0  | 160.1 |
| 35.5° | 117.4  | 124.9 | 131.6  | 138.9 | 143.8  | 147.5 |
| 36°   | 106.1  | 113.7 | 120.3  | 127.0 | 132.0  | 134.5 |
| 36.5° | 95.7   | 102.7 | 109.2  | 115.7 | 120.7  | 123.1 |
| 37°   | 86.6   | 93.8  | 98.9   | 105.1 | 109.5  | 112.3 |
| 37.5° | 77.0   | 83.4  | 89.0   | 95.3  | 98.7   | 100.8 |
| 38°   | 68.9   | 74.9  | 80.3   | 86.0  | 89.1   | 91.3  |
| 38.5° | 61.7   | 67.2  | 72.3   | 77.4  | 80.1   | 82.0  |
| 39°   | 54.3   | 59.7  | 64.0   | 69.2  | 71.9   | 73.4  |
| 39.5° | 48.7   | 53.7  | 57.6   | 62.1  | 64.4   | 66.4  |
| 40°   | 43.0   | 47.6  | 51.5   | 55.4  | 57.7   | 59.2  |
| 40.5° | 37.8   | 42.0  | 45.9   | 49.5  | 51.6   | 52.4  |
| 41°   | 34.0   | 37.8  | 40.7   | 44.0  | 46.0   | 47.1  |
| 41.5° | 29.7   | 33.1  | 36.0   | 39.1  | 40.7   | 41.5  |
| 42°   | 26.2   | 29.4  | 32.1   | 34.7  | 36.0   | 36.5  |
| 42.5° | 23.5   | 26.1  | 28.6   | 30.8  | 31.7   | 32.3  |
| 43°   | 20.7   | 23.1  | 25.5   | 27.1  | 27.8   | 28.0  |
| 43.5° | 18.7   | 20.8  | 22.5   | 23.7  | 24.3   | 24.8  |
| 44°   | 16.8   | 18.6  | 19.6   | 20.6  | 21.2   | 21.6  |
| 44.5° | 14.9   | 16.4  | 17.3   | 18.2  | 18.5   | 18.9  |



TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|-------|--------|------|--------|------|--------|------|
| 45°   | 13.5   | 14.7 | 15.5   | 16.1 | 16.3   | 16.8 |
| 45.5° | 12.2   | 13.0 | 13.8   | 14.4 | 14.5   | 14.9 |
| 46°   | 11.0   | 11.9 | 12.4   | 12.9 | 13.1   | 13.4 |
| 46.5° | 10.1   | 10.8 | 11.3   | 11.6 | 11.8   | 12.2 |
| 47°   | 9.3    | 9.8  | 10.3   | 10.6 | 10.7   | 11.0 |
| 47.5° | 8.7    | 9.1  | 9.5    | 9.7  | 9.9    | 10.2 |
| 48°   | 8.1    | 8.5  | 8.8    | 9.0  | 9.2    | 9.5  |
| 48.5° | 7.6    | 8.0  | 8.3    | 8.4  | 8.6    | 8.8  |
| 49°   | 7.2    | 7.5  | 7.7    | 7.9  | 8.1    | 8.4  |
| 49.5° | 6.8    | 7.1  | 7.3    | 7.5  | 7.6    | 7.9  |
| 50°   | 6.5    | 6.7  | 6.9    | 7.1  | 7.2    | 7.4  |
| 50.5° | 6.2    | 6.3  | 6.5    | 6.7  | 6.9    | 7.1  |
| 51°   | 5.9    | 6.0  | 6.2    | 6.4  | 6.5    | 6.7  |
| 51.5° | 5.6    | 5.8  | 5.9    | 6.1  | 6.2    | 6.4  |
| 52°   | 5.4    | 5.5  | 5.7    | 5.8  | 5.9    | 6.1  |
| 52.5° | 5.2    | 5.3  | 5.4    | 5.6  | 5.7    | 5.9  |
| 53°   | 5.0    | 5.1  | 5.2    | 5.3  | 5.5    | 5.7  |
| 53.5° | 4.8    | 4.9  | 5.0    | 5.1  | 5.3    | 5.4  |
| 54°   | 4.6    | 4.7  | 4.8    | 4.9  | 5.1    | 5.2  |
| 54.5° | 4.4    | 4.5  | 4.6    | 4.8  | 4.9    | 5.1  |
| 55°   | 4.3    | 4.4  | 4.5    | 4.6  | 4.7    | 4.9  |
| 55.5° | 4.2    | 4.2  | 4.3    | 4.4  | 4.6    | 4.7  |
| 56°   | 4.0    | 4.1  | 4.2    | 4.3  | 4.4    | 4.6  |
| 56.5° | 3.9    | 4.0  | 4.0    | 4.1  | 4.3    | 4.4  |
| 57°   | 3.8    | 3.8  | 3.9    | 4.0  | 4.1    | 4.3  |
| 57.5° | 3.7    | 3.7  | 3.8    | 3.9  | 4.0    | 4.1  |
| 58°   | 3.5    | 3.6  | 3.6    | 3.7  | 3.9    | 4.0  |
| 58.5° | 3.4    | 3.5  | 3.5    | 3.6  | 3.7    | 3.9  |
| 59°   | 3.4    | 3.4  | 3.4    | 3.5  | 3.6    | 3.7  |
| 59.5° | 3.2    | 3.2  | 3.3    | 3.4  | 3.5    | 3.6  |
| 60°   | 3.1    | 3.2  | 3.2    | 3.3  | 3.4    | 3.5  |
| 60.5° | 3.0    | 3.1  | 3.1    | 3.2  | 3.3    | 3.4  |
| 61°   | 2.9    | 2.9  | 3.0    | 3.1  | 3.2    | 3.3  |
| 61.5° | 2.9    | 2.9  | 2.9    | 3.0  | 3.1    | 3.2  |
| 62°   | 2.7    | 2.8  | 2.8    | 2.8  | 2.9    | 3.1  |
| 62.5° | 2.6    | 2.7  | 2.7    | 2.8  | 2.8    | 2.9  |
| 63°   | 2.6    | 2.6  | 2.6    | 2.7  | 2.8    | 2.9  |
| 63.5° | 2.5    | 2.5  | 2.5    | 2.6  | 2.7    | 2.7  |
| 64°   | 2.4    | 2.4  | 2.4    | 2.5  | 2.6    | 2.6  |
| 64.5° | 2.3    | 2.3  | 2.3    | 2.4  | 2.5    | 2.5  |
| 65°   | 2.2    | 2.2  | 2.2    | 2.3  | 2.4    | 2.4  |
| 65.5° | 2.1    | 2.1  | 2.1    | 2.2  | 2.3    | 2.4  |
| 66°   | 2.0    | 2.1  | 2.1    | 2.1  | 2.2    | 2.3  |
| 66.5° | 2.0    | 2.0  | 2.0    | 2.0  | 2.1    | 2.2  |
| 67°   | 1.9    | 1.9  | 1.9    | 1.9  | 2.0    | 2.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|-------|--------|------|--------|------|--------|------|
| 67.5° | 1.8    | 1.8  | 1.8    | 1.9  | 1.9    | 2.0  |
| 68°   | 1.7    | 1.7  | 1.8    | 1.8  | 1.8    | 1.9  |
| 68.5° | 1.7    | 1.7  | 1.7    | 1.7  | 1.8    | 1.8  |
| 69°   | 1.6    | 1.6  | 1.6    | 1.6  | 1.7    | 1.7  |
| 69.5° | 1.5    | 1.5  | 1.5    | 1.6  | 1.6    | 1.7  |
| 70°   | 1.5    | 1.5  | 1.5    | 1.5  | 1.5    | 1.6  |
| 70.5° | 1.4    | 1.4  | 1.4    | 1.4  | 1.5    | 1.5  |
| 71°   | 1.3    | 1.3  | 1.3    | 1.3  | 1.4    | 1.4  |
| 71.5° | 1.3    | 1.3  | 1.3    | 1.3  | 1.3    | 1.4  |
| 72°   | 1.2    | 1.2  | 1.2    | 1.2  | 1.3    | 1.3  |
| 72.5° | 1.1    | 1.1  | 1.1    | 1.1  | 1.2    | 1.2  |
| 73°   | 1.1    | 1.1  | 1.1    | 1.1  | 1.1    | 1.2  |
| 73.5° | 1.0    | 1.0  | 1.0    | 1.0  | 1.1    | 1.1  |
| 74°   | 1.0    | 1.0  | 1.0    | 1.0  | 1.0    | 1.0  |
| 74.5° | 0.9    | 0.9  | 0.9    | 0.9  | 0.9    | 1.0  |
| 75°   | 0.9    | 0.9  | 0.9    | 0.9  | 0.9    | 0.9  |
| 75.5° | 0.8    | 0.8  | 0.8    | 0.8  | 0.8    | 0.9  |
| 76°   | 0.8    | 0.8  | 0.8    | 0.8  | 0.8    | 0.8  |
| 76.5° | 0.7    | 0.7  | 0.7    | 0.7  | 0.7    | 0.8  |
| 77°   | 0.7    | 0.7  | 0.7    | 0.7  | 0.7    | 0.7  |
| 77.5° | 0.6    | 0.6  | 0.6    | 0.6  | 0.6    | 0.7  |
| 78°   | 0.6    | 0.6  | 0.6    | 0.6  | 0.6    | 0.6  |
| 78.5° | 0.5    | 0.5  | 0.5    | 0.5  | 0.6    | 0.6  |
| 79°   | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 79.5° | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 80°   | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 80.5° | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 81°   | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 81.5° | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 82°   | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 82.5° | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 83°   | 0.2    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 83.5° | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 84°   | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 84.5° | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 85°   | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 85.5° | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 86°   | 0.1    | 0.1  | 0.1    | 0.2  | 0.2    | 0.2  |
| 86.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 87°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 87.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 88°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 88.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 89°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 89.5° | 0.0    | 0.0  | 0.1    | 0.1  | 0.1    | 0.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|------|--------|------|--------|------|
| 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.1    | 0.1  |
| 90.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 91°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 91.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 93°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 93.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 96°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 96.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 98°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 98.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 99°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 99.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 100.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 103°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 103.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 110.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 111.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 112°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|------|--------|------|--------|------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 113°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 113.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 114°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 114.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 119°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 119.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 123°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 123.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 126°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 126.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 128°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 128.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 129°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 129.5° | 0.1    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 131°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.1    | 0.0  |
| 131.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.1    | 0.1  |
| 132°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 132.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 133°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 133.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 134°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 134.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|------|--------|------|--------|------|
| 135°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 135.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 136°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 136.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 137°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 137.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 138°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 138.5° | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 139°   | 0.1    | 0.1  | 0.1    | 0.1  | 0.1    | 0.1  |
| 139.5° | 0.2    | 0.2  | 0.1    | 0.1  | 0.1    | 0.1  |
| 140°   | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 140.5° | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 141°   | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 141.5° | 0.2    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 142°   | 0.3    | 0.2  | 0.2    | 0.2  | 0.2    | 0.2  |
| 142.5° | 0.3    | 0.3  | 0.3    | 0.3  | 0.2    | 0.2  |
| 143°   | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 143.5° | 0.3    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 144°   | 0.4    | 0.3  | 0.3    | 0.3  | 0.3    | 0.3  |
| 144.5° | 0.4    | 0.4  | 0.4    | 0.4  | 0.3    | 0.3  |
| 145°   | 0.4    | 0.4  | 0.4    | 0.4  | 0.4    | 0.4  |
| 145.5° | 0.5    | 0.5  | 0.4    | 0.4  | 0.4    | 0.4  |
| 146°   | 0.5    | 0.5  | 0.5    | 0.4  | 0.4    | 0.4  |
| 146.5° | 0.5    | 0.5  | 0.5    | 0.5  | 0.5    | 0.5  |
| 147°   | 0.6    | 0.6  | 0.5    | 0.5  | 0.5    | 0.5  |
| 147.5° | 0.6    | 0.6  | 0.6    | 0.6  | 0.5    | 0.5  |
| 148°   | 0.7    | 0.7  | 0.6    | 0.6  | 0.6    | 0.6  |
| 148.5° | 0.7    | 0.7  | 0.7    | 0.7  | 0.6    | 0.6  |
| 149°   | 0.8    | 0.8  | 0.7    | 0.7  | 0.7    | 0.7  |
| 149.5° | 0.9    | 0.8  | 0.8    | 0.7  | 0.7    | 0.7  |
| 150°   | 0.9    | 0.9  | 0.8    | 0.8  | 0.8    | 0.8  |
| 150.5° | 1.0    | 0.9  | 0.9    | 0.9  | 0.8    | 0.8  |
| 151°   | 1.1    | 1.0  | 1.0    | 0.9  | 0.9    | 0.9  |
| 151.5° | 1.1    | 1.1  | 1.0    | 1.0  | 1.0    | 0.9  |
| 152°   | 1.2    | 1.2  | 1.1    | 1.1  | 1.0    | 1.0  |
| 152.5° | 1.3    | 1.3  | 1.2    | 1.1  | 1.1    | 1.1  |
| 153°   | 1.4    | 1.3  | 1.3    | 1.2  | 1.2    | 1.1  |
| 153.5° | 1.4    | 1.4  | 1.3    | 1.3  | 1.2    | 1.2  |
| 154°   | 1.5    | 1.5  | 1.4    | 1.4  | 1.3    | 1.3  |
| 154.5° | 1.6    | 1.6  | 1.5    | 1.4  | 1.4    | 1.4  |
| 155°   | 1.7    | 1.6  | 1.6    | 1.5  | 1.5    | 1.5  |
| 155.5° | 1.8    | 1.7  | 1.6    | 1.6  | 1.6    | 1.5  |
| 156°   | 1.9    | 1.8  | 1.7    | 1.7  | 1.6    | 1.6  |
| 156.5° | 1.9    | 1.9  | 1.8    | 1.8  | 1.7    | 1.7  |
| 157°   | 2.0    | 2.0  | 1.9    | 1.8  | 1.8    | 1.8  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|------|--------|------|--------|------|
| 157.5° | 2.1    | 2.0  | 2.0    | 1.9  | 1.9    | 1.8  |
| 158°   | 2.2    | 2.1  | 2.1    | 2.0  | 1.9    | 1.9  |
| 158.5° | 2.3    | 2.2  | 2.1    | 2.1  | 2.0    | 2.0  |
| 159°   | 2.3    | 2.3  | 2.2    | 2.2  | 2.1    | 2.1  |
| 159.5° | 2.4    | 2.4  | 2.3    | 2.2  | 2.2    | 2.2  |
| 160°   | 2.5    | 2.4  | 2.4    | 2.3  | 2.3    | 2.3  |
| 160.5° | 2.6    | 2.5  | 2.5    | 2.4  | 2.4    | 2.4  |
| 161°   | 2.7    | 2.6  | 2.5    | 2.5  | 2.5    | 2.4  |
| 161.5° | 2.7    | 2.7  | 2.6    | 2.6  | 2.5    | 2.5  |
| 162°   | 2.8    | 2.7  | 2.7    | 2.6  | 2.6    | 2.6  |
| 162.5° | 2.8    | 2.8  | 2.7    | 2.7  | 2.7    | 2.6  |
| 163°   | 2.9    | 2.8  | 2.8    | 2.7  | 2.7    | 2.7  |
| 163.5° | 2.9    | 2.9  | 2.8    | 2.8  | 2.8    | 2.8  |
| 164°   | 3.0    | 2.9  | 2.9    | 2.9  | 2.8    | 2.8  |
| 164.5° | 3.0    | 3.0  | 2.9    | 2.9  | 2.9    | 2.9  |
| 165°   | 3.0    | 3.0  | 3.0    | 3.0  | 2.9    | 2.9  |
| 165.5° | 3.1    | 3.1  | 3.0    | 3.0  | 3.0    | 3.0  |
| 166°   | 3.1    | 3.1  | 3.1    | 3.1  | 3.1    | 3.0  |
| 166.5° | 3.2    | 3.1  | 3.1    | 3.1  | 3.1    | 3.1  |
| 167°   | 3.2    | 3.2  | 3.1    | 3.1  | 3.1    | 3.1  |
| 167.5° | 3.2    | 3.2  | 3.2    | 3.2  | 3.1    | 3.2  |
| 168°   | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 168.5° | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 169°   | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 169.5° | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 170°   | 3.2    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 170.5° | 3.1    | 3.2  | 3.2    | 3.2  | 3.2    | 3.2  |
| 171°   | 3.1    | 3.1  | 3.2    | 3.2  | 3.2    | 3.2  |
| 171.5° | 3.1    | 3.1  | 3.2    | 3.2  | 3.2    | 3.2  |
| 172°   | 3.1    | 3.1  | 3.1    | 3.2  | 3.2    | 3.2  |
| 172.5° | 3.1    | 3.1  | 3.1    | 3.2  | 3.2    | 3.2  |
| 173°   | 3.1    | 3.1  | 3.1    | 3.2  | 3.2    | 3.2  |
| 173.5° | 3.1    | 3.1  | 3.1    | 3.1  | 3.2    | 3.2  |
| 174°   | 3.0    | 3.1  | 3.1    | 3.1  | 3.2    | 3.2  |
| 174.5° | 3.0    | 3.0  | 3.0    | 3.1  | 3.1    | 3.2  |
| 175°   | 2.9    | 3.0  | 3.0    | 3.1  | 3.1    | 3.1  |
| 175.5° | 2.9    | 2.9  | 3.0    | 3.0  | 3.1    | 3.1  |
| 176°   | 2.9    | 2.9  | 3.0    | 3.0  | 3.0    | 3.1  |
| 176.5° | 2.9    | 2.9  | 2.9    | 3.0  | 3.0    | 3.0  |
| 177°   | 2.8    | 2.9  | 2.9    | 2.9  | 3.0    | 3.0  |
| 177.5° | 2.8    | 2.8  | 2.9    | 2.9  | 2.9    | 3.0  |
| 178°   | 2.8    | 2.8  | 2.8    | 2.9  | 2.9    | 2.9  |
| 178.5° | 2.8    | 2.8  | 2.8    | 2.8  | 2.9    | 2.9  |
| 179°   | 2.8    | 2.8  | 2.8    | 2.8  | 2.9    | 2.9  |
| 179.5° | 2.8    | 2.8  | 2.8    | 2.8  | 2.8    | 2.9  |



TEST NUMBER: P979231  
CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CANDELA DISTRIBUTION (continued):**

|      | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|------|--------|------|--------|------|--------|------|
| 180° | 2.8    | 2.8  | 2.8    | 2.8  | 2.8    | 2.8  |

TEST NUMBER: P979231

CATALOG NUMBER: PRLX-CYL2-X-927-10L-SP-U-S-X-X-WHTE

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 3.48             | 4.39 | 3.85 | 4.70 | 5.03 | 2.84           | 3.75 | 3.21 | 4.06 | 4.39 |
|                 | 3H   | 4.39             | 5.19 | 4.78 | 5.53 | 5.91 | 3.83           | 4.62 | 4.22 | 4.96 | 5.34 |
|                 | 4H   | 4.61             | 5.35 | 5.03 | 5.71 | 6.11 | 4.10           | 4.83 | 4.51 | 5.19 | 5.59 |
|                 | 6H   | 4.70             | 5.37 | 5.13 | 5.75 | 6.16 | 4.19           | 4.86 | 4.61 | 5.24 | 5.64 |
|                 | 8H   | 4.70             | 5.32 | 5.14 | 5.72 | 6.14 | 4.19           | 4.82 | 4.63 | 5.21 | 5.63 |
|                 | 12H  | 4.66             | 5.26 | 5.10 | 5.65 | 6.09 | 4.16           | 4.76 | 4.60 | 5.15 | 5.59 |
| 4H              | 2H   | 3.71             | 4.44 | 4.12 | 4.80 | 5.20 | 3.14           | 3.87 | 3.55 | 4.23 | 4.63 |
|                 | 3H   | 4.77             | 5.37 | 5.19 | 5.79 | 6.20 | 4.27           | 4.87 | 4.69 | 5.29 | 5.70 |
|                 | 4H   | 5.06             | 5.59 | 5.50 | 6.02 | 6.48 | 4.61           | 5.14 | 5.05 | 5.57 | 6.03 |
|                 | 6H   | 5.20             | 5.65 | 5.68 | 6.11 | 6.59 | 4.77           | 5.22 | 5.24 | 5.68 | 6.16 |
|                 | 8H   | 5.20             | 5.62 | 5.68 | 6.08 | 6.56 | 4.77           | 5.20 | 5.26 | 5.65 | 6.14 |
|                 | 12H  | 5.18             | 5.54 | 5.68 | 6.04 | 6.52 | 4.76           | 5.12 | 5.26 | 5.62 | 6.10 |
| 8H              | 4H   | 5.06             | 5.48 | 5.54 | 5.94 | 6.42 | 4.64           | 5.07 | 5.13 | 5.52 | 6.01 |
|                 | 6H   | 5.25             | 5.58 | 5.77 | 6.09 | 6.59 | 4.86           | 5.19 | 5.37 | 5.70 | 6.19 |
|                 | 8H   | 5.29             | 5.58 | 5.83 | 6.11 | 6.62 | 4.91           | 5.20 | 5.45 | 5.73 | 6.23 |
|                 | 12H  | 5.32             | 5.57 | 5.85 | 6.07 | 6.66 | 4.94           | 5.19 | 5.47 | 5.69 | 6.28 |
| 12H             | 4H   | 5.01             | 5.37 | 5.51 | 5.87 | 6.35 | 4.60           | 4.96 | 5.09 | 5.45 | 5.94 |
|                 | 6H   | 5.21             | 5.51 | 5.75 | 6.04 | 6.54 | 4.82           | 5.11 | 5.36 | 5.64 | 6.15 |
|                 | 8H   | 5.28             | 5.53 | 5.81 | 6.04 | 6.63 | 4.90           | 5.15 | 5.43 | 5.66 | 6.25 |

END OF REPORT