

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980423

Luminaire Tested: PRLX-243-935-LL5-F-U-S-WHTE-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P980423  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-32)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-243-935-LL5-F-U-S-WHTE-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 243 SHADE WITH FROSTED LENS  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4241.3 lumens  
Efficiency: N/A  
Efficacy: 143.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.36  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P980423  
CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-WHTE-X

### Luminous Intensity Polar Plot





TEST NUMBER: P980423

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-WHTE-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88																												
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																												
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																												
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59																												
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																												
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	46																												
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42																												
8	66	53	45	40	64	53	45	40	51	45	40	50	44	39	49	43	39	37																												
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34																												
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	9901
5°	9817
10°	9690
15°	9515
20°	9406
25°	9319
30°	9198
35°	9154
40°	9135
45°	9102
50°	8076
55°	3457
60°	2084
65°	2226
70°	2295
75°	2223
80°	2142
85°	2174

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9102 cd/sqm

TEST NUMBER: P980423

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-WHTE-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	4.4
10°-20°	526.0	12.4
20°-30°	788.3	18.6
30°-40°	951.6	22.4
40°-50°	989.9	23.3
50°-60°	445.3	10.5
60°-70°	186.9	4.4
70°-80°	123.5	2.9
80°-90°	42.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.0	35.4
0°-40°	2453.6	57.9
0°-60°	3888.9	91.7
0°-90°	4241.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4241.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2007	
5°	1982	188
15°	1863	526
25°	1712	788
35°	1520	952
45°	1304	990
55°	402	445
65°	191	187
75°	117	124
85°	38	42
90°	0	

TEST NUMBER: P980423

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-WHTE-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2006.8
2.5°	2001.3
5°	1982.1
7.5°	1960.2
10°	1934.1
12.5°	1901.2
15°	1862.8
17.5°	1825.7
20°	1791.4
22.5°	1755.8
25°	1711.9
27.5°	1662.5
30°	1614.5
32.5°	1566.5
35°	1519.8
37.5°	1471.8
40°	1418.3
42.5°	1362.1
45°	1304.5
47.5°	1229.0
50°	1052.1
52.5°	735.2
55°	401.9
57.5°	251.0
60°	211.2
62.5°	201.6
65°	190.7
67.5°	176.9
70°	159.1
72.5°	138.5
75°	116.6
77.5°	96.0
80°	75.4
82.5°	56.2
85°	38.4
87.5°	21.9
90°	0.0



TEST NUMBER: P980423  
 CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-WHTE-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.71	13.16	12.07	13.47	13.78	11.71	13.16	12.07	13.47	13.78
	3H	13.80	15.09	14.18	15.41	15.78	13.80	15.09	14.18	15.41	15.78
	4H	14.63	15.83	15.03	16.18	16.56	14.63	15.83	15.03	16.18	16.56
	6H	15.27	16.38	15.69	16.75	17.14	15.27	16.38	15.69	16.75	17.14
	8H	15.51	16.56	15.94	16.95	17.35	15.51	16.56	15.94	16.95	17.35
	12H	15.69	16.69	16.12	17.08	17.51	15.69	16.69	16.12	17.08	17.51
4H	2H	12.37	13.57	12.77	13.92	14.30	12.37	13.57	12.77	13.92	14.30
	3H	14.71	15.70	15.12	16.10	16.50	14.71	15.70	15.12	16.10	16.50
	4H	15.67	16.56	16.11	16.97	17.41	15.67	16.56	16.11	16.97	17.41
	6H	16.46	17.22	16.92	17.66	18.13	16.46	17.22	16.92	17.66	18.13
	8H	16.74	17.46	17.21	17.90	18.37	16.74	17.46	17.21	17.90	18.37
	12H	16.98	17.62	17.46	18.10	18.57	16.98	17.62	17.46	18.10	18.57
8H	4H	16.03	16.74	16.49	17.19	17.66	16.03	16.74	16.49	17.19	17.66
	6H	16.95	17.54	17.45	18.04	18.52	16.95	17.54	17.45	18.04	18.52
	8H	17.33	17.86	17.84	18.37	18.86	17.33	17.86	17.84	18.37	18.86
	12H	17.66	18.14	18.17	18.64	19.20	17.66	18.14	18.17	18.64	19.20
12H	4H	16.06	16.70	16.55	17.18	17.65	16.06	16.70	16.55	17.18	17.65
	6H	17.02	17.56	17.54	18.07	18.56	17.02	17.56	17.54	18.07	18.56
	8H	17.46	17.94	17.98	18.44	19.00	17.46	17.94	17.98	18.44	19.00