

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244807

Luminaire Tested: PRLX-MIN-L-930-02L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-L-930-02L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL LINES SHADE TEXTURE
LIGHT LEVEL 1
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 225.0 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 5.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56			
1	95	89	83	78	88	82	77	73	70	66	63	59	56	53	48	46	44	39			
2	85	76	68	62	79	70	63	58	60	54	50	50	46	42	41	38	35	30			
3	77	66	57	50	71	61	53	47	52	46	41	43	39	35	36	32	29	25			
4	71	58	49	42	65	54	46	40	46	40	35	39	34	30	32	28	25	21			
5	65	52	43	37	60	48	40	34	41	35	30	35	30	26	29	25	22	18			
6	60	47	38	32	55	44	36	30	38	31	26	32	27	23	27	22	19	16			
7	56	43	34	28	52	40	32	27	35	28	24	29	24	21	25	21	18	15			
8	52	39	31	25	48	37	29	24	32	26	21	27	22	19	23	19	16	14			
9	49	36	28	23	45	34	27	22	30	24	20	26	21	17	22	18	15	13			
10	46	34	26	21	43	32	25	20	28	22	18	24	19	16	21	17	14	12			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10317
5°	4731
10°	1102
15°	421
20°	271
25°	216
30°	193
35°	180
40°	174
45°	171
50°	169
55°	171
60°	172
65°	175
70°	176
75°	178
80°	178
85°	182

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 186 cd/sqm

TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.8	6.1
10°-20°	7.6	3.4
20°-30°	7.4	3.3
30°-40°	9.7	4.3
40°-50°	12.7	5.6
50°-60°	15.8	7.0
60°-70°	18.6	8.3
70°-80°	20.3	9.0
80°-90°	21.0	9.3
90°-100°	21.0	9.4
100°-110°	20.0	8.9
110°-120°	17.7	7.9
120°-130°	14.6	6.5
130°-140°	11.0	4.9
140°-150°	7.4	3.3
150°-160°	4.4	1.9
160°-170°	1.8	0.8
170°-180°	0.2	0.1
0°-30°	28.7	12.8
0°-40°	38.4	17.1
0°-60°	66.9	29.7
0°-90°	126.9	56.4
90°-120°	58.8	26.1
90°-150°	91.8	40.8
90°-180°	98.0	43.6
0°-180°	225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	326	
5°	192	14
15°	24	8
25°	16	7
35°	15	10
45°	16	13
55°	18	16
65°	19	19
75°	19	20
85°	19	16
90°	19	11
95°	19	16
105°	19	20
115°	18	18
125°	16	15
135°	14	11
145°	12	7
155°	9	4
165°	6	2
175°	1	0
180°	0	

TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	326.1
2.5°	357.8
5°	191.8
7.5°	78.1
10°	54.2
12.5°	33.2
15°	24.2
17.5°	20.1
20°	17.7
22.5°	16.5
25°	15.7
27.5°	15.4
30°	15.3
32.5°	15.3
35°	15.4
37.5°	15.5
40°	15.8
42.5°	16.0
45°	16.4
47.5°	16.7
50°	16.9
52.5°	17.3
55°	17.6
57.5°	18.0
60°	18.2
62.5°	18.5
65°	18.8
67.5°	19.0
70°	19.1
72.5°	19.2
75°	19.3
77.5°	19.2
80°	19.2
82.5°	19.2
85°	19.3
87.5°	19.3
90°	19.3
92.5°	19.3
95°	19.3
97.5°	19.3
100°	19.2
102.5°	19.1
105°	19.0
107.5°	18.8
110°	18.5

TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	18.2
115°	17.8
117.5°	17.5
120°	17.1
122.5°	16.7
125°	16.3
127.5°	15.8
130°	15.3
132.5°	14.8
135°	14.2
137.5°	13.6
140°	13.0
142.5°	12.4
145°	11.7
147.5°	11.2
150°	10.6
152.5°	9.9
155°	9.4
157.5°	8.7
160°	8.0
162.5°	7.2
165°	6.3
167.5°	5.1
170°	3.5
172.5°	2.1
175°	0.9
177.5°	0.2
180°	0.1

TEST NUMBER: P1244807

CATALOG NUMBER: PRLX-MIN-L-930-02L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.5	2.5	2.4	3.5	4.6	1.5	2.5	2.4	3.5	4.6
	3H	4.5	5.4	5.4	6.4	7.6	4.5	5.4	5.4	6.4	7.6
	4H	5.9	6.8	6.8	7.8	9.0	5.9	6.8	6.8	7.8	9.0
	6H	7.3	8.2	8.2	9.1	10.3	7.3	8.2	8.2	9.1	10.3
	8H	8.0	8.8	8.9	9.8	11.0	8.0	8.8	8.9	9.8	11.0
	12H	8.6	9.4	9.6	10.4	11.6	8.6	9.4	9.6	10.4	11.6
4H	2H	2.3	3.2	3.2	4.1	5.3	2.3	3.2	3.2	4.1	5.3
	3H	5.4	6.2	6.4	7.2	8.4	5.4	6.2	6.4	7.2	8.4
	4H	7.0	7.8	7.9	8.7	9.9	7.0	7.8	7.9	8.7	9.9
	6H	8.6	9.2	9.5	10.2	11.4	8.6	9.2	9.5	10.2	11.4
	8H	9.3	10.0	10.3	10.9	12.2	9.3	10.0	10.3	10.9	12.2
	12H	10.1	10.7	11.1	11.7	12.9	10.1	10.7	11.1	11.7	12.9
8H	4H	7.5	8.2	8.5	9.1	10.4	7.5	8.2	8.5	9.1	10.4
	6H	9.3	9.8	10.2	10.8	12.1	9.3	9.8	10.2	10.8	12.1
	8H	10.2	10.7	11.2	11.7	12.9	10.2	10.7	11.2	11.7	12.9
	12H	11.1	11.6	12.1	12.6	13.9	11.1	11.6	12.1	12.6	13.9
12H	4H	7.6	8.2	8.6	9.2	10.5	7.6	8.2	8.6	9.2	10.5
	6H	9.5	10.0	10.4	10.9	12.2	9.5	10.0	10.4	10.9	12.2
	8H	10.5	10.9	11.4	11.9	13.2	10.5	10.9	11.4	11.9	13.2

(END OF REPORT)