

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244907

Luminaire Tested: PRLX-MIN-M-930-07L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-930-07L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, OPEN WEAVE SHADE TEXTU
LIGHT LEVEL 5
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 747.9 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 28.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244907
CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1244907

CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	56
1	95	89	84	79	88	82	78	73	70	66	63		59	56	53		48	46	44	39
2	86	76	69	62	79	71	64	58	60	55	50		50	46	42		41	38	35	31
3	78	67	58	51	71	62	54	48	52	46	41		44	39	35		36	32	29	25
4	71	59	50	43	65	55	47	41	47	40	35		39	34	30		32	28	25	22
5	66	53	44	37	60	49	41	35	42	36	31		36	31	27		29	26	22	19
6	61	48	39	33	56	45	37	31	38	32	27		33	28	24		27	23	20	17
7	57	44	35	29	52	41	33	28	35	29	25		30	25	22		25	21	19	16
8	53	40	32	27	49	38	30	25	33	27	22		28	23	20		24	20	17	15
9	50	37	29	24	46	35	28	23	31	25	21		26	22	18		23	19	16	14
10	47	35	27	22	44	33	26	21	29	23	19		25	20	17		21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65146
5°	32928
10°	5900
15°	1879
20°	1176
25°	953
30°	828
35°	761
40°	737
45°	722
50°	713
55°	709
60°	711
65°	719
70°	732
75°	750
80°	762
85°	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 793 cd/sqm

TEST NUMBER: P1244907

CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	7.5
10°-20°	24.5	3.3
20°-30°	23.1	3.1
30°-40°	30.4	4.1
40°-50°	40.0	5.3
50°-60°	49.7	6.6
60°-70°	58.7	7.8
70°-80°	66.4	8.9
80°-90°	70.5	9.4
90°-100°	70.5	9.4
100°-110°	66.8	8.9
110°-120°	59.5	8.0
120°-130°	49.1	6.6
130°-140°	37.1	5.0
140°-150°	25.4	3.4
150°-160°	14.3	1.9
160°-170°	5.7	0.8
170°-180°	0.5	0.1
0°-30°	103.5	13.8
0°-40°	133.9	17.9
0°-60°	223.6	29.9
0°-90°	419.1	56.0
90°-120°	196.7	26.3
90°-150°	308.3	41.2
90°-180°	329.0	44.0
0°-180°	747.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1271	
5°	874	56
15°	75	24
25°	50	23
35°	48	30
45°	52	40
55°	55	50
65°	59	59
75°	63	66
85°	65	53
90°	65	35
95°	65	53
105°	63	67
115°	60	59
125°	54	49
135°	48	37
145°	40	25
155°	31	14
165°	20	6
175°	2	1
180°	0	

TEST NUMBER: P1244907

CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1271.2
2.5°	1404.4
5°	874.3
7.5°	289.9
10°	197.0
12.5°	107.9
15°	75.1
17.5°	61.9
20°	54.4
22.5°	51.6
25°	49.7
27.5°	47.8
30°	47.8
32.5°	47.8
35°	47.8
37.5°	48.8
40°	49.7
42.5°	50.7
45°	51.6
47.5°	52.5
50°	53.5
52.5°	54.4
55°	55.3
57.5°	56.3
60°	57.2
62.5°	58.2
65°	59.1
67.5°	60.0
70°	61.0
72.5°	61.9
75°	62.9
77.5°	63.8
80°	63.8
82.5°	64.7
85°	64.7
87.5°	64.7
90°	64.7
92.5°	64.7
95°	64.7
97.5°	64.7
100°	63.8
102.5°	63.8
105°	62.9
107.5°	62.9
110°	61.9

TEST NUMBER: P1244907

CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	61.0
115°	60.0
117.5°	59.1
120°	57.2
122.5°	56.3
125°	54.4
127.5°	53.5
130°	51.6
132.5°	49.7
135°	47.8
137.5°	46.0
140°	44.1
142.5°	42.2
145°	40.3
147.5°	38.5
150°	35.6
152.5°	32.8
155°	31.0
157.5°	28.1
160°	25.3
162.5°	23.5
165°	19.7
167.5°	15.9
170°	11.3
172.5°	6.6
175°	1.9
177.5°	0.0
180°	0.0



TEST NUMBER: P1244907

CATALOG NUMBER: PRLX-MIN-M-930-07L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.2	7.2	7.1	8.1	9.3	6.2	7.2	7.1	8.1	9.3
	3H	9.2	10.2	10.1	11.1	12.3	9.2	10.2	10.1	11.1	12.3
	4H	10.7	11.6	11.6	12.6	13.8	10.7	11.6	11.6	12.6	13.8
	6H	12.2	13.0	13.1	14.0	15.2	12.2	13.0	13.1	14.0	15.2
	8H	12.9	13.7	13.8	14.7	15.9	12.9	13.7	13.8	14.7	15.9
	12H	13.6	14.4	14.5	15.3	16.6	13.6	14.4	14.5	15.3	16.6
4H	2H	7.0	7.9	7.9	8.8	10.0	7.0	7.9	7.9	8.8	10.0
	3H	10.2	11.0	11.1	11.9	13.2	10.2	11.0	11.1	11.9	13.2
	4H	11.8	12.6	12.8	13.5	14.8	11.8	12.6	12.8	13.5	14.8
	6H	13.5	14.1	14.4	15.1	16.3	13.5	14.1	14.4	15.1	16.3
	8H	14.3	14.9	15.2	15.9	17.1	14.3	14.9	15.2	15.9	17.1
	12H	15.1	15.6	16.0	16.6	17.9	15.1	15.6	16.0	16.6	17.9
8H	4H	12.4	13.0	13.3	14.0	15.2	12.4	13.0	13.3	14.0	15.2
	6H	14.2	14.7	15.2	15.8	17.0	14.2	14.7	15.2	15.8	17.0
	8H	15.2	15.6	16.1	16.6	17.9	15.2	15.6	16.1	16.6	17.9
	12H	16.1	16.6	17.1	17.6	18.9	16.1	16.6	17.1	17.6	18.9
12H	4H	12.5	13.0	13.4	14.0	15.3	12.5	13.0	13.4	14.0	15.3
	6H	14.4	14.9	15.4	15.9	17.2	14.4	14.9	15.4	15.9	17.2
	8H	15.4	15.9	16.4	16.9	18.2	15.4	15.9	16.4	16.9	18.2

(END OF REPORT)