

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1057184

Luminaire Tested: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

Issue Date: 8/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057184
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2504-407-5)
Test Lab: INNOVATION CENTER
Issue Date: 8/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK
Description: PrentaLux 2-INCH CYLINDER
DOWNLIGHT 1000 LUMENS, SPOT OPTIC (19-DEGREES)
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1162.4 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.15' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

Luminous Intensity Polar Plot



TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	81	79		
7	94	87	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	79	76	81	78	76	81	78	75	74		
9	88	81	77	74	87	81	76	74	80	76	73	79	76	73	78	75	73	72		
10	86	79	74	71	85	78	74	71	77	74	71	77	73	71	76	73	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3929220	3929220	3929220
5°	3279882	3279882	3279882
10°	1870360	1870360	1870360
15°	895252	895252	895252
20°	501166	501166	501166
25°	351111	351111	351111
30°	243325	243325	243325
35°	127759	127759	127759
40°	47109	47109	47109
45°	14035	14035	14035
50°	6617	6617	6617
55°	4943	4943	4943
60°	4253	4253	4253
65°	3355	3355	3355
70°	2073	2073	2073
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14035 cd/sqm

TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	408.3	35.1
10°-20°	397.6	34.2
20°-30°	228.8	19.7
30°-40°	105.5	9.1
40°-50°	16.0	1.4
50°-60°	3.8	0.3
60°-70°	1.9	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.7	89.0
0°-40°	1140.2	98.1
0°-60°	1160.0	99.8
0°-90°	1162.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1162.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6097	6097	6097	6097	6097	
5°	5070	5070	5070	5070	5070	408
15°	1342	1342	1342	1342	1342	398
25°	494	494	494	494	494	229
35°	162	162	162	162	162	106
45°	15	15	15	15	15	16
55°	4	4	4	4	4	4
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6097.3	6097.3	6097.3	6097.3	6097.3
1°	5981.9	5981.9	5981.9	5981.9	5981.9
2°	5866.4	5866.4	5866.4	5866.4	5866.4
3°	5661.0	5661.0	5661.0	5661.0	5661.0
4°	5365.7	5365.7	5365.7	5365.7	5365.7
5°	5070.3	5070.3	5070.3	5070.3	5070.3
6°	4638.9	4638.9	4638.9	4638.9	4638.9
7°	4207.4	4207.4	4207.4	4207.4	4207.4
8°	3765.0	3765.0	3765.0	3765.0	3765.0
9°	3311.7	3311.7	3311.7	3311.7	3311.7
10°	2858.3	2858.3	2858.3	2858.3	2858.3
11°	2496.6	2496.6	2496.6	2496.6	2496.6
12°	2135.0	2135.0	2135.0	2135.0	2135.0
13°	1831.7	1831.7	1831.7	1831.7	1831.7
14°	1586.8	1586.8	1586.8	1586.8	1586.8
15°	1341.9	1341.9	1341.9	1341.9	1341.9
16°	1188.3	1188.3	1188.3	1188.3	1188.3
17°	1034.7	1034.7	1034.7	1034.7	1034.7
18°	912.5	912.5	912.5	912.5	912.5
19°	821.6	821.6	821.6	821.6	821.6
20°	730.8	730.8	730.8	730.8	730.8
21°	675.0	675.0	675.0	675.0	675.0
22°	619.3	619.3	619.3	619.3	619.3
23°	571.9	571.9	571.9	571.9	571.9
24°	532.8	532.8	532.8	532.8	532.8
25°	493.8	493.8	493.8	493.8	493.8
26°	460.4	460.4	460.4	460.4	460.4
27°	427.0	427.0	427.0	427.0	427.0
28°	393.7	393.7	393.7	393.7	393.7
29°	360.3	360.3	360.3	360.3	360.3
30°	327.0	327.0	327.0	327.0	327.0
31°	292.3	292.3	292.3	292.3	292.3
32°	257.6	257.6	257.6	257.6	257.6
33°	224.7	224.7	224.7	224.7	224.7
34°	193.6	193.6	193.6	193.6	193.6
35°	162.4	162.4	162.4	162.4	162.4
36°	137.4	137.4	137.4	137.4	137.4
37°	112.4	112.4	112.4	112.4	112.4
38°	91.1	91.1	91.1	91.1	91.1
39°	73.5	73.5	73.5	73.5	73.5
40°	56.0	56.0	56.0	56.0	56.0
41°	45.4	45.4	45.4	45.4	45.4
42°	34.9	34.9	34.9	34.9	34.9
43°	26.8	26.8	26.8	26.8	26.8
44°	21.1	21.1	21.1	21.1	21.1

TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
45°	15.4	15.4	15.4	15.4	15.4
46°	12.7	12.7	12.7	12.7	12.7
47°	10.1	10.1	10.1	10.1	10.1
48°	8.3	8.3	8.3	8.3	8.3
49°	7.5	7.5	7.5	7.5	7.5
50°	6.6	6.6	6.6	6.6	6.6
51°	5.7	5.7	5.7	5.7	5.7
52°	4.8	4.8	4.8	4.8	4.8
53°	4.4	4.4	4.4	4.4	4.4
54°	4.4	4.4	4.4	4.4	4.4
55°	4.4	4.4	4.4	4.4	4.4
56°	4.0	4.0	4.0	4.0	4.0
57°	3.5	3.5	3.5	3.5	3.5
58°	3.3	3.3	3.3	3.3	3.3
59°	3.3	3.3	3.3	3.3	3.3
60°	3.3	3.3	3.3	3.3	3.3
61°	2.9	2.9	2.9	2.9	2.9
62°	2.4	2.4	2.4	2.4	2.4
63°	2.2	2.2	2.2	2.2	2.2
64°	2.2	2.2	2.2	2.2	2.2
65°	2.2	2.2	2.2	2.2	2.2
66°	1.8	1.8	1.8	1.8	1.8
67°	1.3	1.3	1.3	1.3	1.3
68°	1.1	1.1	1.1	1.1	1.1
69°	1.1	1.1	1.1	1.1	1.1
70°	1.1	1.1	1.1	1.1	1.1
71°	1.1	1.1	1.1	1.1	1.1
72°	1.1	1.1	1.1	1.1	1.1
73°	0.9	0.9	0.9	0.9	0.9
74°	0.4	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.0	0.0	0.0
76°	0.0	0.0	0.0	0.0	0.0
77°	0.0	0.0	0.0	0.0	0.0
78°	0.0	0.0	0.0	0.0	0.0
79°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
81°	0.0	0.0	0.0	0.0	0.0
82°	0.0	0.0	0.0	0.0	0.0
83°	0.0	0.0	0.0	0.0	0.0
84°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
86°	0.0	0.0	0.0	0.0	0.0
87°	0.0	0.0	0.0	0.0	0.0
88°	0.0	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1057184
CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1057184

CATALOG NUMBER: PRLX-CYL2S-X-930-10L-SP-U-S-X-X-BLAK

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.93	4.83	4.30	5.15	5.46	3.93	4.83	4.30	5.15	5.46
	3H	4.37	5.16	4.75	5.49	5.86	4.37	5.16	4.75	5.49	5.86
	4H	4.32	5.05	4.72	5.40	5.79	4.32	5.05	4.72	5.40	5.79
	6H	4.20	4.87	4.62	5.24	5.64	4.20	4.87	4.62	5.24	5.64
	8H	4.14	4.76	4.58	5.15	5.57	4.14	4.76	4.58	5.15	5.57
	12H	4.07	4.67	4.51	5.05	5.49	4.07	4.67	4.51	5.05	5.49
4H	2H	4.25	4.98	4.66	5.33	5.72	4.25	4.98	4.66	5.33	5.72
	3H	4.87	5.46	5.28	5.87	6.28	4.87	5.46	5.28	5.87	6.28
	4H	4.78	5.31	5.22	5.74	6.19	4.78	5.31	5.22	5.74	6.19
	6H	4.66	5.11	5.13	5.56	6.04	4.66	5.11	5.13	5.56	6.04
	8H	4.59	5.01	5.06	5.46	5.93	4.59	5.01	5.06	5.46	5.93
	12H	4.52	4.87	5.01	5.37	5.84	4.52	4.87	5.01	5.37	5.84
8H	4H	4.65	5.07	5.13	5.52	5.99	4.65	5.07	5.13	5.52	5.99
	6H	4.52	4.84	5.03	5.35	5.84	4.52	4.84	5.03	5.35	5.84
	8H	4.44	4.73	4.98	5.25	5.75	4.44	4.73	4.98	5.25	5.75
	12H	4.38	4.63	4.91	5.13	5.71	4.38	4.63	4.91	5.13	5.71
12H	4H	4.58	4.94	5.07	5.43	5.91	4.58	4.94	5.07	5.43	5.91
	6H	4.44	4.73	4.98	5.25	5.75	4.44	4.73	4.98	5.25	5.75
	8H	4.38	4.63	4.91	5.13	5.71	4.38	4.63	4.91	5.13	5.71