

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244956

Luminaire Tested: PRLX-MIN-S-930-02L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244956
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-S-930-02L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, PINSTRIPE SHADE TEXTURE
LIGHT LEVEL 1
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 259.0 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.38
Luminous Opening: Rectangular w/ Sides (W: 0.62' x L: 0.62' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 6.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

Luminous Intensity Polar Plot



TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97		87	87	87		78
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58
3	85	74	66	60	80	71	63	58	64	58	53		58	53	49		52
4	78	66	58	52	74	63	56	50	58	51	46		52	47	43		47
5	72	60	52	46	68	58	50	44	53	46	41		48	43	38		44
6	67	55	47	41	64	53	45	39	48	42	37		44	39	35		40
7	63	51	42	37	60	49	41	36	45	38	34		41	36	32		38
8	59	47	39	34	56	45	38	33	42	35	31		38	33	29		35
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		33
10	53	41	34	29	50	39	33	28	37	31	27		34	29	26		32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6024
5°	5992
10°	5300
15°	1261
20°	1055
25°	885
30°	704
35°	581
40°	508
45°	463
50°	426
55°	399
60°	375
65°	353
70°	337
75°	318
80°	291
85°	271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 463 cd/sqm

TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.7	8.8
10°-20°	23.9	9.2
20°-30°	21.8	8.4
30°-40°	21.6	8.3
40°-50°	22.0	8.5
50°-60°	22.2	8.6
60°-70°	21.5	8.3
70°-80°	19.5	7.5
80°-90°	16.0	6.2
90°-100°	15.0	5.8
100°-110°	14.3	5.5
110°-120°	12.8	4.9
120°-130°	10.6	4.1
130°-140°	7.6	2.9
140°-150°	4.3	1.7
150°-160°	2.3	0.9
160°-170°	0.9	0.3
170°-180°	0.1	0.0
0°-30°	68.4	26.4
0°-40°	90.0	34.7
0°-60°	134.1	51.8
0°-90°	191.1	73.8
90°-120°	42.2	16.3
90°-150°	64.7	25.0
90°-180°	68.0	26.3
0°-180°	259.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	219	
5°	243	23
15°	61	24
25°	48	22
35°	34	22
45°	28	22
55°	25	22
65°	22	21
75°	18	19
85°	14	12
90°	14	8
95°	14	11
105°	14	14
115°	13	13
125°	12	11
135°	10	8
145°	7	4
155°	5	2
165°	3	1
175°	0	0
180°	0	

TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	218.6
2.5°	226.6
5°	243.0
7.5°	240.1
10°	235.9
12.5°	104.4
15°	60.7
17.5°	57.5
20°	54.2
22.5°	51.4
25°	48.0
27.5°	43.6
30°	39.9
32.5°	36.5
35°	34.1
37.5°	32.1
40°	30.6
42.5°	29.4
45°	28.4
47.5°	27.4
50°	26.4
52.5°	25.6
55°	24.8
57.5°	24.0
60°	23.2
62.5°	22.4
65°	21.6
67.5°	21.0
70°	20.2
72.5°	19.4
75°	18.5
77.5°	17.5
80°	16.3
82.5°	15.1
85°	14.5
87.5°	14.1
90°	13.9
92.5°	13.9
95°	13.7
97.5°	13.7
100°	13.7
102.5°	13.7
105°	13.5
107.5°	13.5
110°	13.3

TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	13.1
115°	12.9
117.5°	12.7
120°	12.5
122.5°	12.1
125°	11.9
127.5°	11.5
130°	10.9
132.5°	10.5
135°	9.7
137.5°	9.1
140°	8.3
142.5°	7.5
145°	6.7
147.5°	6.2
150°	5.8
152.5°	5.4
155°	4.8
157.5°	4.4
160°	4.0
162.5°	3.6
165°	3.0
167.5°	2.4
170°	1.6
172.5°	0.8
175°	0.2
177.5°	0.0
180°	0.0

TEST NUMBER: P1244956

CATALOG NUMBER: PRLX-MIN-S-930-02L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.5	6.6	6.2	7.4	8.3	5.5	6.6	6.2	7.4	8.3
	3H	7.8	8.8	8.5	9.6	10.5	7.8	8.8	8.5	9.6	10.5
	4H	8.8	9.8	9.6	10.6	11.5	8.8	9.8	9.6	10.6	11.5
	6H	9.8	10.7	10.6	11.5	12.5	9.8	10.7	10.6	11.5	12.5
	8H	10.2	11.1	11.0	11.9	12.9	10.2	11.1	11.0	11.9	12.9
	12H	10.6	11.5	11.4	12.3	13.2	10.6	11.5	11.4	12.3	13.2
4H	2H	6.1	7.1	6.8	7.8	8.8	6.1	7.1	6.8	7.8	8.8
	3H	8.6	9.5	9.4	10.3	11.2	8.6	9.5	9.4	10.3	11.2
	4H	9.8	10.6	10.6	11.4	12.4	9.8	10.6	10.6	11.4	12.4
	6H	10.9	11.6	11.7	12.5	13.4	10.9	11.6	11.7	12.5	13.4
	8H	11.4	12.1	12.2	12.9	13.9	11.4	12.1	12.2	12.9	13.9
	12H	11.9	12.5	12.8	13.4	14.4	11.9	12.5	12.8	13.4	14.4
8H	4H	10.2	10.9	11.0	11.7	12.7	10.2	10.9	11.0	11.7	12.7
	6H	11.5	12.1	12.3	12.9	13.9	11.5	12.1	12.3	12.9	13.9
	8H	12.1	12.6	13.0	13.5	14.5	12.1	12.6	13.0	13.5	14.5
	12H	12.8	13.2	13.6	14.1	15.1	12.8	13.2	13.6	14.1	15.1
12H	4H	10.3	10.9	11.1	11.7	12.7	10.3	10.9	11.1	11.7	12.7
	6H	11.6	12.1	12.5	13.0	14.0	11.6	12.1	12.5	13.0	14.0
	8H	12.3	12.8	13.2	13.6	14.7	12.3	12.8	13.2	13.6	14.7

(END OF REPORT)