

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244922

Luminaire Tested: PRLX-MIN-M-935-07L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-935-07L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, OPEN WEAVE SHADE TEXTU
LIGHT LEVEL 5
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 772.0 lumens
Efficiency: N/A
Efficacy: 26.7 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 28.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	95	89	84	79	88	82	78	73	70	66	63	59	56	53	48	46	44	39		
2	86	76	69	62	79	71	64	58	60	55	50	50	46	42	41	38	35	31		
3	78	67	58	51	71	62	54	48	52	46	41	44	39	35	36	32	29	25		
4	71	59	50	43	65	55	47	41	47	40	35	39	34	30	32	28	25	22		
5	66	53	44	37	60	49	41	35	42	36	31	36	31	27	29	26	22	19		
6	61	48	39	33	56	45	37	31	38	32	27	33	28	24	27	23	20	17		
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	19	16		
8	53	40	32	27	49	38	30	25	33	27	22	28	23	20	24	20	17	15		
9	50	37	29	24	46	35	28	23	31	25	21	26	22	18	23	19	16	14		
10	47	35	27	22	44	33	26	21	29	23	19	25	20	17	21	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67236
5°	33987
10°	6089
15°	1939
20°	1215
25°	983
30°	856
35°	787
40°	761
45°	745
50°	735
55°	732
60°	735
65°	742
70°	755
75°	774
80°	786
85°	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 819 cd/sqm

TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	7.5
10°-20°	25.3	3.3
20°-30°	23.8	3.1
30°-40°	31.3	4.1
40°-50°	41.3	5.3
50°-60°	51.3	6.6
60°-70°	60.6	7.8
70°-80°	68.5	8.9
80°-90°	72.7	9.4
90°-100°	72.7	9.4
100°-110°	68.9	8.9
110°-120°	61.4	8.0
120°-130°	50.7	6.6
130°-140°	38.3	5.0
140°-150°	26.2	3.4
150°-160°	14.8	1.9
160°-170°	5.9	0.8
170°-180°	0.5	0.1
0°-30°	106.9	13.8
0°-40°	138.2	17.9
0°-60°	230.8	29.9
0°-90°	432.6	56.0
90°-120°	203.1	26.3
90°-150°	318.2	41.2
90°-180°	339.0	43.9
0°-180°	772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1312	
5°	902	58
15°	78	25
25°	51	24
35°	49	31
45°	53	41
55°	57	51
65°	61	61
75°	65	68
85°	67	54
90°	67	37
95°	67	54
105°	65	69
115°	62	61
125°	56	51
135°	49	38
145°	42	26
155°	32	15
165°	20	6
175°	2	1
180°	0	

TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1312.0
2.5°	1449.4
5°	902.4
7.5°	299.2
10°	203.3
12.5°	111.3
15°	77.5
17.5°	63.9
20°	56.2
22.5°	53.3
25°	51.3
27.5°	49.4
30°	49.4
32.5°	49.4
35°	49.4
37.5°	50.3
40°	51.3
42.5°	52.3
45°	53.3
47.5°	54.2
50°	55.2
52.5°	56.2
55°	57.1
57.5°	58.1
60°	59.1
62.5°	60.0
65°	61.0
67.5°	62.0
70°	62.9
72.5°	63.9
75°	64.9
77.5°	65.8
80°	65.8
82.5°	66.8
85°	66.8
87.5°	66.8
90°	66.8
92.5°	66.8
95°	66.8
97.5°	66.8
100°	65.8
102.5°	65.8
105°	64.9
107.5°	64.9
110°	63.9

TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	62.9
115°	62.0
117.5°	61.0
120°	59.1
122.5°	58.1
125°	56.2
127.5°	55.2
130°	53.3
132.5°	51.3
135°	49.4
137.5°	47.4
140°	45.5
142.5°	43.6
145°	41.6
147.5°	39.7
150°	36.8
152.5°	33.9
155°	32.0
157.5°	29.0
160°	26.1
162.5°	24.2
165°	20.3
167.5°	16.5
170°	11.6
172.5°	6.8
175°	1.9
177.5°	0.0
180°	0.0

TEST NUMBER: P1244922

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.3	7.3	7.2	8.2	9.4	6.3	7.3	7.2	8.2	9.4
	3H	9.3	10.3	10.2	11.2	12.4	9.3	10.3	10.2	11.2	12.4
	4H	10.8	11.7	11.7	12.7	13.9	10.8	11.7	11.7	12.7	13.9
	6H	12.3	13.2	13.2	14.1	15.3	12.3	13.2	13.2	14.1	15.3
	8H	13.0	13.8	13.9	14.8	16.0	13.0	13.8	13.9	14.8	16.0
	12H	13.7	14.5	14.6	15.4	16.7	13.7	14.5	14.6	15.4	16.7
4H	2H	7.1	8.0	8.0	8.9	10.1	7.1	8.0	8.0	8.9	10.1
	3H	10.3	11.1	11.2	12.0	13.3	10.3	11.1	11.2	12.0	13.3
	4H	11.9	12.7	12.9	13.6	14.9	11.9	12.7	12.9	13.6	14.9
	6H	13.6	14.2	14.5	15.2	16.5	13.6	14.2	14.5	15.2	16.5
	8H	14.4	15.0	15.3	16.0	17.2	14.4	15.0	15.3	16.0	17.2
	12H	15.2	15.7	16.1	16.7	18.0	15.2	15.7	16.1	16.7	18.0
8H	4H	12.5	13.1	13.4	14.1	15.3	12.5	13.1	13.4	14.1	15.3
	6H	14.3	14.8	15.3	15.9	17.1	14.3	14.8	15.3	15.9	17.1
	8H	15.3	15.7	16.2	16.7	18.0	15.3	15.7	16.2	16.7	18.0
	12H	16.2	16.7	17.2	17.7	19.0	16.2	16.7	17.2	17.7	19.0
12H	4H	12.6	13.2	13.5	14.1	15.4	12.6	13.2	13.5	14.1	15.4
	6H	14.5	15.0	15.5	16.0	17.3	14.5	15.0	15.5	16.0	17.3
	8H	15.5	16.0	16.5	17.0	18.3	15.5	16.0	16.5	17.0	18.3

(END OF REPORT)