

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244926

Luminaire Tested: PRLX-MIN-M-940-01L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-940-01L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 1
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 166.0 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 6.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	56
1	95	89	84	79	88	82	78	73	70	66	63		59	56	53		48	46	44	39
2	86	76	69	62	79	71	64	58	60	55	50		50	46	42		41	38	35	30
3	78	67	58	51	71	62	54	48	52	46	41		44	39	35		36	32	29	25
4	71	59	50	43	65	55	47	41	47	40	35		39	34	30		32	28	25	22
5	66	53	44	37	60	49	41	35	42	36	31		36	30	27		29	26	22	19
6	61	48	39	33	56	45	37	31	38	32	27		33	28	24		27	23	20	17
7	57	44	35	29	52	41	33	28	35	29	25		30	25	22		25	21	18	16
8	53	40	32	27	49	38	30	25	33	27	22		28	23	20		24	20	17	15
9	50	37	29	24	46	35	28	23	31	25	21		26	22	18		23	19	16	14
10	47	35	27	22	44	33	26	21	29	23	19		25	20	17		21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14457
5°	7307
10°	1309
15°	418
20°	262
25°	211
30°	184
35°	169
40°	163
45°	161
50°	159
55°	158
60°	158
65°	159
70°	162
75°	166
80°	170
85°	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 176 cd/sqm



TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.4	7.5
10°-20°	5.4	3.3
20°-30°	5.1	3.1
30°-40°	6.7	4.1
40°-50°	8.9	5.4
50°-60°	11.0	6.7
60°-70°	13.0	7.8
70°-80°	14.7	8.9
80°-90°	15.7	9.4
90°-100°	15.7	9.4
100°-110°	14.8	8.9
110°-120°	13.2	7.9
120°-130°	10.9	6.6
130°-140°	8.2	5.0
140°-150°	5.6	3.4
150°-160°	3.2	1.9
160°-170°	1.3	0.8
170°-180°	0.1	0.1
0°-30°	23.0	13.8
0°-40°	29.7	17.9
0°-60°	49.6	29.9
0°-90°	93.0	56.0
90°-120°	43.7	26.3
90°-150°	68.5	41.2
90°-180°	73.0	44.0
0°-180°	166.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	282	
5°	194	12
15°	17	5
25°	11	5
35°	11	7
45°	12	9
55°	12	11
65°	13	13
75°	14	15
85°	14	12
90°	14	8
95°	14	12
105°	14	15
115°	13	13
125°	12	11
135°	11	8
145°	9	6
155°	7	3
165°	4	1
175°	0	0
180°	0	

TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	282.1
2.5°	311.7
5°	194.0
7.5°	64.3
10°	43.7
12.5°	23.9
15°	16.7
17.5°	13.7
20°	12.1
22.5°	11.5
25°	11.0
27.5°	10.6
30°	10.6
32.5°	10.6
35°	10.6
37.5°	10.8
40°	11.0
42.5°	11.2
45°	11.5
47.5°	11.7
50°	11.9
52.5°	12.1
55°	12.3
57.5°	12.5
60°	12.7
62.5°	12.9
65°	13.1
67.5°	13.3
70°	13.5
72.5°	13.7
75°	13.9
77.5°	14.2
80°	14.2
82.5°	14.4
85°	14.4
87.5°	14.4
90°	14.4
92.5°	14.4
95°	14.4
97.5°	14.4
100°	14.2
102.5°	14.2
105°	13.9
107.5°	13.9
110°	13.7

TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	13.5
115°	13.3
117.5°	13.1
120°	12.7
122.5°	12.5
125°	12.1
127.5°	11.9
130°	11.5
132.5°	11.0
135°	10.6
137.5°	10.2
140°	9.8
142.5°	9.4
145°	9.0
147.5°	8.5
150°	7.9
152.5°	7.3
155°	6.9
157.5°	6.2
160°	5.6
162.5°	5.2
165°	4.4
167.5°	3.5
170°	2.5
172.5°	1.5
175°	0.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1244926

CATALOG NUMBER: PRLX-MIN-M-940-01L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.0	2.0	1.8	2.9	4.1	1.0	2.0	1.8	2.9	4.1
	3H	4.0	4.9	4.9	5.9	7.1	4.0	4.9	4.9	5.9	7.1
	4H	5.5	6.4	6.4	7.3	8.5	5.5	6.4	6.4	7.3	8.5
	6H	7.0	7.8	7.9	8.8	10.0	7.0	7.8	7.9	8.8	10.0
	8H	7.7	8.5	8.6	9.4	10.7	7.7	8.5	8.6	9.4	10.7
	12H	8.4	9.1	9.3	10.1	11.3	8.4	9.1	9.3	10.1	11.3
4H	2H	1.7	2.6	2.6	3.6	4.8	1.7	2.6	2.6	3.6	4.8
	3H	4.9	5.7	5.9	6.7	7.9	4.9	5.7	5.9	6.7	7.9
	4H	6.6	7.3	7.5	8.3	9.5	6.6	7.3	7.5	8.3	9.5
	6H	8.2	8.9	9.2	9.9	11.1	8.2	8.9	9.2	9.9	11.1
	8H	9.0	9.7	10.0	10.6	11.9	9.0	9.7	10.0	10.6	11.9
	12H	9.8	10.4	10.8	11.4	12.7	9.8	10.4	10.8	11.4	12.7
8H	4H	7.1	7.7	8.1	8.7	10.0	7.1	7.7	8.1	8.7	10.0
	6H	9.0	9.5	9.9	10.5	11.8	9.0	9.5	9.9	10.5	11.8
	8H	9.9	10.4	10.9	11.4	12.7	9.9	10.4	10.9	11.4	12.7
	12H	10.9	11.3	11.9	12.3	13.6	10.9	11.3	11.9	12.3	13.6
12H	4H	7.2	7.8	8.2	8.8	10.1	7.2	7.8	8.2	8.8	10.1
	6H	9.2	9.7	10.1	10.6	11.9	9.2	9.7	10.1	10.6	11.9
	8H	10.2	10.6	11.2	11.6	12.9	10.2	10.6	11.2	11.6	12.9

(END OF REPORT)