

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244932

Luminaire Tested: PRLX-MIN-M-940-04L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-940-04L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 501.9 lumens
Efficiency: N/A
Efficacy: 31.0 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	95	89	84	79	88	82	78	73	70	66	63	59	56	53	48	46	44	39		
2	86	76	69	62	79	71	64	58	60	55	50	50	46	42	41	38	35	31		
3	78	67	58	51	71	62	54	48	52	46	41	44	39	35	36	32	29	25		
4	71	59	50	43	65	55	47	41	47	40	35	39	34	30	32	28	25	22		
5	66	53	44	37	60	49	41	35	42	36	31	36	31	27	29	26	22	19		
6	61	48	39	33	56	45	37	31	38	32	27	33	28	24	27	23	20	17		
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	19	16		
8	53	40	32	27	49	38	30	25	33	27	22	28	23	20	24	20	17	15		
9	50	37	29	24	46	35	28	23	31	25	21	26	22	18	23	19	16	14		
10	47	35	27	22	44	33	26	21	29	23	19	25	20	17	21	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43719
5°	22100
10°	3960
15°	1261
20°	789
25°	640
30°	556
35°	511
40°	496
45°	484
50°	478
55°	475
60°	477
65°	483
70°	491
75°	503
80°	511
85°	523

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 532 cd/sqm

TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	7.5
10°-20°	16.4	3.3
20°-30°	15.5	3.1
30°-40°	20.4	4.1
40°-50°	26.9	5.3
50°-60°	33.3	6.6
60°-70°	39.4	7.8
70°-80°	44.6	8.9
80°-90°	47.3	9.4
90°-100°	47.3	9.4
100°-110°	44.8	8.9
110°-120°	39.9	8.0
120°-130°	32.9	6.6
130°-140°	24.9	5.0
140°-150°	17.0	3.4
150°-160°	9.6	1.9
160°-170°	3.8	0.8
170°-180°	0.3	0.1
0°-30°	69.5	13.8
0°-40°	89.9	17.9
0°-60°	150.0	29.9
0°-90°	281.3	56.0
90°-120°	132.0	26.3
90°-150°	206.9	41.2
90°-180°	221.0	44.0
0°-180°	501.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	587	38
15°	50	16
25°	33	15
35°	32	20
45°	35	27
55°	37	33
65°	40	39
75°	42	45
85°	43	35
90°	43	24
95°	43	35
105°	42	45
115°	40	40
125°	36	33
135°	32	25
145°	27	17
155°	21	10
165°	13	4
175°	1	0
180°	0	

TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	853.1
2.5°	942.5
5°	586.8
7.5°	194.5
10°	132.2
12.5°	72.4
15°	50.4
17.5°	41.6
20°	36.5
22.5°	34.6
25°	33.4
27.5°	32.1
30°	32.1
32.5°	32.1
35°	32.1
37.5°	32.7
40°	33.4
42.5°	34.0
45°	34.6
47.5°	35.3
50°	35.9
52.5°	36.5
55°	37.1
57.5°	37.8
60°	38.4
62.5°	39.0
65°	39.7
67.5°	40.3
70°	40.9
72.5°	41.6
75°	42.2
77.5°	42.8
80°	42.8
82.5°	43.4
85°	43.4
87.5°	43.4
90°	43.4
92.5°	43.4
95°	43.4
97.5°	43.4
100°	42.8
102.5°	42.8
105°	42.2
107.5°	42.2
110°	41.6

TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	40.9
115°	40.3
117.5°	39.7
120°	38.4
122.5°	37.8
125°	36.5
127.5°	35.9
130°	34.6
132.5°	33.4
135°	32.1
137.5°	30.9
140°	29.6
142.5°	28.3
145°	27.1
147.5°	25.8
150°	23.9
152.5°	22.0
155°	20.8
157.5°	18.9
160°	17.0
162.5°	15.7
165°	13.2
167.5°	10.7
170°	7.6
172.5°	4.4
175°	1.3
177.5°	0.0
180°	0.0

TEST NUMBER: P1244932

CATALOG NUMBER: PRLX-MIN-M-940-04L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.8	5.8	5.7	6.8	7.9	4.8	5.8	5.7	6.8	7.9
	3H	7.8	8.8	8.7	9.7	10.9	7.8	8.8	8.7	9.7	10.9
	4H	9.3	10.2	10.2	11.2	12.4	9.3	10.2	10.2	11.2	12.4
	6H	10.8	11.7	11.7	12.6	13.8	10.8	11.7	11.7	12.6	13.8
	8H	11.5	12.3	12.4	13.3	14.5	11.5	12.3	12.4	13.3	14.5
	12H	12.2	13.0	13.1	13.9	15.2	12.2	13.0	13.1	13.9	15.2
4H	2H	5.6	6.5	6.5	7.4	8.6	5.6	6.5	6.5	7.4	8.6
	3H	8.8	9.6	9.7	10.5	11.8	8.8	9.6	9.7	10.5	11.8
	4H	10.4	11.2	11.4	12.1	13.4	10.4	11.2	11.4	12.1	13.4
	6H	12.1	12.7	13.0	13.7	15.0	12.1	12.7	13.0	13.7	15.0
	8H	12.9	13.5	13.8	14.5	15.7	12.9	13.5	13.8	14.5	15.7
	12H	13.7	14.2	14.6	15.2	16.5	13.7	14.2	14.6	15.2	16.5
8H	4H	11.0	11.6	11.9	12.6	13.8	11.0	11.6	11.9	12.6	13.8
	6H	12.8	13.4	13.8	14.4	15.6	12.8	13.4	13.8	14.4	15.6
	8H	13.8	14.3	14.7	15.2	16.5	13.8	14.3	14.7	15.2	16.5
	12H	14.7	15.2	15.7	16.2	17.5	14.7	15.2	15.7	16.2	17.5
12H	4H	11.1	11.7	12.1	12.6	13.9	11.1	11.7	12.1	12.6	13.9
	6H	13.0	13.5	14.0	14.5	15.8	13.0	13.5	14.0	14.5	15.8
	8H	14.0	14.5	15.0	15.5	16.8	14.0	14.5	15.0	15.5	16.8

(END OF REPORT)