

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245130

Luminaire Tested: PRLX-NIM-M-927-01L-U-WO

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-927-01L-U-WO
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, WOVEN OVAL SHADE TEXTU
LIGHT LEVEL 1
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 134.7 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 6.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245130
CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

Luminous Intensity Polar Plot





TEST NUMBER: P1245130

CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	79	88	82	77	73	70	66	63	58	56	53	48	46	44	39
2	85	76	68	62	78	70	63	58	60	54	50	50	46	42	40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41	43	39	35	35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35	39	34	30	32	28	25	21
5	65	52	44	37	60	49	41	35	42	35	30	35	30	26	29	25	22	19
6	60	47	39	32	56	44	36	31	38	32	27	32	27	23	27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24	30	25	21	25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	17	14
9	49	37	29	24	46	34	27	22	30	24	20	26	21	18	22	18	15	13
10	47	34	27	22	43	32	25	21	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12161
5°	5329
10°	1027
15°	338
20°	203
25°	159
30°	144
35°	132
40°	139
45°	131
50°	125
55°	133
60°	129
65°	139
70°	137
75°	136
80°	136
85°	137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 140 cd/sqm

TEST NUMBER: P1245130

CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.4	7.0
10°-20°	4.3	3.2
20°-30°	3.9	2.9
30°-40°	5.3	3.9
40°-50°	7.3	5.4
50°-60°	9.2	6.8
60°-70°	11.0	8.1
70°-80°	12.1	9.0
80°-90°	12.4	9.2
90°-100°	12.4	9.2
100°-110°	12.1	9.0
110°-120°	11.2	8.3
120°-130°	9.2	6.8
130°-140°	7.0	5.2
140°-150°	4.4	3.3
150°-160°	2.5	1.9
160°-170°	0.8	0.6
170°-180°	0.1	0.1
0°-30°	17.7	13.1
0°-40°	23.0	17.0
0°-60°	39.5	29.3
0°-90°	74.9	55.6
90°-120°	35.7	26.5
90°-150°	56.3	41.8
90°-180°	60.0	44.5
0°-180°	134.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	142	9
15°	14	4
25°	8	4
35°	8	5
45°	9	7
55°	10	9
65°	11	11
75°	11	12
85°	11	9
90°	11	6
95°	11	9
105°	11	12
115°	11	11
125°	10	9
135°	9	7
145°	7	4
155°	5	3
165°	3	1
175°	0	0
180°	0	

TEST NUMBER: P1245130

CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

CANDELA DISTRIBUTION (FULL):

0°	
0°	237.3
2.5°	238.3
5°	141.5
7.5°	50.0
10°	34.3
12.5°	19.8
15°	13.5
17.5°	10.4
20°	9.4
22.5°	8.3
25°	8.3
27.5°	8.3
30°	8.3
32.5°	8.3
35°	8.3
37.5°	8.3
40°	9.4
42.5°	9.4
45°	9.4
47.5°	9.4
50°	9.4
52.5°	10.4
55°	10.4
57.5°	10.4
60°	10.4
62.5°	10.4
65°	11.4
67.5°	11.4
70°	11.4
72.5°	11.4
75°	11.4
77.5°	11.4
80°	11.4
82.5°	11.4
85°	11.4
87.5°	11.4
90°	11.4
92.5°	11.4
95°	11.4
97.5°	11.4
100°	11.4
102.5°	11.4
105°	11.4
107.5°	11.4
110°	11.4

TEST NUMBER: P1245130

CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

CANDELA DISTRIBUTION (continued):

	0°
112.5°	11.4
115°	11.4
117.5°	11.4
120°	10.4
122.5°	10.4
125°	10.4
127.5°	10.4
130°	9.4
132.5°	9.4
135°	9.4
137.5°	8.3
140°	8.3
142.5°	7.3
145°	7.3
147.5°	6.2
150°	6.2
152.5°	6.2
155°	5.2
157.5°	5.2
160°	4.2
162.5°	3.1
165°	3.1
167.5°	2.1
170°	2.1
172.5°	1.0
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245130

CATALOG NUMBER: PRLX-NIM-M-927-01L-U-WO

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.4	1.4	1.3	2.3	3.5	0.4	1.4	1.3	2.3	3.5
	3H	3.5	4.5	4.4	5.4	6.6	3.5	4.5	4.4	5.4	6.6
	4H	4.9	5.8	5.8	6.8	8.0	4.9	5.8	5.8	6.8	8.0
	6H	6.3	7.2	7.3	8.1	9.3	6.3	7.2	7.3	8.1	9.3
	8H	7.0	7.8	7.9	8.8	10.0	7.0	7.8	7.9	8.8	10.0
	12H	7.6	8.4	8.6	9.4	10.6	7.6	8.4	8.6	9.4	10.6
4H	2H	1.2	2.1	2.1	3.1	4.3	1.2	2.1	2.1	3.1	4.3
	3H	4.5	5.3	5.4	6.2	7.5	4.5	5.3	5.4	6.2	7.5
	4H	6.0	6.8	7.0	7.7	9.0	6.0	6.8	7.0	7.7	9.0
	6H	7.6	8.3	8.5	9.2	10.5	7.6	8.3	8.5	9.2	10.5
	8H	8.4	9.0	9.3	9.9	11.2	8.4	9.0	9.3	9.9	11.2
	12H	9.1	9.7	10.1	10.7	11.9	9.1	9.7	10.1	10.7	11.9
8H	4H	6.6	7.2	7.5	8.1	9.4	6.6	7.2	7.5	8.1	9.4
	6H	8.3	8.8	9.3	9.9	11.1	8.3	8.8	9.3	9.9	11.1
	8H	9.2	9.7	10.2	10.7	12.0	9.2	9.7	10.2	10.7	12.0
	12H	10.1	10.6	11.1	11.6	12.9	10.1	10.6	11.1	11.6	12.9
12H	4H	6.7	7.2	7.6	8.2	9.5	6.7	7.2	7.6	8.2	9.5
	6H	8.5	9.0	9.5	10.0	11.3	8.5	9.0	9.5	10.0	11.3
	8H	9.5	9.9	10.4	10.9	12.2	9.5	9.9	10.4	10.9	12.2

(END OF REPORT)