

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245136

Luminaire Tested: PRLX-NIM-M-927-04L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-M-927-04L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL LINES SHADE TEXT LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 389.2 lumens
Efficiency: N/A
Efficacy: 24.0 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86		73	73	73		61	61	61	56
1	95	89	83	78	88	82	77	73	70	66	63		58	55	53		48	46	44	38
2	85	76	68	62	78	70	63	58	60	54	50		50	46	42		40	37	35	30
3	77	66	58	51	71	61	54	47	52	46	41		43	39	35		35	32	29	25
4	71	59	50	43	65	54	46	40	46	40	35		39	34	30		32	28	25	21
5	65	52	43	37	60	49	41	35	42	35	30		35	30	26		29	25	22	18
6	60	47	39	32	56	44	36	30	38	32	27		32	27	23		27	23	20	17
7	56	43	35	29	52	40	33	27	35	29	24		30	25	21		25	21	18	15
8	53	40	32	26	49	37	30	25	32	26	22		28	23	19		23	19	17	14
9	49	37	29	24	46	34	27	22	30	24	20		26	21	18		22	18	15	13
10	47	34	27	22	43	32	25	21	28	22	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35038
5°	15359
10°	2965
15°	976
20°	584
25°	460
30°	416
35°	382
40°	401
45°	378
50°	360
55°	384
60°	373
65°	401
70°	396
75°	393
80°	394
85°	398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 404 cd/sqm



TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.2	7.0
10°-20°	12.5	3.2
20°-30°	11.3	2.9
30°-40°	15.3	3.9
40°-50°	20.9	5.4
50°-60°	26.6	6.8
60°-70°	31.7	8.1
70°-80°	34.9	9.0
80°-90°	36.0	9.3
90°-100°	36.0	9.3
100°-110°	34.9	9.0
110°-120°	32.4	8.3
120°-130°	26.6	6.8
130°-140°	20.1	5.2
140°-150°	12.8	3.3
150°-160°	7.4	1.9
160°-170°	2.4	0.6
170°-180°	0.2	0.1
0°-30°	50.9	13.1
0°-40°	66.3	17.0
0°-60°	113.8	29.2
0°-90°	216.3	55.6
90°-120°	103.3	26.5
90°-150°	162.8	41.8
90°-180°	173.0	44.5
0°-180°	389.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	408	27
15°	39	12
25°	24	11
35°	24	15
45°	27	21
55°	30	27
65°	33	32
75°	33	35
85°	33	27
90°	33	18
95°	33	27
105°	33	35
115°	33	32
125°	30	27
135°	27	20
145°	21	13
155°	15	7
165°	9	2
175°	0	0
180°	0	

TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	683.7
2.5°	686.7
5°	407.8
7.5°	143.9
10°	99.0
12.5°	57.0
15°	39.0
17.5°	30.0
20°	27.0
22.5°	24.0
25°	24.0
27.5°	24.0
30°	24.0
32.5°	24.0
35°	24.0
37.5°	24.0
40°	27.0
42.5°	27.0
45°	27.0
47.5°	27.0
50°	27.0
52.5°	30.0
55°	30.0
57.5°	30.0
60°	30.0
62.5°	30.0
65°	33.0
67.5°	33.0
70°	33.0
72.5°	33.0
75°	33.0
77.5°	33.0
80°	33.0
82.5°	33.0
85°	33.0
87.5°	33.0
90°	33.0
92.5°	33.0
95°	33.0
97.5°	33.0
100°	33.0
102.5°	33.0
105°	33.0
107.5°	33.0
110°	33.0

TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	33.0
115°	33.0
117.5°	33.0
120°	30.0
122.5°	30.0
125°	30.0
127.5°	30.0
130°	27.0
132.5°	27.0
135°	27.0
137.5°	24.0
140°	24.0
142.5°	21.0
145°	21.0
147.5°	18.0
150°	18.0
152.5°	18.0
155°	15.0
157.5°	15.0
160°	12.0
162.5°	9.0
165°	9.0
167.5°	6.0
170°	6.0
172.5°	3.0
175°	0.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245136

CATALOG NUMBER: PRLX-NIM-M-927-04L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.1	5.1	4.9	6.0	7.2	4.1	5.1	4.9	6.0	7.2
	3H	7.2	8.1	8.1	9.1	10.3	7.2	8.1	8.1	9.1	10.3
	4H	8.6	9.5	9.5	10.5	11.7	8.6	9.5	9.5	10.5	11.7
	6H	10.0	10.9	11.0	11.8	13.0	10.0	10.9	11.0	11.8	13.0
	8H	10.7	11.5	11.6	12.5	13.7	10.7	11.5	11.6	12.5	13.7
	12H	11.3	12.1	12.3	13.1	14.3	11.3	12.1	12.3	13.1	14.3
4H	2H	4.9	5.8	5.8	6.8	8.0	4.9	5.8	5.8	6.8	8.0
	3H	8.2	9.0	9.1	9.9	11.2	8.2	9.0	9.1	9.9	11.2
	4H	9.7	10.5	10.7	11.4	12.7	9.7	10.5	10.7	11.4	12.7
	6H	11.3	11.9	12.2	12.9	14.2	11.3	11.9	12.2	12.9	14.2
	8H	12.1	12.7	13.0	13.6	14.9	12.1	12.7	13.0	13.6	14.9
	12H	12.8	13.4	13.8	14.4	15.6	12.8	13.4	13.8	14.4	15.6
8H	4H	10.2	10.9	11.2	11.8	13.1	10.2	10.9	11.2	11.8	13.1
	6H	12.0	12.5	13.0	13.5	14.8	12.0	12.5	13.0	13.5	14.8
	8H	12.9	13.4	13.9	14.4	15.7	12.9	13.4	13.9	14.4	15.7
	12H	13.8	14.3	14.8	15.3	16.6	13.8	14.3	14.8	15.3	16.6
12H	4H	10.4	10.9	11.3	11.9	13.2	10.4	10.9	11.3	11.9	13.2
	6H	12.2	12.7	13.2	13.7	15.0	12.2	12.7	13.2	13.7	15.0
	8H	13.2	13.6	14.1	14.6	15.9	13.2	13.6	14.1	14.6	15.9

(END OF REPORT)